

4


3

2

1




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		C6	REVISED PER ECO-10-007112	05APR10	JR	CR

D



- 1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR - SEE TABLE.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, SEE TABLE.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
- 2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3 END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.
- 4 WIRE SIZE RANGE
12 - 30 AWG
- 5 RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC., FILE N° E60677.
- 6 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
- 7 NOT CUMULATIVE TOLERANCE.

C



282900-3 AS SHOWN


D

C

B

A

RECOMMENDED PC BOARD LAYOUT



BLACK	MATTE TIN	25	5	1-282900-6
BLACK	0.76um GOLD	25	5	1-282900-5
GREEN	TIN	40	8	282900-8
GREEN	0.76um GOLD	25	5	282900-5
GREEN	TIN	15	3	282900-3
GREEN	TIN	10	2	282900-2
COLOR	PLATING	DIM.A	N° OF POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 07NOV2001 E. ZANOLINI		Tyco Electronics Harrisburg, PA 17105-3608	
CHK 07NOV2001 D. BIEVENOUR		APVD 07NOV2001 D. BIEVENOUR		NAME	
PRODUCT SPEC 108-20166		APPLICATION SPEC 114-20079		TERMINAL BLOCK, PCB MOUNT 2ND LEVEL STACKING W/INTERLOCK, 5mm. PITCH	
WEIGHT -		SIZE A3		CAGE CODE 00779	
CUSTOMER DRAWING		SCALE 3:1		SHEET 1 OF 1	
				REV C6	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[282900-8](#)