

TOSHIBA CMOS Linear Integrated Circuit Silicon Monolithic

TCK207AN

0.75 V, 2A Load Switch IC with Reverse Current Blocking in Ultra Small Package

TCK207AN is 0.75 V ultra-low voltage load switch IC for a power management with slew rate control driver and reverse current blocking (SW OFF state) function.

Switch ON resistance is only 21.5 m Ω (typ.) at 0.75 V, -1.5 A condition and output current is available up to 2.0 A (DC). TCK207AN features output auto-discharge function.

This device is available in ultra-small package DFN4A (1.2 mm \times 1.2 mm, t: 0.38 mm) .Thus this device is ideal for portable applications that require high-density board assembly such as SSD, HDD, cellular phone.

2 DFN4A

Weight: 1.4 mg (Typ.)

Features

- Low input voltage operation: V_{IN} = 0.75 to 3.6 V
- High output current: I_{OUT} (DC) = 2.0 A
- Low ON resistance :


 $R_{ON} = 21.5 \text{ m}\Omega$ (typ.) at $V_{IN} = 3.3 \text{ V}$, -1.5 A

 $R_{ON} = 21.5 \text{ m}\Omega$ (typ.) at $V_{IN} = 1.2 \text{ V}$, -1.5 A


 $R_{ON} = 21.5 \text{ m}\Omega$ (typ.) at $V_{IN} = 0.75 \text{ V}$, -1.5 A

- Built in Slew rate control driver
- Built in Reverse current blocking(SW OFF state)
- Built in Auto-discharge
- Active High and Pull down connection between CONTROL and GND
- Ultra-small package: DFN4A (1.2 mm x 1.2 mm, t: 0.38 mm)

Pin Assignment (Top view)



Marking



Start of commercial production 2020-03



• Absolute Maximum Ratings (Ta = 25°C)

Characteristics	Symbol		Unit	
Input voltage	V _{IN}		-0.3 to 4.0	V
Control voltage	Vст		-0.3 to 4.0	V
Output voltage	Vout		-0.3 to V _{IN} +0.3	V
Output current		DC	2.0	A
	lout	Pulse	3.0 (Note 1)	А
Power dissipation	PD		1 (Note 2)	W
Operating temperature range	T _{opr}		−40 to 85	°C
Junction temeperature	Tj		150	°C
Storage temperature	T _{stg}		−55 to 150	°C

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings. Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc.).

Note1: 100 µs pulse, 2% duty cycle


Note2: Rating at mounting on a board

(Glass epoxy(FR4) board dimension : 40mm x 40mm (double sided board), t=1.6mm Metal pattern ratio : a surface approximately 70%, the reverse side approximately 70%

Through hole: diameter 0.5mm x 24)



Block Diagram



Function Table

Function						
Reverse current blocking	Output auto-discharge	Control pin connection				
Bulit in	Bulit in	Pull down (Active High)				

Operation Logic Table

$0.75 \text{ V} \le \text{V}_{\text{IN}} \le 3.6 \text{V} \text{ (Ta = -40 to } 85^{\circ}\text{C)}$

Control voltage	Output Q ₁	ON
	Discharge Q ₂	OFF
"High"	Reverse current block	Disable
Control voltage "Low"	Output Q₁	OFF
	Discharge Q ₂	ON
	Reverse current block	Active
Control voltage "OPEN"	Output Q₁	OFF
	Discharge Q ₂	ON
	Reverse current block	Active



Electrical Characteristics

• DC Characteristics (Ta = -40 to 85°C)

	0	Test Condition		Ta = 25°C			Ta = -40 to 85°C		11-7
Characteristics	Symbol			Min	Тур.	Max	Min	Max	Unit
Input voltage	VIN		_	0.75	_	3.6	0.75	3.6	V
CONTROL High-level input voltage	VIH	_	0.9 V ≤ V _{IN}	0.85	_	_	0.9 (Note3)	_	٧
			V _{IN} < 0.9V	VIN	_	_	VIN	_	V
CONTROL Low-level input voltage	VIL	_	0.9 V ≤ V _{IN}	_	_	0.4	_	0.4	V
			VIN < 0.9V	_	_	0.3	_	0.3	V
Quiescent current (ON state)	IQ	$V_{IN} = V_{CT} = 3.6 \text{ V}, I_{OUT} = 0 \text{ mA}$		_	22	_	_	35	μА
Standby current (SW OFF state)	IQ(OFF)	V _{IN} = 3.6 V, V _{CT} = 0 V, V _{OUT} : OPEN			0.7	_		5	μА
Reverse blocking current	I _{RB}	V _{OUT} = 3.6 V, V _{IN} = 0 V, V _{CT} = 0 V			0.1	_		10	μА
	Ron	VIN = 3.3 V, IOUT	r = -1.5 A	_	21.5	31		37.3	
		V _{IN} = 1.8 V, I _{OUT} = -1.5 A		_	21.5	31	_	37.3	mΩ
On resistance		V _{IN} = 1.2 V, I _{OUT} = -1.5 A		_	21.5	31	_	37.3	
		V _{IN} = 1.0 V, I _{OUT} = -1.5 A		_	21.5	31	_	37.3	
		V _{IN} = 0.75 V, I _{OUT} = -1.5 A			21.5	31		37.3	
Discharge on resistance	R _{SD}	V _{IN} = 1.8 V, V _{OU}	T = 1.6 V	_	80	_	_	_	Ω

Note 3: V_{IH} 0.85V (Min) @ Ta=0 to 85°C



• AC Characteristics (Ta = 25°C)

$V_{IN} = 0.75 V$

Characteristics	Symbol	Test Condition(Figure 1)	Min	Тур.	Max	Unit
V _{OUT} rise time	t _r	$R_L = 500 \ \Omega, \ C_L = 0.1 \ \mu F$	_	180	_	μS
V _{OUT} fall time	t _f	$R_L = 500 \ \Omega, \ C_L = 0.1 \ \mu F$	_	30	_	μS
Turn on delay	ton	$R_L = 500 \ \Omega, \ C_L = 0.1 \ \mu F$	_	75	_	μS
Turn off delay	tOFF	$R_L = 500 \Omega$, $C_L = 0.1 \mu F$	_	8	_	μS


$V_{IN} = 1.2 V$

Characteristics	Symbol	Test Condition(Figure 1)	Min	Тур.	Max	Unit
V _{OUT} rise time	t _r	$R_L = 500 \ \Omega, \ C_L = 0.1 \ \mu F$	_	240	_	μS
Vout fall time	tf	$R_L = 500 \ \Omega, \ C_L = 0.1 \ \mu F$		20	_	μS
Turn on delay	ton	$R_L = 500 \ \Omega, \ C_L = 0.1 \ \mu F$	_	65	_	μS
Turn off delay	tOFF	$R_L = 500 \Omega$, $C_L = 0.1 \mu F$	_	8	_	μS

$V_{IN} = 1.8 V$

Characteristics	Symbol	Test Condition(Figure 1)	Min.	Тур.	Max.	Unit
V _{CT} - V _{OUT} rise time	ton + t _r	$R_L = 500 \ \Omega, \ C_L = 0.1 \ \mu F$		400		μS

AC Waveform







Figure 1 t_r , t_f , t_{ON} , t_{OFF} Waveforms



Application Note

1. Application circuit example

The figure below shows the configuration for TCK207AN.



1) Input capacitor

An input capacitor (C_{IN}) is necessary for the stable operation of TCK207AN. And it is effective to reduce voltage drop due to sharp changes in output current and also for improved stability of the power supply. When used, place C_{IN} more than 1.0 μ F as close to V_{IN} pin to improve stability of the power supply.

2) Output capacitor

An output capacitor (C_{OUT}) is not necessary for the guaranteed operation of TCK207AN. However, there is a possibility of overshoot or undershoot caused by output load transient response, board layout and parasitic components of load switch IC. In this case, an output capacitor with C_{OUT} more than 0.1 μ F is recommended.

3) Control pin

A control pin for TCK207AN is Active High with Schmitt trigger circuit. This controls both the pass-through n-ch MOSFET and the discharge n-ch MOSFET, operated by the control voltage. When the control voltage level is High, Output n-ch MOSFET is ON state and discharge n-ch MOSFET is SW OFF state. When control voltage level is Low, the state of the MOSFETs is reversed. Also, pull down resistance equivalent to a few $M\Omega$ is connected between CONTROL and GND, thus the load switch IC is in SW OFF state even when CONTROL pin is OPEN. In addition, CONTROL pin has a tolerant function such that it can be used even if the control voltage is higher than the input voltage.

2. Reverse current blocking

Reverse current blocking (SW OFF state) function is designed in this product. This function is active at output n-ch MOSEFT turned off.

However this function does not assure for the suppression of uprising device operation. In use of this product, please read through and understand dissipation idea for absolute maximum ratings from the above mention or our 'Semiconductor Reliability Handbook'. Then use this product under absolute maximum ratings in any condition. Furthermore, Toshiba recommends inserting failsafe system into the design.




3. Power Dissipation

Board-mounted power dissipation rating for TCK207AN is available in the Absolute Maximum Ratings table. Power dissipation is measured on the board condition shown below.

[The Board Condition]


(Glass epoxy(FR4) board dimension : 40 mm x 40 mm (double sided board), t = 1.6 mm Metal pattern ratio : a surface approximately 70%, the reverse side approximately 70% Through hole : diameter 0.5 mm x 24)





Please allow sufficient margin when designing a board pattern to fit the expected power dissipation. Also take into consideration the ambient temperature, input voltage, output current etc. and applying the appropriate derating for allowable power dissipation during operation.



Representative Typical Characteristics








Note: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.



Package dimension

DFN4A

Unit: mm




Weight: 1.4 mg (Typ.)



Land pattern dimensions (for reference only)

Unit: mm





RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE
 EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY
 CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT
 ("UNINTENDED USE"). Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation,
 equipment used in nuclear facilities, equipment used in the aerospace industry, lifesaving and/or life supporting medical equipment,
 equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or
 explosions, safety devices, elevators and escalators, and devices related to power plant. IF YOU USE PRODUCT FOR UNINTENDED USE,
 TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT. For details, please contact your TOSHIBA sales representative or contact us via our
 website.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any
 applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any
 infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any
 intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR
 PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER,
 INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING
 WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2)
 DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR
 INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE,
 ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for
 the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass
 destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations
 including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export
 and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and
 regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please
 use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including
 without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT
 OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.

TOSHIBA ELECTRONIC DEVICES & STORAGE CORPORATION

https://toshiba.semicon-storage.com/

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Toshiba:

TCK207AN,LF