











MATERIALS			
NO	COMPONENT NAME	BASE MATERIAL	FINISH
1	HOUSING	DIALLYL PHTHALATE RESIN	
2	END TERMINAL	SILVER CLAD COPPER ALLOY	GOLD FLASH
3	CENTER TERMINAL	COPPER ALLOY	GOLD FLASH
4	ROCKER CONTACT	SILVER CLAD COPPER ALLOY	GOLD FLASH
5	ACTUATOR TIP	PHENOL RESIN, UL94 HB	
6	ACTUATOR SPRING	MUSIC WIRE	
7	ACTUATOR	PHENOL RESIN, UL94 HB	
8	ACTUATOR GUIDE	POLYAMID	
9	FRAME	STAINLESS STEEL PER 100-77	
10	RETAINER/STOPPER	BRASS	NONE
11	PLUNGER SPRING	MUSIC WIRE	
12	PLUNGER PIN	BRASS	
13	BUSHING	ZINC	NICKEL
14	PLUNGER	BRASS	NICKEL
15	MOUNTING NUTS (1)	BRASS	NICKEL
17	INTERNAL TOOL LOCKWASHER	STEEL	NICKEL
18	STEM O-RING		
19	BUSHING O-RING		

SPECIFICATIONS — SEE NOTE 3			
CURRENT RATING UL & CSA	6A @ 125 VAC (RESISTIVE)		
	3A @ 250 VAC (RESISTIVE)		
	4A @ 28 VDC (RESISTIVE)		
INITIAL CONTACT RESISTANCE	10 MILLIOHMS MAX @ 2–4 VDC, 1A		
DIELECTRIC STRENGTH	1,500 MEGOHMS MIN.		
WITHSTANDING VOLTAGE	1,000 VAC		
TRAVEL	.140		
ACTUATION FORCE	.4 to 2 kgf		
OPERATING TEMPERATURE	–20C TO +85C		
STORAGE TEMPERATURE	–40C TO +85C		
CONTACT TIMING	BREAK BEFORE MAKE		
TERMINAL SEAL	OVER MOLDED		
DURABILITY	PARAMETER	PUSH ON/ PUSH OFF	MOMENTARY
	250 VAC (3A RESISTIVE)	50,000	50,000
	125 VAC (6A RESISTIVE)	50,000	50,000
	28 VDC (4A RESISTIVE)	50,000	50,000


- | | |
|---|--|
| 1 | TERMINAL NUMBERS ARE FOR REFERENCE ONLY AND DO NOT APPEAR ON THE SWITCHES |
| 2 | EACH SWITCH SUPPLIED WITH THE FOLLOWING MOUNTING HARDWARE:
(1) 1/4-40 UNS-2B HEX NUT
(1) LOCK WASHER
(1) BUSHING 'O' RING |
| 5 | WIRE LUG CONTACTS WILL ACCEPT 2 #20 AWG SOLID OR STRANDED WIRES |
| 6 | MARK SWITCH |
| 7 | ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS) |
| 8 | PUSHBUTTON CAP SOLD SEPARATELY. SEE DRAWING 1825068 AND 1825069 FOR AVAILABLE CAPS |
| 9 | LASER MARKING USED FOR PARTS |



PART NUMBER	Alco P/N	Mark Switch 	Poles	Throws	Terminal	Function		Connected Terminals	
									
4-1437567-8	MPE406R	MPE 406R	4	2	Wire lug	ON	MOM	2-1, 5-4, 8-7, 11-10	2-3, 5-6, 8-9, 11-12
4-1437567-7	MPE406N	MPE 406N	4	2	Wire lug	ON	ON	2-1, 5-4, 8-7, 11-10	2-3, 5-6, 8-9, 11-12
4-1437567-6	MPE306F	MPE 306F	3	2	Wire lug	ON	MOM	2-1, 5-4, 8-7	2-3, 5-6, 8-9
4-1437567-5	MPE206R	MPE 206R	2	2	Wire lug	ON	MOM	2-1, 5-4	2-3, 5-6
4-1437567-4	MPE206N	MPE 206N	2	2	Wire lug	ON	ON	2-1, 5-4	2-3, 5-6
4-1437567-3	MPE106F	MPE 106F	1	2	Wire lug	ON	MOM	2-1	2-3
4-1437567-2	MPE106D	MPE 106D	1	2	Wire lug	ON	ON	2-1	2-3


THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN M.BINNER	15NOVD04	 TE Connectivity	
DIMENSIONS: INCHES		CHK M.ZITTO	15NOVD04		
		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ALCOSWITCH GREEN SERIES PUSHBUTTON SWITCH, MPE SERIES	
		0 PLC ± . 1 PLC ± . 2 PLC ± . 3 PLC ± .012 4 PLC ± . ANGLES ± .		PRODUCT SPEC — APPLICATION SPEC —	
MATERIAL —		FINISH —		SIZE A1	
		WEIGHT —		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO 4-1437567-3	
				RESTRICTED TO —	
				SCALE 3:1	
				SHEET 1 OF 3	
				REV A0	

LOC		DIST		REVISIONS				
AD		00		REV	DATE	BY	CHK	APP
				1	15NOV04	M. ZITTO		
				2	15NOV04	M. ZITTO		




MPE-106


MPE-206



WIRE LUG TERMINAL



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BINNER	15NOV04	TE Connectivity	
		CHK M. ZITTO	15NOV04		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME ALCOSWITCH GREEN SERIES PUSHBUTTON SWITCH, MPE SERIES	
		0. PLC ± .012 1. PLC ± .012 2. PLC ± .012 3. PLC ± .012 4. PLC ± .012 ANGLES ± .012		APPLICATION SPEC	
MATERIAL		FINISH		WEIGHT	
-		-		-	
CUSTOMER DRAWING		SCALE 3:1		SHEET 2 OF 3	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[MPE206N](#)