






THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
(C) COPYRIGHT - By -	ALL RIGHTS RESERVED.	






LOC	DIST	REVISIONS					
—	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C3	REVISED PER ECO-14-010935	19JUL2014	NK	RH

			Materials
No	Component name	Base material	Plating
1	Housing	Diallyl phthalate resin	
2	End terminal	silver clad copper alloy	gold flash
3	Center terminal	copper alloy	gold flash
4	Rocker contact	silver clad copper alloy	gold flash
5	Actuator tip	Phenol resin, UL94 HB	
6	Actuator spring	music wire	
7	Actuator	Phenol resin, UL94 HB	
8	Actuator guide	polymer	
9	Frame	stainless steel 100-77	
10	Retainer/Stopper	polyamid resin	none
11	Plunger spring	music wire	
12	Plunger pin	brass	
13	Bushing	zinc	nickel
14	Plunger	brass	nickel
15	Mounting nuts (2)	brass	nickel
16	Locating ring	cold rolled steel	nickel
17	Internal tooth lockwasher	steel	nickel



Specifications			
Current rating UL & CSA	6A @ 125 VAC (resistive)		
	3A @ 250 VAC (resistive)		
	4A @ 28 VDC (resistive)		
Initial contact resistance	10 milliohms max @ 2–4 VDC, 1A		
Dielectric strength	1,000 megohms min.		
Withstanding voltage	1,500 VAC		
Travel	.140		
Actuation force	.4 to 2 kgf		
Operating temperature	–20C to +85C		
Storage temperature	–40C to +85C		
Contact timing	break before make		
Terminal seal	over molded		
Durability	Parameter	Push on/ Push off	Momentary
	250 VAC (3A resistive)	30,000	30,000
	125 VAC (6A resistive)	30,000	30,000
	28 VDC (4A resistive)	30,000	30,000



PART NUMBER	Alco P/N	Mark SWITCH 	Poles	Throws	Terminal	Function		Connected Terminals	
									
5-1437567-8	MPG406R	MPG 406R	4	2	Wire lug	ON	MOM	2-1, 5-4, 8-7, 11-10	2-3, 5-6, 8-9, 11-12
5-1437567-7	MPG406N	MPG 406N	4	2	Wire lug	ON	ON	2-1, 5-4, 8-7, 11-10	2-3, 5-6, 8-9, 11-12
5-1437567-6	MPG306F	MPG 306F	3	2	Wire lug	ON	MOM	2-1, 5-4, 8-7	2-3, 5-6, 8-9
5-1437567-5	MPG306D	MPG 306D	3	2	Wire lug	ON	ON	2-1, 5-4, 8-7	2-3, 5-6, 8-9
5-1437567-4	MPG206RPC	MPG 206RPC	2	2	PC	ON	MOM	2-1, 5-4	2-3, 5-6
5-1437567-3	MPG206R	MPG 206R	2	2	Wire lug	ON	MOM	2-1, 5-4	2-3, 5-6
5-1437567-2	MPG206NPC	MPG 206NPC	2	2	PC	ON	ON	2-1, 5-4	2-3, 5-6
5-1437567-1	MPG206N	MPG 206N	2	2	Wire lug	ON	ON	2-1, 5-4	2-3, 5-6
5-1437567-0	MPG106F	MPG 106F	1	2	Wire lug	ON	MOM	2-1	2-3
4-1437567-9	MPG106D	MPG 106D	1	2	Wire lug	ON	ON	2-1	2-3

NOTES:

1. TERMINAL NUMBERS ARE FOR REFERENCE ONLY AND DO NOT APPEAR ON THE SWITCHES.
2. EACH SWITCH SUPPLIED WITH THE FOLLOWING MOUNTING HARDWARE:
 - (2) 15/32-32 UNS-2B HEX NUTS
 - (1) INTERNAL TOOTH LOCKWASHER
 - (1) LOCATING RING






WIRE LUG CONTACTS WILL ACCEPT 2 #20 AWG SOLID OR STRANDED WIRES.






MARK SWITCH



7. ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS).
8. BLACK CAP INCLUDED WITH EACH SWITCH IF DIFFERENT COLOR REQUIRED ORDER SEPARATELY DRAWING NUMBER 7-1437627-1
9. LASER MARKING USED FOR PARTS.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. M.BINNER	02MAR09	 TE Connectivity		
		CHK. M.ZITTO	15NOV04			
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED: M.ZITTO APVD 15NOV04		NAME	ALCOSWITCH GREEN SERIES PUSHBUTTON SWITCH, MPG SERIES	
		PRODUCT SPEC				
		APPLICATION SPEC				
		SIZE		CAGE CODE		DRAWING NO
		WEIGHT				
MATERIAL		FINISH		A1 00779  4-1437567-9		
		CUSTOMER DRAWING		SCALE 3:1 SHEET 1 OF 3 REV C		

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
—	—	—	—	SEE SHEET 1	—	—







MPG-206








THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER	02MAR09	 TE Connectivity			
DIMENSIONS: INCHES		CHK M.ZITTO	15NOV04				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		AP'D M.ZITTO	15NOV04	NAME ALCOSWITCH GREEN SERIES PUSHBUTTON SWITCH, MPG SERIES		
	0 PLC ± .012		PRODUCT SPEC				
	1 PLC ± .012		APPLICATION SPEC				
	4 PLC ± .012		WEIGHT				
MATERIAL	FINISH	—		SIZE CAGE CODE DRAWING NO		RESTRICTED TO	
—	—	—		A1 00779 C 4-1437567-9		—	
CUSTOMER DRAWING				SCALE	3:1	SHEET 2 OF 3	REV C.3

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
—	—	—	—	SEE SHEET 1	—	—



COUNTRY OF ORGIN STAMPED HERE EITHER SIDE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER	02MAR09	 TE Connectivity	
DIMENSIONS: INCHES		CHK M.ZITTO	15NOV04		
	TOLERANCES, UNLESS OTHERWISE SPECIFIED:		RPV0 M.ZITTO	NAME ALCOSWITCH GREEN SERIES PUSHBUTTON SWITCH, MPG SERIES	SIZE A1
	0 PLC ± —		PRODUCT SPEC		
	1 PLC ± —		APPLICATION SPEC		
	2 PLC ± —				
	3 PLC ± .012				
	4 PLC ± —				
ANGLES ± ± —		WEIGHT	RESTRICTED TO		
FINISH		—		—	
MATERIAL		—		—	
		CUSTOMER DRAWING		SCALE 3:1 SHEET 3 OF 3 REV C.3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[MPG406N](#)