

Photocouplers Photorelay

TLP3440

1. Applications (Note)

- · Measuring Instruments
- · High-Speed Logic IC Testers
- · High-Speed Memory Testers
- · Battery Control and Monitoring

Note: The product(s) described herein should not be used for any other application.


2. General

The TLP3440 photorelay consists of a photo MOSFET optically coupled to an infrared LED. It is housed in a VSON4 package. The TLP3440 features low output capacitance of $C_{\rm OFF}$, thus it is suitable for high frequency signal applications.

3. Features


- (1) Normally opened (1-Form-A)
- (2) OFF-state output terminal voltage: 40 V (min)
- (3) Trigger LED current: 3 mA (max)
- (4) ON-state current: 120 mA (max)
- (5) ON-state resistance: 12Ω (typ.), 14Ω (max)
- (6) Output capacitance: 0.45 pF(typ.), 0.8 pF(max)
- (7) Isolation voltage: 500 Vrms (min)

4. Packaging and Pin Assignment





5. Internal Circuit



6. Absolute Maximum Ratings (Note) (Unless otherwise specified, T_a = 25 °C)

	Characteristics		Symbol	Note	Rating	Unit
LED	Input forward current		I _F		30	mA
	Input forward current derating	(T _a ≥ 25 °C)	$\Delta I_F/\Delta T_a$		-0.3	mA/°C
	Input reverse voltage		V _R		5	V
	Input power dissipation		P _D		50	mW
	Input power dissipation derating	$(T_a \ge 25 ^{\circ}C)$	$\Delta P_D/\Delta T_a$		-0.5	mW/°C
	Junction temperature		Tj		125	℃
Detector	OFF-state output terminal voltage		V _{OFF}		40	V
	ON-state current		I _{ON}		120	mA
	ON-state current derating	$(T_a \ge 25 ^{\circ}C)$	Δl _{ON} /ΔT _a		-1.2	mA/°C
	ON-state current (pulsed)	(t = 100 ms, Duty = 1/10)	I _{ONP}		360	mA
	Output power dissipation		Po		202	mW
	Output power dissipation derating	$(T_a \ge 25 ^{\circ}C)$	$\Delta P_O/\Delta T_a$		-2.02	mW/°C
	Junction temperature		Tj		125	°C
Common	Storage temperature		T _{stg}		-40 to 125	
	Operating temperature		T _{opr}		-40 to 110	
	Lead soldering temperature	(10 s)	T _{sol}		260	
	Isolation voltage	AC, 60 s, R.H. ≤ 60 %	BV _S	(Note 1)	500	Vrms

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

Note 1: This device is considered as a two-terminal device: Pins 1 and 2 are shorted together, and pins 3 and 4 are shorted together.

Note: This device is sensitive to electrostatic discharge (ESD). Extreme ESD conditions should be guarded against by using proper antistatic precautions for the worktable, operator, solder iron, soldering equipment and so on.

7. Recommended Operating Conditions (Note)

Characteristics	Symbol	Note	Min	Тур.	Max	Unit
Supply voltage	V_{DD}		_		32	V
Input forward current	I _F		5	7.5	20	mA
ON-state current	I _{ON}				120	mA
Operating temperature	T _{opr}		-20		85	°C

Note: The recommended operating conditions are given as a design guide necessary to obtain the intended performance of the device. Each parameter is an independent value. When creating a system design using this device, the electrical characteristics specified in this data sheet should also be considered.



8. Electrical Characteristics (Unless otherwise specified, T_a = 25 °C)

	Characteristics	Symbol	Note	Test Condition	Min	Тур.	Max	Unit
LED	Input forward voltage	V _F		I _F = 10 mA	1.1	1.27	1.4	V
	Input reverse current	I _R		V _R = 5 V		_	10	μА
	Input capacitance	Ct		V = 0 V, f = 1 MHz		30		pF
Detector	OFF-state current	I _{OFF}		V _{OFF} = 40 V		_	1	nA
	Output capacitance	C _{OFF}		V = 0 V, f = 100 MHz, t < 1 s		0.45	0.8	pF

9. Coupled Electrical Characteristics (Unless otherwise specified, Ta = 25 °C)

Characteristics	Symbol	Note	Test Condition	Min	Тур.	Max	Unit
Trigger LED current	I _{FT}		I _{ON} = 100 mA	_	_	3	mA
Return LED current	I _{FC}		I _{OFF} = 10 μA	0.1		_	
ON-state resistance	R _{ON}		I _{ON} = 120 mA, I _F = 5 mA, t < 1 s		12	14	Ω

10. Isolation Characteristics (Unless otherwise specified, Ta = 25 °C)

Characteristics	Symbol	Note	Test Condition	Min	Тур.	Max	Unit
Total capacitance (input to output)	Cs	(Note 1)	V _S = 0 V, f = 1 MHz	_	1		pF
Isolation resistance	R _S	(Note 1)	V _S = 500 V, R.H. ≤ 60 %		1014		Ω
Isolation voltage	BVS	(Note 1)	AC, 60 s	500			Vrms

Note 1: This device is considered as a two-terminal device: Pins 1 and 2 are shorted together, and pins 3 and 4 are shorted together.

11. Switching Characteristics (Unless otherwise specified, T_a = 25 °C)

Characteristics	Symbol	Note	Test Condition	Min	Тур.	Max	Unit
Turn-on time	t _{ON}		See Fig. 11.1.	_	_	200	μS
Turn-off time	t _{OFF}		$R_L = 200 \Omega$, $V_{DD} = 20 V$, $I_F = 5 mA$			300	




Fig. 11.1 Switching Time Test Circuit and Waveform



12. Characteristics Curves (Note)




Fig. 12.1 I_F - T_a




Fig. 12.3 I_F - V_F




Fig. 12.5 R_{ON} - T_a




Fig. 12.2 I_{ON} - T_a




Fig. 12.4 I_{ON} - V_{ON}




Fig. 12.6 I_{FT} - T_a






Fig. 12.7 toN, toFF - IF




Fig. 12.8 toN, toFF - Ta




Fig. 12.9 loff - Voff




Fig. 12.10 I_{OFF} - T_a




Fig. 12.11 C_{OFF}/C_{OFF}(0 V) - V_{OFF}

Note: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.



13. Soldering and Storage

13.1. Precautions for Soldering

The soldering temperature should be controlled as closely as possible to the conditions shown below.


· When using soldering reflow

(See the figure shown below, which is based on the package surface temperature.)

Reflow soldering may be performed up to twice.

The first reflow soldering should be performed within 168 hours after opening the moisture-proof packaging.

The second reflow soldering must be performed within 168 hours of the first reflow.



	Symbol	Min	Max	Unit
Preheat temperature	Ts	150	200	ů
Preheat time	ts	60	120	S
Ramp-up rate (T _L to T _P)			3	°C/s
Liquidus temperature	TL	217		°C
Time above T _L	tL	60	150	S
Peak temperature	T _P		260	°C
Time during which T_c is between ($T_P - 5$) and T_P	t _P		30	s
Ramp-down rate (T _P to T _L)			6	°C/s

When using soldering Iron
 Complete soldering within 10 seconds for lead temperature not exceeding 260 °C.
 Heating by soldering iron must be done only once per lead.



13.2. Precautions for General Storage

- · Avoid storage locations where devices may be exposed to moisture or direct sunlight.
- Do not store the products in locations with poisonous gases (especially corrosive gases) or in dusty conditions.
- Store the products in locations with minimal temperature fluctuations. Rapid temperature changes during storage can cause condensation, resulting in lead oxidation or corrosion, which will deteriorate the solderability of the leads.
- Do not allow loads to be applied directly to devices while they are in storage.
- If devices have been stored for more than two years under normal storage conditions, it is recommended that you check the leads for ease of soldering prior to use.
- · Follow the precautions printed on the packing label of the device for transportation and storage.
- Thermal stress may cause a crack in surface-mount products during surface-mount assembly if they have absorbed atmospheric moisture. To prevent a crack, please observe the following precautions.
 - 1. Moisture-proof bags may be stored unopened for up to 12 months under the following conditions.

Temperature: 5 °C to 30 °C

Humidity: 90 % (max)

- 2. After opening the moisture-proof bag, the devices should be assembled within 168 hours in an environment of 5 $^{\circ}$ C to 30 $^{\circ}$ C/70 %RH or below.
- 3. If, upon opening, the moisture indicator card shows a humidity of 30 % or above (i.e., has turned pink) or the expiration date has passed, the devices should be baked in tape and reel.

After baking, use the baked devices within 72 hours, but perform baking only once.


Baking conditions: 60±5 °C, for 64 to 72 hours.

Expiration date: 12 months from the sealing date, which is imprinted on the label affixed.


- 4. Repeated baking can affect the peeling strength of taping and cause a trouble during mounting. Furthermore, protect the devices against static electricity for baking.
- 5. If the laminated packing material is broken, its hermeticity deteriorates. Therefore, do not throw or drop the packed devices.
- 6. When restoring devices after removal from their packing, use anti-static containers.



14. Land Pattern Dimensions (for reference only)



15. Marking



16. Ordering Information

When placing an order, please specify the part number, tape type and quantity as shown in the following example.

Example) TLP3440(TP,F 3000 pcs

Part number: TLP3440

Tape type: TP

[[G]]/RoHS COMPATIBLE: F (Note 1)

Quantity (must be a multiple of 3000): 3000 pcs


Note 1: Please contact your Toshiba sales representative for details on environmental information such as the product's RoHS compatibility.

RoHS is the Directive 2011/65/EU of the European Parliament and of the Council of 8 June 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.



Package Dimensions

Unit: mm



Weight: 10 mg (typ.)

	Package Name(s)
TOSHIBA: 11-2D1A	



RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- · TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's
 written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications; including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications.
 TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE").
 - Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, lifesaving and/or life supporting medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, and devices related to power plant.
 - IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT.
 - For details, please contact your TOSHIBA sales representative or contact us via our website.
- · Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any
 applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE
 FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER,
 INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING
 WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND
 (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT,
 OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR
 PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- GaAs (Gallium Arsenide) is used in Product. GaAs is harmful to humans if consumed or absorbed, whether in the form of dust or vapor.
 Handle with care and do not break, cut, crush, grind, dissolve chemically or otherwise expose GaAs in Product.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product.
 Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.

TOSHIBA ELECTRONIC DEVICES & STORAGE CORPORATION

https://toshiba.semicon-storage.com/

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Toshiba:

TLP3440(TP,F