





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER ECO-12-006972	23AUG2012	KH	JE


- 1
- FINISH:
CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF
TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON
TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
COMPLIANT PIN AREA: 0.5µm MIN MATTE TIN OVER BASE PLATING.
- 2
- PHOSPHOR BRONZE
- 3
- LCP, UL94V-0
- 4
- CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- 5
- REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 6
- APPLICATION SEATING HEIGHT TO PRINTED CIRCUIT BOARD
- 7
- DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 8
- CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995



SECTION B-B



RECOMMENDED
PRINTED CIRCUIT BOARD
LAYOUT
COMPONENT SIDE OF PRINTED CIRCUIT BOARD



5.50	8.2	5120739-1
M	L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO	07DEC04	 TE Connectivity			
DIMENSIONS:		CHK R. PATTERSON	07DEC04				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R. PATTERSON	07DEC04	NAME	HEADER ASSEMBLY, 30 POSITION, 6 ROW, BACKPLANE CONNECTOR, -		
		PRODUCT SPEC					
	0 PLC ±.1	APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	1 PLC ±.05						
	2 PLC ±.10			A1	00779	C=5120739	
	3 PLC ±.05						
	4 PLC ±.1						
MATERIAL	HOUSING: 3	WEIGHT					
		CUSTOMER DRAWING					
	CONTACTS: 2	SCALE 5:1		SHEET 1 OF 1 REV B			
	SIGNAL CONTACT: 4						
	FINISH GROUND CONTACT: 1						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5120739-1](#)