




- 1 FASTON TERMINALS, BASE P/N 63654,
ARE USED IN THIS PRODUCT.
- 2 TIN PLATE PER MIL-T-10727,
0.001016 [0.000040] MIN.
-  3 MATERIAL: HOUSING- 6/6 NYLON, V0
TERMINAL- H04 BRASS,
STRESS RELIEVED FASTON TERMINAL

STANDARD	NATURAL	TIN 	2.29—3.30 [.090—.130]	0.5—1.3 mm ² [20—16]	0.813 [.032]	521830—2
PACKAGING	HOUSING COLOR	TERMINAL FINISH	INSULATION RANGE	WIRE SIZE	MATING TAB THK ±0.025 [±.001]	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 17JUN05	 TE Connectivity			
		CHK G PORTA 17JUN05				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD G PORTA 17JUN05	NAME			
	0 PLC ± —	PRODUCT SPEC	ASSEMBLY, RECEPTACLE, ULTRA—POD, 4.8 [.187] SERIES			
	1 PLC ± —	118—1285				
	2 PLC ± —	APPLICATION SPEC				
	3 PLC ± 0.25 [.010]	114—2124				
	4 PLC ± —					
ANGLES ± —		SIZE CAGE CODE DRAWING NO	RESTRICTED TO			
MATERIAL 	FINISH —	WEIGHT —	A2	00779	C=521830	—
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[521830-2](#)