

# CSE5-100401

### Description:


EE5 Surface mounting design  
Height: 5.3mm Max  
Optimal performance at 250 kHz and above  
Primary Current Rating: 10 amps  
Insulation Resistance: 10MΩ Minimum  
Operating Temperature Range: -15°C to +105°C  
Custom designs available  
Energy Time (E.T.) = 21.6V μS Max

### Application:


Ac current detection  
Output supply for control circuit  
Switching Power Supply

## Electrical Specifications @ 25C


Turns N1:N2	Secondary Min Inductance (μH)	Secondary Max DCR (mΩ)	Color Code	
			Dot	Tape
1:40	320	1140	RED	RED




### Mechanical:



### Packing:



**Schematic:**



**RoHS Compliance:** As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.

\* Upon printing, this document is considered “uncontrolled”. Please contact Triad Magnetics’ website for the most current version

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Triad Magnetics:](#)

[CSE5-100401](#)