






RECOMENDED HOLE LAYOUT
FOR BOTTOM ENTRY OR PASS
THROUGH APPLICATIONS

- ① TE CONNECTIVITY LOGO AND CSA LOGO ARE MOLDED INTO THE HOUSING.
- ② TOLERANCE NON-CUMULATIVE.
- ③ DUPLEX PLATED: 0.00076 (.000030) GOLD IN CONTACT AREA, .00381-.00762 (.000150-.000300) BRIGHT TIN-LEAD ON LEADS, ALL OVER 0.00127 (.000050) MIN NICKEL.
- ④ THESE DIMENSIONS PERTAIN TO CAVITY C/L'S ONLY, NOT TO CONTACT LOCATIONS.
- ⑤ NO PART NUMBER MARKING REQUIRED ON THIS PART NUMBER.
- ⑥ HOUSING: FLAME RETARDANT GLASS FILLED POLYESTER - BLACK.
CONTACTS: PHOS. BRONZE.
- ⑦ POINT OF CONTACT DIMENSION.
- ⑧ POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE CONTACT BEAMS).
- ⑨ DUPLEX PLATED: 0.00076 (.000030) GOLD DUPLEX IN CONTACT AREA, .00381-.00762 (.000150-.000300) MATTE TIN ON LEADS, ALL OVER 0.00127 (.000050) MIN NICKEL.
- ⑩ ROHS 2002/95/EC COMPLIANT
- ⑪ PART NUMBER AND DATE CODE ARE MARKED IN APPROXIMATE LOCATION SHOWN.
- ⑫ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. BOLES 19-11-92 CHK T. KINSEY 19-11-92 APVD —		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		NAME ASSEMBLY, MOD II DOUBLE ROW, .100 X .100 C/L, VERTICAL MOUNTED, CLOSED ENTRY, SHORT PT. CONTACTS	
		PRODUCT SPEC 108-25026 APPLICATION SPEC 114-25018		SIZE A2	
MATERIAL 		WEIGHT —		CAGE CODE 00779	
FINISH 		DRAWING NO C-534236		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 4:1 SHEET 1 of 2 REV V2	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOCAD

DIST00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

FINISH	A	B	NO OF POSN	PART NO.	
5	9	1.300	1.200	26	10 9-534236-1
OBSOLETE	9	4.000	3.900	80	10 9-534236-0
	9	3.900	3.800	78	10 8-534236-9
	9	3.800	3.700	76	10 8-534236-8
	9	3.700	3.600	74	10 8-534236-7
	9	3.600	3.500	72	10 8-534236-6
	9	3.500	3.400	70	10 8-534236-5
	9	3.400	3.300	68	10 8-534236-4
	9	3.300	3.200	66	10 8-534236-3
	9	3.200	3.100	64	10 8-534236-2
	9	3.100	3.000	62	10 8-534236-1
	9	3.000	2.900	60	10 8-534236-0
	9	2.900	2.800	58	10 7-534236-9
	9	2.800	2.700	56	10 7-534236-8
	9	2.700	2.600	54	10 7-534236-7
	9	2.600	2.500	52	10 7-534236-6
	9	2.500	2.400	50	10 7-534236-5
	9	2.400	2.300	48	10 7-534236-4
	9	2.300	2.200	46	10 7-534236-3
	9	2.200	2.100	44	10 7-534236-2
	9	2.100	2.000	42	10 7-534236-1
OBSOLETE	9	2.000	1.900	40	10 7-534236-0
	9	1.900	1.800	38	10 6-534236-9
OBSOLETE	9	1.800	1.700	36	10 6-534236-8
OBSOLETE	9	1.700	1.600	34	10 6-534236-7
	9	1.600	1.500	32	10 6-534236-6
OBSOLETE	9	1.500	1.400	30	10 6-534236-5
	9	1.400	1.300	28	10 6-534236-4
OBSOLETE	9	1.300	1.200	26	10 6-534236-3
	9	1.200	1.100	24	10 6-534236-2
OBSOLETE	9	1.100	1.000	22	10 6-534236-1
OBSOLETE	9	1.000	.900	20	10 6-534236-0
	9	.900	.800	18	10 5-534236-9
5	9	.800	.700	16	10 5-534236-8
	9	.700	.600	14	10 5-534236-7
5	9	.600	.500	12	10 5-534236-6
	9	.500	.400	10	10 5-534236-5
OBSOLETE	9	.400	.300	8	10 5-534236-4
OBSOLETE	9	.300	.200	6	10 5-534236-3
OBSOLETE	9	.200	.100	4	10 5-534236-2
OBSOLETE	9	.100	-	2	10 5-534236-1
FINISH	A	B	NO OF POSN	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

MATERIAL

6

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FINISH

3

9

DWN
R. BOLES
19-11-92

CHK
T. KINSEY
19-11-92

APVD
-

PRODUCT SPEC
108-25026

APPLICATION SPEC
114-25018

WEIGHT
-

CUSTOMER DRAWING

NAME

ASSEMBLY, MOD II DOUBLE ROW,
.100 X .100 C/L, VERTICAL MOUNTED,
CLOSED ENTRY, SHORT PT. CONTACTS

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=534236

RESTRICTED TO
-

SCALE
4:1

SHEET
2 OF 2

REV
V2

FINISH	A	B	NO OF POSN	PART NO.	
5 12	3	1.300	1.200	26	4 534236-1
OBSOLETE	3	4.000	3.900	80	4 534236-0
	3	3.900	3.800	78	3 534236-9
	3	3.800	3.700	76	3 534236-8
	3	3.700	3.600	74	3 534236-7
	3	3.600	3.500	72	3 534236-6
	3	3.500	3.400	70	3 534236-5
	3	3.400	3.300	68	3 534236-4
	3	3.300	3.200	66	3 534236-3
12	3	3.200	3.100	64	3 534236-2
	3	3.100	3.000	62	3 534236-1
OBSOLETE	3	3.000	2.900	60	3 534236-0
	3	2.900	2.800	58	2 534236-9
OBSOLETE	3	2.800	2.700	56	2 534236-8
	3	2.700	2.600	54	2 534236-7
12	3	2.600	2.500	52	2 534236-6
	3	2.500	2.400	50	2 534236-5
12	3	2.400	2.300	48	2 534236-4
	3	2.300	2.200	46	2 534236-3
12	3	2.200	2.100	44	2 534236-2
	3	2.100	2.000	42	2 534236-1
12	3	2.000	1.900	40	2 534236-0
	3	1.900	1.800	38	1 534236-9
12	3	1.800	1.700	36	1 534236-8
	3	1.700	1.600	34	1 534236-7
12	3	1.600	1.500	32	1 534236-6
	3	1.500	1.400	30	1 534236-5
12	3	1.400	1.300	28	1 534236-4
	3	1.300	1.200	26	1 534236-3
12	3	1.200	1.100	24	1 534236-2
	3	1.100	1.000	22	1 534236-1
12	3	1.000	.900	20	1 534236-0
	3	.900	.800	18	534236-9
12	3	.800	.700	16	534236-8
	3	.700	.600	14	534236-7
12	3	.600	.500	12	534236-6
	3	.500	.400	10	5 534236-5
12	3	.400	.300	8	5 534236-4
	3	.300	.200	6	5 534236-3
12	3	.200	.100	4	5 534236-2
	3	.100	-	2	5 534236-1
FINISH	A	B	NO OF POSN	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

MATERIAL

6

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FINISH

3

9

DWN
R. BOLES
19-11-92

CHK
T. KINSEY
19-11-92

APVD
-

PRODUCT SPEC
108-25026

APPLICATION SPEC
114-25018

WEIGHT
-

CUSTOMER DRAWING

NAME

ASSEMBLY, MOD II DOUBLE ROW,
.100 X .100 C/L, VERTICAL MOUNTED,
CLOSED ENTRY, SHORT PT. CONTACTS

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=534236

RESTRICTED TO
-

SCALE
4:1

SHEET
2 OF 2

REV
V2

1471-9 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-534236-2](#)