






- 1 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER PER ASTM D5138 LCP000 G30A 32250, COLOR: NATURAL.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3 CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL.
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA UNCONTROLLED ENVIRONMENT.
ON LEADS
0.0006 MIN TIN-LEAD OVER UNDERPLATE.
LUBRICATION (ENTIRE CONTACT):
SURFACE CONDITIONER PER AMP SPEC 112-1002 AFTER PLATING.
- 4 PART MARKING PER AMP INCORPORATED SPECIFICATION 115-9009, LOCATED APPROXIMATELY AS SHOWN.
- 5 DIMENSION APPLIES WHEN SEATED ON PRINTED CIRCUIT BOARD.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



DETAIL Z
SCALE 20:1

OBSOLETE	4.25	34	17	35.88	3	72	1-536504-2
3	4.25	130	65	131.88	3	264	1-536504-4
OBSOLETE	4.25	106	53	107.88	3	216	1-536504-0
6	4.25	118	59	119.88	3	240	536504-9
OBSOLETE	4.25	70	35	71.88	3	144	536504-8
OBSOLETE	4.25	66	33	67.88	3	136	536504-7
OBSOLETE	4.25	58	29	59.88	3	120	536504-6
6	4.25	82	41	83.88	3	168	536504-5
OBSOLETE	4.25	94	47	95.88	3	192	536504-4
	4.25	46	23	47.88	3	96	536504-3
	4.25	22	11	23.88	3	48	536504-2
OBSOLETE	4.25	10	5	11.88	3	24	536504-1
	D	C	B	A	FINISH	NO OF POSN	PART NUMBER

RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
(COMPONENT SIDE)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
D.R.BENDER
CHK
D.BAECHTLE
APVD

10/27/92
02/18/93

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC $\pm$ -
1 PLC $\pm$ -
2 PLC $\pm$.13
3 PLC $\pm$ -
4 PLC $\pm$ -
ANGLES $\pm$ -

MATERIAL
1

PRODUCT SPEC
APPLICATION SPEC
WEIGHT

SIZE
CAGE CODE
DRAWING NO
A100779

RESTRICTED TO
-

TE Connectivity

PIN ASSEMBLY, SIGNAL MODULE, Z-PACK 2mm FB, 2mm

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 1

REV V

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[536504-4](#)