

# SPECIFICATION CONTROL DRAWING

55A1131

TITLE  
THREE CONDUCTOR CABLE, MODIFIED ETFE  
INSULATED, SHIELDED, JACKETED, LIGHTWEIGHT, 600 VOLT

Date  
25APR11


Revision  
P

This specification sheet forms a part of the latest issue of Raychem Specification 55A.

COMPONENT WIRES - 55A0111

SHIELD - TIN-COATED COPPER

JACKET - RADIATION-CROSSLINKED,  
MODIFIED ETFE



CABLE CONSTRUCTION DETAILS

PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inch)		OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55A1131-30-*	30	38	.006	.008	.085	.090	6.4
55A1131-28-*	28	38	.006	.008	.091	.096	7.6
55A1131-26-*	26	38	.006	.008	.102	.108	9.7
55A1131-24-*	24	38	.006	.008	.113	.119	12.3
55A1131-22-*	22	38	.006	.008	.126	.132	15.9
55A1131-20-*	20	38	.006	.008	.143	.149	21.7
55A1131-18-*	18	38	.006	.008	.165	.172	30.4
55A1131-16-*	16	38	.006	.008	.182	.189	37.4
55A1131-14-*	14	38	.007	.009	.221	.229	54.0
55A1131-12-*	12	38	.007	.009	.260	.270	77.5
55A1131-10-*	10	38	.007	.009	.311	.327	118.

## CABLE RATINGS AND ADDITIONAL REQUIREMENTS

### TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)

ACCELERATED AGING: 300 ± 3°C for 7 hours

BLOCKING: 200 ± 3°C for 6 hours

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

FLAMMABILITY: Procedure 1, 3 seconds (maximum);

3 in. (maximum); no flaming of facial tissue

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in<sup>2</sup> (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms), 60 Hz, 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100% test

LIFE CYCLE: 200 ± 3°C for 168 hours

LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL):

1000 volts (rms), 60 Hz, 1 minute

### PART NUMBER:

The "\*" in the part numbers above shall be replaced by a color code designator with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 20, white, black and red component wires; white jacket: 55A1131-20-9/0/2-9

NOTE: Nominal values are for information only.  
Nominal values are not requirements.

COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-881.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

Page 1 of 1

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

**TE** TE Connectivity

Tyco Electronics Corporation  
Raychem Wire and Cable  
300 Constitution Drive, Menlo Park, California 94025  
1-800-2 Raychem Fax 1-650-381-6297

© 2011 Tyco Electronics Corporation. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55A1131-24-0/2/9-9](#)