

SPECIFICATION SHEET

55A1826

15 March 1983  
Revision A

CABLE, ELECTRIC, RADIATION-CROSSLINKED, EXTRUDED, MODIFIED, FLUOROPOLYMER-INSULATED,  
TWO CONDUCTOR, SHIELDED, JACKETED, NORMAL WEIGHT


200°C

The complete requirements for procuring the cable described herein shall consist of this document and the issue in effect of Raychem Specification 55A.

COMPONENT WIRES - 55A0816

SHIELD - NICKEL-COATED COPPER

JACKET - RADIATION-CROSSLINKED,  
MODIFIED ETFE



PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inches)		OUTSIDE DIAMETER (inches)		MAXIMUM WEIGHT (lb/1000 ft)
			MINIMUM	NOMINAL <sup>1/</sup>	NOMINAL <sup>1/</sup>	MAXIMUM	
			55A1826-26-*	26	38	.006	
55A1826-24-*	24	38	.006	.008	.123	.129	11.4
55A1826-22-*	22	38	.006	.008	.135	.142	14.5
55A1826-20-*	20	38	.006	.008	.151	.159	18.7
55A1826-18-*	18	38	.006	.008	.173	.182	25.3
55A1826-16-*	16	38	.006	.008	.189	.198	30.4

<sup>1/</sup> Nominal values are for information only. Nominal values are not requirements.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)

ACCELERATED AGING: 300 ± 3°C for 7 hours

BLOCKING: 200 ± 3°C for 6 hours

DIELECTRIC WITHSTAND: 1500 volts, 60 Hz

FLAMMABILITY:

Procedure 1, 3 seconds (maximum); 3 in. (maximum);

no flaming of facial tissue

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 psi (minimum)

JACKET FLAWS:

Spark Test, 1000 volts, 60 Hz (rms), 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100% test

LIFE CYCLE: 230 ± 3°C for 500 hours

LOW TEMPERATURE-COLD BEND: -65 ± 3°C for 4 hours

SHIELD COVERAGE: 85% (minimum)

THERMAL SHOCK: 300 ± 3°C for 6 hours

VOLTAGE WITHSTAND TEST: (After Accelerated Aging, Immersion, Life Cycle, Low Temperature-Cold Bend and Thermal Shock) 1000 volts, 60 Hz, 1 minute

PART NUMBER:

The "\*" in the part numbers above shall be replaced by color code designators in accordance with MIL-STD-681 with a slash separating component wire colors and a dash separating the component wire colors from the jacket color.

Example:

AWG 20, white and black component wires;

white jacket: 55A1826-20-9/0-9.

**Raychem**

Raychem Corporation  
300 Constitution Drive, Menlo Park, California 94025  
4151 361 3333 TWX 910 373 1205

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55A1826-24-9/96-9CS2275](#) [55A1826-20-9/96-9CS2275](#) [55A1826-24-6/9-9CS2275](#)