

# SPECIFICATION CONTROL DRAWING

SCD

55A4122

Title

TWO CONDUCTOR CABLE, JACKETED, GENERAL PURPOSE, 600 VOLT

Date

12-8-15

Revision

D

This specification sheet forms a part of the latest issue of Raychem Specification 55A.

COMPONENT WIRES - 55A0112

JACKET - RADIATION-CROSSLINKED,  
MODIFIED ETFE



## CABLE CONSTRUCTION DETAILS

PART NUMBER 1/	CONDUCTOR SIZE (AWG)	JACKET THICKNESS (inch)		OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)
		MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55A4122-30-*	30	.006	.008	.064	.069	2.6
55A4122-28-*	28	.006	.008	.070	.075	3.3
55A4122-26-*	26	.006	.008	.080	.085	4.5
55A4122-24-*	24	.006	.008	.090	.095	5.9
55A4122-22-*	22	.006	.008	.102	.107	7.8
55A4122-20-*	20	.006	.008	.116	.122	11.2
55A4122-18-*	18	.006	.008	.136	.143	16.1
55A4122-16-*	16	.006	.008	.152	.160	20.1
55A4122-14-*	14	.006	.008	.186	.195	30.5
55A4122-12-*	12	.007	.009	.224	.235	45.6
55A4122-10-*	10	.007	.009	.274	.288	72.6
55A4122-8-*	8	.008	.010	.396	.416	134.

## CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

ACCELERATED AGING: 300 ± 3°C for 7 hours

BLOCKING: 200 ± 3°C for 6 hours

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

FLAMMABILITY (Procedure 1):

3 seconds (maximum); 3 inches (maximum);

no flaming of facial tissue

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in<sup>2</sup> (minimum)

LIFE CYCLE: 230 ± 3°C for 500 hours

LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

### 1/ PART NUMBER:

The "\*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 20, black and brown component wires;  
white jacket: 55A4122-20-0/1-9

NOTE: Nominal values are for information only. Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.

Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Page 1 of 1

Raychem, TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks.

DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.  
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



**Raychem Wire & Cable**  
501 Oakside Avenue  
Redwood City, CA 94063-3800  
Phone: 1-800-227-8816  
Fax: 1-650-361-6297

© 2008-2015 Tyco Electronics Corporation. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## TE Connectivity:

[55A4122-16-9/96-9CS2275](#) [55A4122-24-6/69-9](#) [55A4122-20-2/29-9](#) [55A4122-24-0/9-9](#) [55A4122-20-9/96-9CS2275](#)  
[55A4122-22-9/96-9CS2275](#) [55A4122-14-2/9-9](#) [55A4122-16-2/9-9](#) [55A4122-22-6/9-9CS2275](#) [55A4122-20-2/9-9](#)  
[55A4122-22-2/9-9](#) [55A4122-22-5/59-9](#)