



TRA6927M3

4G/3G Multiband Phantom® Antenna

698-960 MHz/1700-2700 MHz

The unique Phantom® antenna operates simultaneously in the 698-960 MHz and 1700- 2700 MHz bands, making it ideal for 4G/3G applications. The mechanically robust design is suitable for both indoor and outdoor applications with wide bandwidth and a low angle radiation pattern that is superior to traditional gain antennas in most applications. The antenna is ideal for both ceiling and surface mount applications.

The industry standard NMO mounting socket mates with all TE Connectivity's magnetic, trunk lid and hole mount configurations. A threaded permanent stud mount model is also available for vandal resistant mounting on brackets, panels, ceilings or any other kind of housing.

FEATURES AND BENEFITS

- Mechanically robust for both indoor and outdoor applications
- Applicable for both 3G and 4G application
- Domestic LTE 700 band and Global LTE 2600 band
- WiMAX 2300/2500/2600 bands
- Domestic Cellular and Global GSM
- Phantom out-performs a 3-dBi whip in many applications

| ELECTRICAL SPECIFICATIONS | | | | | |
|------------------------------|----------------------------|-------------|---------------|----------------|----------------|
| Operating Frequency (MHz) | 698-960, 1710-2700 | | | | |
| VSWR | 698-806 MHz | 806-960 MHz | 1710-2110 MHz | 2110- 2170 MHz | 2300- 2700 MHz |
| | < 2.5: 1.0 | < 2.0: 1.0 | < 2.0: 1.0 | < 2.5: 1.0 | < 2.0: 1.0 |
| Peak Gain (dBi) | 698-960 MHz | | 1710-1990 MHz | 2100-2700 MHz | |
| | 3.5 | | 5.5 | 4.6 | |
| Efficiency (%) | 698-960 MHz | | 1710-1990 MHz | 2100-2700 MHz | |
| | 90 (max: 96) | | 91 (max: 95) | 80 (max: 86) | |
| Nominal Impedance (Ohms) | 50 | | | | |
| Max Power - Ambient 25°C (W) | 100 | | | | |
| Polarization | Vertical | | | | |
| Terminations | NMO or P-Mount w/Type N(f) | | | | |

MECHANICAL SPECIFICATIONS

| | |
|--|--------------------------|
| Dimensions - diameter x height - cm (inches) | 3.65 x 8.38 (1.44 x 3.3) |
| Color | Black or white available |
| Cable and Mount | MB195 (sold separately) |
| Radome Material | SABIC Lexan |

ENVIRONMENTAL SPECIFICATIONS

| | |
|---|------------------------------|
| Operating Environment (Indoor or Outdoor) | Indoor and Outdoor |
| Operating Temperature - °C (°F) | -40 to +85°C (-40 to +185°F) |
| Material Substance Compliance | RoHS |
| Ingress Protection Rating | IP67 |

MODEL AND ORDERING INFORMATION

| MODEL | DESCRIPTION | COLOR RADOME | HEIGHT | WEIGHT CONNEC-TOR |
|------------------------------|----------------|--------------|--------|--------------------|
| TRA6927M3PB-001 | 4G/3G Phantom* | Black | 3.30" | 0.31 lbs Type N(f) |
| TRA6927M3NB-001 | 4G/3G Phantom* | Black | 3.30" | 0.28 lbs NMO |
| TRA6927M3PW-001 | 4G/3G Phantom* | White | 3.30" | 0.31 lbs Type N(f) |
| TRA6927M3NW-001 | 4G/3G Phantom* | White | 3.30" | 0.28 lbs NMO |
| TRA6927M3PB-002 ¹ | 4G/3G Phantom* | Black | 3.30" | 0.38 lbs Type N(f) |
| TRA6927M3PW-002 ¹ | 4G/3G Phantom* | White | 3.30" | 0.38 lbs Type N(f) |
| TRA6927M3PB-003 ² | 4G/3G Phantom* | Black | 3.30" | 0.31 lbs Type N(f) |


Permanent Mounting Option:

The letter P in the above part numbers indicates a permanent mounting option.


¹ Extended Connector 23 mm maximum plate thickness.

² No logo option.


RADIATION PATTERN




750 MHz




849 MHz




960 MHz



1710 MHz



1950 MHz



2700 MHz

TE TECHNICAL SUPPORT CENTER

| | |
|-------------------|-----------------------|
| USA: | +1 (800) 522-6752 |
| Canada: | +1 (905) 475-6222 |
| Mexico: | +52 (0) 55-1106-0800 |
| Latin/S. America: | +54 (0) 11-4733-2200 |
| Germany: | +49 (0) 6251-133-1999 |
| UK: | +44 (0) 800-267666 |
| France: | +33 (0) 1-3420-8686 |
| Netherlands: | +31 (0) 73-6246-999 |
| China: | +86 (0) 400-820-6015 |

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, complete, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE EXPRESSLY DISCLAIMS ALL IMPLIED WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. In no event will TE be liable for any direct, indirect, incidental, special or consequential damages arising from or related to recipient's use of the information. It is the sole responsibility of recipient of this information to verify the results of this information using their engineering and product environment. Recipient assumes any and all risks associated with the use of the information. Antenna performance may vary. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements.

©2025 TE Connectivity. All Rights Reserved.

05/25 Original

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TRA6927M3NW-001](#)