



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Cavity Plug**
Primary Product Material: **PBT GF**
Primary Product Color: **Natural**
Operating Temperature (Max): **125 °C [257 °F]**
Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**

Features

Product Type Features

Connector Seal & Plug Type	Cavity Plug
----------------------------	-------------

Body Features

Primary Product Material	PBT GF
Primary Product Color	Natural

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Packaging Features

Packaging Method	Box
Packaging Quantity	10000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


TE Part # CAT-N58-ATHA68
68POS,HYBRID,REC and TAB HSG ASSY

Also in the Series | Generation Y Connector System

Automotive Connector Caps & Covers (19)	Automotive Headers(14)	Automotive Housings(140)	Automotive Terminals(43)



Connector Seals & Cavity Plugs(6)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(14)



Rectangular Power Connectors(2)



Wire-to-Board Headers & Receptacles (13)

Customers Also Bought



TE Part #2378797-1
Shield, 26P GenY, Hand Mate Conn



TE Part #2098634-1
Carrier, 20P, GY LAC, Black



TE Part #2351963-2
46POS, HYBRID, REC HSG ASSY, SLD, COD A



TE Part #2-1355132-1
COVER 94POS



TE Part #CAT-G3353-CH8172
GET .64 CONNECTOR SYSTEM, CONNECTOR HSG



TE Part #CAT-A11-T273
1.5/2.8 CONNECTOR SYSTEM, RECPT AND TAB



TE Part #2288276-1
Assy, Plug, USCAR, GenY, 20p, Key A, No CPA



TE Part #2377194-1
CVTY PLUG, 0.64 GENER. Y, CVTY DIA, MAT-SL

Documents

Product Drawings
CVTY PLUG, MATE-AX, CVTY DIA, MAT-SL

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2377195-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2377195-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2377195-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2377195-1](#)