

# SPECIFICATION CONTROL DRAWING

**55A7238**


TITLE THREE CONDUCTOR CABLE, SHIELDED, JACKETED,  
GENERAL PURPOSE, 600 VOLT

Date 4-8-06

Revision A

This specification sheet forms a part of the latest issue of Raychem Specification 55A.

COMPONENT WIRES - 55A0213      SHIELD - TIN-COATED COPPER      JACKET - RADIATION-CROSSLINKED,  
MODIFIED ETFE



FILAMENT STRIPPING THREAD - NOMEX®, 200/1/4E, No finish

### CABLE CONSTRUCTION DETAILS

PART NUMBER <sup>1/</sup>	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inches)		OUTSIDE DIAMETER (inches)		MAXIMUM WEIGHT (lb/1000 ft.)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55A7238-22-*	22	38	.006	.008	.135	.142	17.4
55A7238-20-*	20	38	.006	.008	.152	.160	23.5
55A7238-18-*	18	38	.006	.008	.176	.185	32.5
55A7238-16-*	16	38	.006	.008	.191	.201	39.0
55A7238-14-*	14	38	.007	.009	.225	.236	56.5
55A7238-12-*	12	38	.007	.009	.264	.277	81.0

### CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature  
VOLTAGE RATING: 600 volts (rms) at sea level  
ACCELERATED AGING: 300 ± 3°C for 7 hours

BLOCKING: 200 ± 3°C for 6 hours  
DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

FLAMMABILITY:

Procedure 1, 3 seconds (maximum); 3 in. (maximum);  
no flaming of facial tissue

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)  
Tensile Strength, 5000 lbf/in<sup>2</sup> (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms)  
Impulse Dielectric Test, 6.0 kV (peak)

LIFE CYCLE: 200 ± 3°C for 168 hours

LOW TEMPERATURE-COLD BEND: -65 ± 3°C for 4 hours

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST: (POST ENVIRONMENTAL)  
1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "\*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wires color from the jacket color. Colors shown do not necessarily reflect the sequence of manufacturing.

Example: AWG 20, black, brown and red component wires;  
white jacket: 55A7238-20-0/1/2-9

NOTE: Nominal values are for information only.  
Nominal values are not requirements.

NOMEX® is a registered trademark of E.I. du Pont de Nemours and Company.

*Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.*

<sup>1/</sup> COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.  
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

**tyco**  
Electronics

**Raychem** Wire & Cable  
501 Oakside Avenue  
Redwood City, CA 94063-3800  
Phone: 1-800-227-8816  
Fax: 1-650-361-6297

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## TE Connectivity:

[55A7238-12-3/6/9-9CS2627](#) [55A7238-14-3/6/9-9CS2627](#) [55A7238-18-3/6/9-9CS2627](#) [55A7238-20-3/6/9-9CS2627](#)  
[55A7238-22-3/6/9-9CS2627](#)