

# SPECIFICATION CONTROL DRAWING

55PC1816

TITLE


ONE CONDUCTOR CABLE, SHIELDED, JACKETED, 600 VOLT

Date

4-18-95

Revision

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.



## CONSTRUCTION DETAILS

PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
			LOWER SPEC LIMIT	TARGET WALL	LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC1816-24-*	24	38	.0050	.0060	.069	.073	.077	5.74	6.04
55PC1816-22-*	22	38	.0050	.0060	.075	.079	.083	7.07	7.40
55PC1816-20-*	20	38	.0050	.0060	.084	.087	.091	9.14	9.49
55PC1816-18-*	18	38	.0050	.0060	.094	.097	.101	12.06	12.51
55PC1816-16-*	16	38	.0050	.0060	.102	.105	.109	14.44	14.92

## CABLE RATINGS AND ADDITIONAL REQUIREMENTS

### TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)

CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in<sup>2</sup> (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms), 60 Hz, 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100 % test

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL):

1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "\*" in the part numbers above shall be replaced by a color code designator with a dash separating the component wire color from the jacket color.

Example: AWG 22, white component wire;

white jacket: 55PC1816-22-9-9

COLOR AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-881.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HERIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF IMPLEMENTATION FOR BID.

**Raychem**

Raychem Corporation  
300 Constitution Drive, Menlo Park, California 94025  
1-800-2-Raychem Fax: 1-415-361-6297

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55PC1816-24-9-9CS3332](#) [55PC1816-22-9-9CS3332](#)