

## HDMI over Cat5/6 Extender Kit, Transmitter/Receiver for Video/Audio, USB Powered, Up to 125 ft. (38 m), TAA

MODEL NUMBER: B126-1A1-U



Transmitter and receiver work in tandem to extend an HDMI audio/video signal via Cat5e/6 cable to an HDMI display up to 125 ft. Ideal for digital signs, schools, retail settings and trade show presentations.

### Description

The B126-1A1-U HDMI over Cat5/Cat6 Active Extender Kit includes a transmitter unit and a receiver unit that work in tandem to extend an HDMI audio/video signal to an HDMI projector, monitor or television. The kit is ideal for digital signs, trade shows, presentations, classrooms, churches, retail settings and other applications where the video source is located farther than conventional cables allow. A latching HDMI connector on the built-in cable provides a more secure connection

The transmitter's built-in HDMI cable connects to the audio/video source, and the receiver's built-in HDMI cable connects to the display. Cat5e/6 cable connects the two units (for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series). Each unit is powered by an included USB Micro-B to USB-A cable, which must be connected between the unit and a USB port on the source device, display or USB wall charger. You can also connect an optional HDMI monitor to the transmitter's local port with a user-supplied HDMI cable, such as Tripp Lite's P568-Series.

The B126-1A1-U can extend a 1080p (@ 60 Hz) signal up to 125-ft. (38.1 m) with full, rich stereo. Built-in RJ45 LEDs indicate the units are receiving power and a signal from the source. Built-in equalization control lets you fine-tune the image quality at each remote display. Easy to set up with no software or drivers to install. Works with all operating systems and HDMI sources.

### Features

#### Extends HDMI Audio/Video Signals to an HDMI Display

- Extends a 1080p (@ 60 Hz) signal up to 125-ft. (38.1 m)
- Ideal for digital signs, trade shows, presentations, classrooms, churches and retail settings

### Highlights

- Supports high-definition video resolutions up to 1080p (@ 60 Hz)
- Supports stereo audio and HDCP
- Works with all operating systems and HDMI sources
- Built-in cable includes latching HDMI connector for a more secure connection
- Plug and play—no software, drivers or external power supply
- Built-in equalization control lets you adjust monitor image

### System Requirements

- Computer, Blu-ray™ player or other source with HDMI port
- Display with HDMI port

### Package Includes

- Transmitter unit
- Receiver unit
- (2) USB Micro-B to USB-A cables, 3-ft. (0.91 m)
- Screwdriver for adjusting equalization
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

- Transmitter and receiver connect with one Cat5e/6 cable (for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series)
- Supports stereo audio and HDCP
- Built-in equalization control lets you adjust the image on the remote display

#### Easy to Set Up and Use

- Plug-and-play engineering—no software, drivers or external power supply
- Powered via included USB cables
- Units connect quickly to source and display with built-in HDMI cables
- Built-in cable includes latching HDMI connector for a more secure connection
- Optional local HDMI monitor connects to transmitter with user-supplied HDMI cable
- LEDs indicate when units are receiving power and a signal from the source
- Works with all operating systems and HDMI sources

#### TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332190260
Product Type	Extender Kit
Technology	HDMI; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1920x1080 (1080p @ 60Hz)
Max 1280 x 720 (720p) Range (ft)	125
Max 1920 x 1080 (1080p) Range (ft)	125
Transmitter Video Input	HDMI
Transmitter - Number of Video Outputs	1
Transmitter - Local Display Output	HDMI
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Range Extension using other Tripp Lite product	175ft @ 1080i 125ft @ 1080p
Recommended Cabling	N202-Series Cat6 Patch Cable
Other Tripp Lite product used to extend range	B126-110



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
Maximum Signal Range (ft)	125
Maximum Signal Range (m)	38
<b>AUDIO</b>	
Audio Input	HDMI
Audio Output	HDMI
Audio Specification	Stereo Audio
<b>INPUT</b>	
Product Length (in.)	8.4
<b>POWER</b>	
Power Source	Transmitter and Receiver (Included)
Power Source Type	USB
Power Over Cable (PoC) Support	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	TX & RX: Green (Power), Orange (Activity)
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Polycarbonate
Number of Displays	1
Form Factor/Mounting Options	Pigtail
Rackmountable	No
Receiver Unit Dimensions (hwd / cm.)	2.4 x 6.1 x 5.2
Receiver Unit Dimensions (hwd / in.)	0.9 x 2.4 x 2
Receiver Unit Weight (kg)	0.07
Receiver Unit Weight (lbs.)	0.15
Shipping Dimensions (hwd / cm)	4.32 x 19.81 x 14.22
Shipping Dimensions (hwd / in.)	1.70 x 7.80 x 5.60
Shipping Weight (kg)	0.23
Shipping Weight (lbs.)	0.50



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Transmitter Unit Dimensions (hwd / cm.)	2.4 x 6.1 x 5.2
Transmitter Unit Dimensions (hwd / in.)	0.9 x 2.4 x 2
Transmitter Unit Weight (kg)	0.07
Transmitter Unit Weight (lbs.)	0.15
Unit Packaging Type	Box
Housing	Plastic
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104 °F (0 to 40 °C)
Storage Temperature Range	5 to 122 °F (-15 to 50 °C)
Relative Humidity	0% to 85%, Non-Condensing
<b>COMMUNICATIONS</b>	
Signal Range (ft.)	125
Signal Range (m)	38
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
<b>CONNECTIONS</b>	
Side A - Connector 1	HDMI (MALE)
Side A - Connector 2	MICRO-USB B (FEMALE); RJ45 (FEMALE)
Side A - Connector 3	HDMI (FEMALE)
Side B - Connector 1	HDMI (MALE)
Side B - Connector 2	MICRO-USB B (FEMALE); RJ45 (FEMALE)
Connector Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	1.4
Driver Required	No
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
Built-In Equalizer	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B126-1A1-U](#)