






WIRE CRIMP				TERMINAL CRIMP HEIGHT	
CRIMP SYMBOL	DIM	GO	NO GO		
A	F	.0273	.0303	.031	.028
	D	.0361	.0382		
B	F	.0403	.0443	.0465	.0425
	D	.0496	.0528		




INSULATION CRIMP			
CRIMP SYMBOL	DIM	GO	NO GO
A	O	.0610	.0690
B	O	.0790	.0870




INSULATION CRIMP



WIRE CRIMP CRIMP SYMBOL A



WIRE CRIMP CRIMP SYMBOL B



SIDE VIEW OF GAGE



DOUBLE END HANDLE A.G.D. STD.

SUGGESTED GAGE DESIGN

1. CRIMP GAGE DIMENSIONS APPLY WHEN TOOL IS CLOSED OR BOTTOMED BUT NOT UNDER PRESSURE.
2. FOR REPLACEMENT OF PARTS SUCH AS PINS AND SNAP RINGS, ORDER REPAIR KIT NO. 125218-1.
3. FOR REPLACEMENT OF PARTS OTHER THAN PINS AND SNAP RINGS, TOOL IS TO BE RETURNED TO AMP INC. HARRISBURG, PENNA. TO INSURE PROPER CRIMP ADJUSTMENT.
4. FOR TOOL USAGE, SEE INSTRUCTION SHEET NO. 15-1778.
5. HAND TOOL TO BE CHECKED BY MEASURING TERMINAL CRIMP HEIGHT.
6. FOR REPLACEMENT OF HANDLE SPRING ORDER PART NO. 125416-1.

ENLARGED END VIEWS OF GAGES

REV	DESCRIPTION	DATE
A-1	LOC M WAS R	11-4-71
A	REVISED	11-4-71

REV	DESCRIPTION	DATE
1	REQUIRED PER ASSEMBLY	
2		
3		
4		
5		
6		
7		
8		
9		
10		

DWG SIZE	NUMBER	NAME	REMARKS	ITEM NO
19	59528	59528		
BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.				
DR	CHK	DE	APP	
59528	59528	59528	59528	
MATERIAL AND FINISH		CLASS		
11		11		
WIRE RANGE		TYPE		
11		11		
TOLERANCE EXCEPT AS NOTED		SCALE		
11		11		
NAME		LOC		
59528		59528		
STRAIGHT ACTION HAND TOOL				

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[59528](#)