

## DisplayPort to DVI over Cat5/6 Active Extender Kit, Pigtail Transmitter/Receiver for Video/Audio, 125 ft. (38 m)

MODEL NUMBER: **B150-1A1-DVI**



Transmitter and receiver work in tandem to convert a DisplayPort signal to DVI and extend it via Cat5e/6 cable to a projector, monitor or television up to 125 ft. away. Ideal for digital signs, schools and trade shows.

### Description

The B150-1A1-DVI DisplayPort to DVI over Cat5/6 Active Extender Kit includes a transmitter unit and a receiver unit that work in tandem to convert a DisplayPort audio/video signal to DVI and then extend it to a projector, monitor or television up to 125-ft. (38.1 m) away. The kit is ideal for digital signs, trade shows, presentations, classrooms, churches, retail settings and other applications where the video source is located farther than convention cables allow.

One Cat5e/6 cable connects the transmitter and receiver (for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series). A built-in DisplayPort plug connects the transmitter to the source, while a built-in DVI-D single-link plug connects the receiver to the display. Included USB Micro-B cables supply power to the units via USB ports on the source and display or USB wall chargers.

Please note: In order to properly power the unit via an external source, a minimum of 500mA will be needed. Any type of power supply will work as well as any standard USB port that is USB 2.0 or newer. The B150-1A1-DVI can extend a high-definition 1920 x 1080 (60 Hz) signal up to 125-ft. (38.1 m). In addition to crystal-clear video, including 24-bit True Color (8 bits per channel), the kit delivers full, rich stereo. LEDs on the RJ45 ports indicate when the units are receiving power and a DVI signal from the source. Built-in equalization control lets you fine-tune the image on the DVI display. Easy to set up with no software or drivers to install. Compatible with all operating systems. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Features

#### Converts DisplayPort Signal to DVI, Extends It Up to 125-ft. (38.1 m)

- Ideal for digital signs, trade shows, presentations, classrooms, churches and retail settings
- Extends a high-definition 1920 x 1080 (60 Hz) signal up to 125-ft. (38.1 m)
- Transmitter and receiver connect with one Cat5e/6 cable (for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series)
- Supports 24-bit True Color (8 bits per channel) and stereo audio
- Built-in equalization control lets you adjust the image on the display

### Highlights

- Supports high-definition video resolutions up to 1920 x 1080 (60 Hz)
- Supports 24-bit True Color (8 bits per channel) and stereo audio
- Included USB Micro-B cables supply power to both units
- Works with all operating systems
- Plug and play—no software or drivers to install
- HDCP 1.3 compliant

### System Requirements

- Computer with DisplayPort output port\*
- Display with DVI-D input port

### Package Includes

- Transmitter unit
- Receiver unit
- Screwdriver for adjusting equalization
- (2) USB Micro-B cables, 3-ft. (0.91 m)
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

- HDCP 1.3 compliant

#### Easy to Set Up and Use

- Plug-and-play engineering—no software or drivers to download and install
- Works with all operating systems
- Built-in cables connect transmitter to DisplayPort source and receiver to DVI-D display
- Included USB Micro-B cables provide power to the units
- LEDs indicate when the units are receiving power and sharing a signal

#### TAA Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332191311
Product Type	Extender Kit
Technology	DVI; DisplayPort; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1920x1080 (1080p @ 60Hz)
Max 720P Range (ft)	150
Max 1080P Range (ft)	125
Max 1280 x 720 (720p) Range (ft)	125
Max 1920 x 1080 (1080p) Range (ft)	125
Transmitter Video Input	DisplayPort
Transmitter - Number of Video Outputs	1
Receiver/Transceiver Video Output	DVI-D (Single Link)
Receiver - Number of Video Outputs	1
Recommended Cabling	Solid Wire Cat6 Cables (Tripp Lite's N202-Series)
HDR Support	No
3D Video Supported	Yes
Maximum Signal Range (ft)	125
Maximum Signal Range (m)	38
AUDIO	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Audio Input	Displayport
<b>POWER</b>	
Power Source	Transmitter and Receiver (Included)
Power Source Type	USB
Power Over Cable (PoC) Support	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	TX & RX: (x1) Green (Connection), (x1) Orange (Data transmission)
<b>PHYSICAL</b>	
Color	Black
Number of Displays	1
Form Factor/Mounting Options	Pigtail
Receiver Unit Dimensions (hwd / in.)	2.4 x 0.94 x 2.04
Receiver Unit Weight (lbs.)	0.07
Shipping Dimensions (hwd / cm)	4.39 x 19.99 x 15.11
Shipping Dimensions (hwd / in.)	1.73 x 7.87 x 5.95
Shipping Weight (kg)	0.22
Shipping Weight (lbs.)	0.49
Transmitter Unit Dimensions (hwd / in.)	2.42 x 1 x 3
Transmitter Unit Weight (lbs.)	0.07
Unit Packaging Type	Box
Housing	Plastic
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 122 °F (0 to 50 °C)
Storage Temperature Range	-40 to 158 °F (-40 to 70 °C)
Relative Humidity	0% to 85%, Non-Condensing
<b>COMMUNICATIONS</b>	
Max 1024 x 768 Range (ft)	150
Max 480P Range (ft)	150
Max 1440 x 900 Range (ft)	150
Max 1080i Range (ft)	150
Max 480i Range (ft)	150
Max 640 x 480 Range (ft)	150



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Max 800 x 600 Range (ft)	150
Max 1600 x 1200 Range (ft)	150
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	DISPLAYPORT (MALE)
Side A - Connector 2	RJ45 (FEMALE)
Side A - Connector 3	MICRO-USB B (FEMALE)
Side B - Connector 1	DVI-D SINGLE LINK (MALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	MICRO-USB B (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
Displayport Specification	1.2
Driver Required	No
Built-In Equalizer	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, REACH, RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B150-1A1-DVI](#)