

Swivel/Tilt Wall Mount with Screen Adjustment for 13" to 27" TVs and Monitors

MODEL NUMBER: DWM1327SP



Hangs a flat-panel television, monitor or other display on the wall. Ideal for home, office, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

Description

The VESA-compliant DWM1327SP Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home, office, hotels, bars and restaurants, it fits most flat-panel displays from 13 to 27 inches.

The full-motion swivel arm can be independently adjusted for angle and height to give you maximum flexibility in positioning your display to fit your environment and comfort level. A 180° swivel, -15° to +15° tilt and -2° to +2° screen level adjustment capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with soft rubber-feel finish supports up to 33 lbs (14.9 kgs). Comes fully assembled for quick mounting to the wall with included hardware. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm and 100 x 100 mm.

Features

Mounts Your TV or Monitor to the Wall Fits most flat-panel televisions, monitors and other displays from 13 to 27 in. Ideal for home, office, hotels, bars and restaurants Full-motion swivel arm adjusts independently for angle and height Mounting hardware included

Convenient One-Touch Adjustment 180° swivel, -15° to +15° tilt and -2° to +2° screen level adjustment capability provides comfortable viewing from multiple angles

Durable Metal Construction Supports up to 33 lbs (14.9 kgs) Soft rubber-feel finish with decorative covers blends with any décor Fully assembled for immediate installation Display cable attaches to mount to reduce clutter

VESA Compliance Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm

Highlights

- Fits most flat-panel displays from 13 to 27 in.
- One-touch adjustment for comfortable viewing
- 180° swivel, -15° to +15° tilt and -2° to +2° screen adjustment
- Supports up to 33 lbs (14.9 kgs)

Package Includes

- DWM1327SP Swivel/Tilt Wall Mount for 13" to 27" TVs and Monitors
- (4) M4 screws
- (4) M5 screws
- (4) Washers
- (3) Anchor bolts
- (3) Concrete anchors
- Wrench
- Hex key, 4 mm
- Hex key, 6 mm
- Owner's manual

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332183538
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black; Silver
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Degrees of Motion	-15/+15 Tilt; 180 Swivel; -2/+2 Level Adjustment
Material of Construction	Steel
Maximum Screen Size (cm)	68.58
Maximum Screen Size (in.)	27
Maximum Weight Capacity (kg)	15
Maximum Weight Capacity (lbs.)	33
Min/Max Arm Extension (cm)	5.49 - 58.04
Min/Max Arm Extension (in.)	2.16 - 22.85
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Motion	Full
Mounting Location	Wall
Number of Displays	1
Shipping Dimensions (hwd / cm)	8.99 x 40.00 x 50.01
Shipping Dimensions (hwd / in.)	3.54 x 15.75 x 19.69
Shipping Weight (kg)	3.92
Shipping Weight (lbs.)	8.64
Unit Dimensions (hwd / cm)	19 x 47.5 x 13.2
Unit Dimensions (hwd / in.)	7.48 x 18.69 x 5.20
Unit Weight (kg)	3.92
Unit Weight (lbs.)	8.64
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
SPECIAL FEATURES	
Cord Management	No
Security Lock	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

STANDARDS & COMPLIANCE	
Approvals	RoHS3, REACH
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[DWM1327SP](#)