


Sleeve Holds 1 High-Density Copper/Fiber Cassette, 0U

MODEL NUMBER: **N484-00U**



Description

Tripp Lite's N484-00U is a compact, 0U chassis that allows you to mount a single High Density Copper / Fiber Cassette on the metal surface of any rack enclosure, cable manager, or other similar structure via the attached magnets. Unlike standard rackmount solutions, the N484-00U allows you to locate a copper / fiber cassette where standard chassis' cannot go, connecting cables at the cable manager where they are being routed through. It's also perfect for adding copper / fiber connectivity where no existing rack infrastructure exists, such as a remote work station, a new build-out, or temporary install locations. Choose amongst a wide array of cassettes ranging from LC and MTP fiber to RJ45 copper. Fiber cassettes come in multiple variations, allowing you to connect and interconnect your 10Gb, 40Gb, and 100/120Gb equipment. In addition, it gives you the flexibility to add as you go, without needing to purchase a 1U chassis when you only need to add one more cassette.

Features

- Space Saving 0U design allows a Copper / Fiber Cassette to be mounted on the metal surface of any rack enclosure, cable manager or other similar structure via the attached magnets
- Unlike standard rackmount solutions, the N484-00U allows you to locate a copper / fiber cassette where standard chassis' cannot go, connecting cables at the cable manager where they are being routed through.
- It's also perfect for adding Copper / Fiber connectivity where no existing rack infrastructure exists, such as a remote work station, a new build-out, or temporary install locations
- Choose amongst a wide array of cassettes ranging from LC and MTP fiber to RJ45 copper, all in a single 0U sleeve
- Fiber cassettes allow for the connection and interconnection of 10Gb, 40Gb, and 100/120Gb equipment
- Gives you the flexibility to add as you go, without needing to purchase a 1U chassis when you only need to add one more cassette.

Highlights

- Space Saving 0U design allows a Copper / Fiber Cassette to be mounted on the metal surface of any rack enclosure, cable manager or other similar structure via the attached magnets
- Perfect for adding Copper / Fiber connectivity where no existing rack infrastructure exists, such as a remote work station, a new build-out, or temporary install locations
- Choose amongst a wide array of cassettes ranging from LC and MTP fiber to RJ45 copper, all in a single 0U sleeve
- Fiber cassettes allow for the connection and interconnection of 10Gb, 40Gb, and 100/120Gb equipment

Package Includes

- High Density Copper / Fiber Enclosure Panel, 0U, 1-Cassette Capacity



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Fully passive; no added heat or cooling load
- Manufactured with heavy duty, 1.0mm Cold Rolled Steel

Specifications

OVERVIEW	
UPC Code	037332187253
Technology	Cat5/5e; Cat6; Cat6a; Multimode; MTP/MPO
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	6.60 x 12.19 x 23.11
Shipping Dimensions (hwd / in.)	2.60 x 4.80 x 9.10
Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.80
Unit Dimensions (hwd / in.)	1.5 x 4.4 x 7.3
ENVIRONMENTAL	
Operating Temperature Range	-4 to 122 F (-20 to 50 C)
STANDARDS & COMPLIANCE	
Approvals	RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N484-00U](#)