

Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 2 ft. (0.61 m), White

MODEL NUMBER: **P018-002-AWH**



Heavy-duty C14 to C15 power cord connects a PoE network switch or other device with a C16 power inlet to a PDU or UPS system.

Features

C15 to C14 Power Cord for Network Devices That Require a Heavy-Gauge Connection This 250V C15 to C14 cable features 14 AWG wire suitable for high power connections, making it reliable for large server applications that require a higher-rated, heavier-gauge cable. The C15 connector is designed for higher-temperature devices, such as electric kettles, PoE (Power over Ethernet) switches with high-wattage power supplies, and similar network components. This IEC C14 to IEC C15 cord can also replace or upgrade the standard power cord provided by the device's manufacturer. The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This C15 to C14 power cable features a white SJT jacket and fully molded white ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

Highlights

- Recommended for powering PoE switches with high-wattage power supplies
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- C14 to C15 power cable replaces or upgrades original manufacturer's power cord
- Color-coded white for fast, easy identification in a crowded rack or workstation
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like high-wattage PoE switches to a PDU up to 2-ft. (0.61 m) away in your data center
- Update or replace the standard power cord provided by a device's original manufacturer
- Extend an existing power connection by 2-ft. (0.61 m)

Package Includes

- P018-002-AWH IEC C14 to IEC C15 Power Cable, 2-ft. (0.61 m), White

Specifications

OVERVIEW	
UPC Code	037332199096
Device Compatibility	Network Switch; UPS; PDU



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	250
PHYSICAL	
Color	White
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	2
Cable Length (m)	0.6
Cable Length (in.)	24
Cable Length (cm)	60.96
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.15 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.90 x 7.00 x 0.50
Shipping Weight (kg)	0.15
Shipping Weight (lbs.)	0.33
ENVIRONMENTAL	
Operating Temperature Range	-4 F to 221 F (-20 TO 105 C)
Storage Temperature Range	-4 F to 221 F (-20 TO 105 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C15
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P018-002-AWH](#)