


5.8kW Single-Phase Switched Automatic Transfer Switch PDU, Two 200-240V L6-30P Inputs, 16-C13 2-C19 & 1 L6-30R Outlet, 2U, TAA

MODEL NUMBER: PDUMH30HVATNET



Features

- 200-240V 30A Automatic Transfer Switch (ATS) / Switched PDU (Agency de-rated to 24A continuous)
- ATS features provide redundant power for critical network equipment with a single input power cord
- 2 digit display reports output power consumption in amps
- 2U horizontal rackmount form factor; 12.5 in. / 31.8 cm depth
- 19 built-in switched outlets (16 C13, 2 C19 & 1 L6-30R)
- Set of Plug-lock output power cable retention sleeves prevent accidental disconnection of connected devices
- Set of two 10-ft. / (3.05 m) NEMA L6-30P input cables support connection to separate PRIMARY and SECONDARY inputs
- ATS circuits normally maintain output sourced from the primary input cable; As primary input power fails or becomes unstable, the ATS will switch to maintain output sourced from the secondary input cable until power on the primary input is restored and stable
- ATS configurations enable fault-tolerant, hot-swappable UPS protection when used with a single UPS and fully redundant UPS protection when each cord is connected to a separate UPS system (in a two-UPS environment, the primary input cable must be supported by an online UPS with zero transfer time similar to Tripp Lite SmartOnline series)
- Advanced ATS configurations utilizing separate mains circuits, backup generators and even separate out of phase utility power grid feeds are fully supported
- On-board ATS processor constantly evaluates power quality on both inputs to prevent transfer to the secondary source when unavailable or of lower quality than the primary source
- Super-fast switch-over between primary and secondary power sources occurs in 2-6 milliseconds

Highlights

- Single phase 24A 200-240V Auto Transfer Switch / ATS PDU with Solid State Switching
- Separate primary & secondary inputs enable redundant-power option for non-redundant network devices
- Pre-installed WEBCARDLX with latest version of PADM20 for IP-based Auto Probe feature
- 2U rackmount, 2 L6-30P inputs, 19 switched outlets (16 C13, 2 C19, 1 L6-30R)
- Individually switched outlets, network interface and visual current, voltage and environmental monitoring

Package Includes

- 2U PDUMH30HVATNET 24A ATS SWITCHED PDU
- 2U rackmount installation brackets
- (16) IEC C13 plug retention sleeves
- (2) IEC C19 plug retention sleeves
- (1) Micro-USB-to-USB A configuration cable (73-1689)
- User manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Switched outlets and Ethernet interface supports individual outlet control on a real-time or programmable basis and user-specified alarm notification thresholds for all reported site power conditions
- Pre-installed WEBCARDLX with the latest version of PowerAlert Device Manager firmware (PADM20) provides enhanced remote management capabilities
- PADM20 and PowerAlert Element Manager (PAEM) form a powerful tool for expanding maintenance functions in large installations, including firmware update checks and backup and restoration of device configurations
- IP-based Auto Probe detects lost connectivity and restores service autonomously
- Outlets are factory programmed for sequential turn-on at 250 millisecond intervals when the PDU is first energized to prevent inrush-related equipment interaction on startup
- Front panel LED's confirm power availability on both input lines and for each output receptacle
- Includes IEC plug retention sleeves to keep vital network equipment plugged in and continuously powered
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332159601
PDU Type	Auto-Transfer Switch; Switched
INPUT	
PDU Input Voltage	200-240V DUAL INPUT
Recommended Electrical Service	Two single-phase 30A 200-240V circuits
Maximum Input Amps	24
Maximum Input Amps Details	Agency rated to 24A continuous
PDU Plug Type	(2) NEMA L6-30P
Input Phase	Single-Phase
Input Cord Details	Set of two inputs connect to separate PRIMARY and SECONDARY power sources
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
OUTPUT	
Output Capacity Details	5.8kW (240V), 5.5kW (230V), 5.3kW (220V), 5kW (208V), 4.8kW (200V) total capacity / 30A max (Agency de-rated to 24A); 24A max per L6-30R outlet; 16A max per breakered outlet bank; 16A max per C19 outlet; 12A max per C13 outlet
Frequency Compatibility	50 / 60 Hz



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Output Receptacles	(16) C13; (2) C19; (1) L6-30R
Output Nominal Voltage	200-240V
Overload Protection	Includes two 20A output circuit breakers; Breaker 1 controls the upper row of 9 outlets (8 C13, 1 C19); Breaker 2 controls the lower row of outlets (8 C13, 1 C19); L6-30R outlet is unbreakered
Customized Load Management Receptacles	Each outlet is individually controllable via remote interface

USER INTERFACE, ALERTS & CONTROLS

Front Panel LCD Display	Digital display reports output amps in 4 separately metered loading segments (BANK 1: Outlets #1-9; BANK 2: Outlets #10-18; BANK 3: Outlet #19), whole-PDU output kW load level and input voltage on primary and secondary input lines
Front Panel LEDs	19 LEDs display power on/off status for each outlet, plus 2 LEDs for power status on Primary and Secondary input connection and three additional LEDs to label the displayed numeric value as Amps, kW or Voltage. Network Link/Activity (Green): Flashes for network activity. Network Speed (Yellow): 10 Mbps (Flashing), 100 Mbps (On steady). LX Platform Interface Status: Normal Operation (Solid Green); Software Update (Alternating Green/Orange ~1/sec); Factory Reset (Alternating Green/Orange ~2/sec).
Switches	ENTER and MODE switches toggle the digital display to show output amps (Banks 1-4), total kW output and input voltage (primary, secondary). LX Platform Interface: Recessed reset switch for interface reboot and factory reset
Current Measurement Accuracy (Amps)	+/-1%
Voltage Measurement Accuracy (Volts)	+/-1%
Power Measurement Accuracy (Watts)	+/-1%

PHYSICAL

Form Factors Supported	2U rackmount
Material of Construction	Metal
Minimum Required Rack Depth (cm)	40.64
Minimum Required Rack Depth (inches)	16
PDU Form Factor	Horizontal (2U)
Shipping Dimensions (hwd / cm)	19.81 x 42.67 x 50.55
Shipping Dimensions (hwd / in.)	7.80 x 16.80 x 19.90
Shipping Weight (kg)	8.80
Shipping Weight (lbs.)	19.40
Unit Dimensions (hwd / cm)	8.8 x 44.5 x 31.8
Unit Dimensions (hwd / in.)	3.5 x 17.5 x 12.5
Unit Weight (kg)	6.21
Unit Weight (lbs.)	13.70

ENVIRONMENTAL

Operating Temperature Range	0C ~ 40C (32F ~ 104F)
-----------------------------	-----------------------



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5 to 95% (non-condensing)
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
COMMUNICATIONS	
PowerAlert Software	LX Platform Interface: PowerAlert Device Manager 15 (PADM15)
Communications Cable	Micro-USB- to-USB A configuration/console access cable
Network Monitoring Port	RJ45 Network port, Micro-USB Configuration port, USB A port supports a variety of Envirosense2 environmental and control modules. See Accessories>Management Hardware section for more information about these modules.
SNMP Compatibility	Pre-installed LX platform interface provides remote monitoring via Java-free HTML5 web interface, telnet, SSH and SNMP management systemsPre-installed LX platform interface provides remote monitoring via Java-free HTML5 web interface, telnet, SSH and SNMP management systems
Network Speed	10/100 Mbps
Communications Interface	Pre-installed network card; USB
SPECIAL FEATURES	
High Availability PDU Features	Auto Probe Monitoring and Reboot (included)
STANDARDS & COMPLIANCE	
Certifications	Tested to UL 60950-1 (USA, Canada), Class A (Emissions), NOM (Mexico), RoHS Complaint, TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDUMH30HVATNET](#)