

SmartRack 12U Desktop 2-Post Open-Frame Rack

MODEL NUMBER: SR2POST12



Free-standing open-frame 2-post rack stores and organizes 12U of 19-inch rack equipment in labs, test setups, network closets and other secure IT areas with limited floor space where you need easy access to equipment.

Description

The SR2POST12 SmartRack® 12U Desktop 2-Post Open-Frame Rack provides an economical rack-mount solution for laboratories, test setups, small network closets and other secure IT locations with limited floor space where you need equipment to be organized and easy to access. It's ideal for mounting network switches, routers, patch panels, audio/video components and other EIA-standard 19-inch rack equipment up to 36 inches deep.

Constructed from heavy-duty steel with a durable black powder-coated finish, the SR2POST12 has a maximum load capacity of 110 lbs (49.9 kgs). Stationed on a desktop, floor or counter, this free-standing rack saves precious space and allows you fast, easy access at your immediate workspace for organizing, installing and servicing equipment and cabling.

The SR2POST12 is easy to assemble using the included hardware. The vertical mounting rails have square-hole mounting and cable management slots for securing equipment to the steel frame. Only user-supplied standard hand tools are required for setup.

Features

Saves Valuable Workspace

- Perfect for installing network switches, routers, patch panels and audio/video components in secure IT areas with limited floor space
- Houses EIA-standard 19 in. rack equipment up to 36 in. deep
- Maximum load capacity of 110 lbs (49.9 kgs)

Highlights

- Maximum load capacity of 110 lbs (49.9 kgs)
- Secures 12U of 19 in. rack equipment up to 36 in. deep
- Heavy-duty steel construction designed to last
- Easy to assemble with included hardware
- Free-standing design rests on rubber feet

Package Includes

- (2) Uprights
- (2) Base brackets
- Front cross member
- (8) M5 screws
- (20) M6 screws
- (20) M6 cage nuts
- (20) M6 cup washers
- (4) Rubber feet
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Free-Standing Open-Frame Design

- Allows fast, easy access for organizing, installing and servicing equipment and cabling
- Rests on desktop, floor or counter at your immediate workspace

Easy Assembly and Installation

- Made from heavy-duty steel with a durable black powder-coated finish
- Easy to assemble with included hardware and user-supplied hand tools
- Vertical mounting rails with square-hole mounting and cable management slots

Specifications

OVERVIEW	
UPC Code	037332188458
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Open-Frame
PHYSICAL	
Color	Black
EIA Mounting Rails	M6 Cagenuts
Maximum Device Depth (cm)	91.44
Maximum Device Depth (in.)	36
Maximum Device Depth (mm)	914
Rack Height	12U
Shipping Dimensions (hwd / cm)	8.13 x 9.14 x 63.50
Shipping Dimensions (hwd / in.)	3.20 x 3.60 x 25.00
Shipping Weight (kg)	2.40
Shipping Weight (lbs.)	5.30
Unit Weight (kg)	1.81
Unit Weight (lbs.)	4
Weight Capacity - Stationary (kg)	50
Weight Capacity - Stationary (lbs.)	110
Rack Depth	Standard
Number of Vertical Mounting Rails	2
STANDARDS & COMPLIANCE	
Approvals	EIA-310-D, IEC 60297-3-100, RoHS



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SR2POST12](#)