

## Dual-Monitor Desktop Mount Stand for 13" to 27" Flat-Screen Displays

MODEL NUMBER: DDR1327SDD



Full-motion desktop stand mounts 2 flat-screen monitors on independently adjustable arms and a single base to free up valuable space on your desk, table or workstation. Recommended for home or office use.

### Description

The VESA-compliant DDR1327SDD Dual Flat-Screen Monitor Desktop Mount Stand mounts two flat-screen monitors on a sturdy base, allowing you to free up valuable workspace on your desk, table or workstation. Recommended for home or office, the DDR1327SDD fits most flat-panel displays from 13 to 27 inches.

Position your monitors with one-touch ease to optimize viewing angle and height to fit your environment and comfort level. A 180° swivel and -45° to +45° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your monitors in portrait or landscape orientation.

Each VESA mount supports up to 26 lbs (11.8 kgs). The durable steel frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Mounting hardware is included. Conforms to VESA-compliant displays with either of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm.

### Features

**Mounts 2 Flat-Screen Monitors on a Sturdy Base**Fits most flat-panel TVs, monitors and other displays from 13 to 27 in.Frees up valuable workspace on your desk, table or workstationMounting arms adjust independently for viewing angleIdeal for home or office use

**Convenient One-Touch Adjustment**180° swivel and -45° to +45° tilt capability provide comfortable viewingFull 360° rotation for viewing in portrait or landscape orientation

**Durable Steel Construction**Each mount supports up to 26 lbs (11.8 kgs)Scratch-resistant powder-coated finish blends with any décorMounting hardware included

**VESA Compliance**Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm

### Highlights

- Fits most flat-panel displays from 13 to 27 in.
- One-touch adjustment for comfortable viewing
- Rotates 360° for viewing in portrait or landscape orientation
- 180° swivel and -45° to +45° tilt for wide range of motion
- Supports up to 26 lbs (11.8 kgs) per VESA mount

### Package Includes

- Pole
- Base
- (2) Mounting arms
- Locking head assembly
- Pole cable guide
- Base collar
- (2) VESA plate assemblies
- (2) Arm cable guides
- (2) End caps
- (8) Washers
- (18) Screws
- Hex key, 3 mm
- Hex key, 4 mm
- Hex key, 6 mm
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332203397



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Device Compatibility	Monitor/HDTV
<b>PHYSICAL</b>	
Color	Black
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Degrees of Motion	-45/+45 Tilt; 180 Swivel; 360 Rotate
Material of Construction	Steel
Maximum Screen Size (cm)	68.58
Maximum Screen Size (in.)	27
Maximum Weight Capacity (kg)	12
Maximum Weight Capacity (lbs.)	26
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Motion	Full
Mounting Location	Desktop
Number of Displays	2
Shipping Dimensions (hwd / cm)	32.59 x 46.00 x 13.21
Shipping Dimensions (hwd / in.)	12.83 x 18.11 x 5.20
Shipping Weight (kg)	5.79
Shipping Weight (lbs.)	12.76
Unit Dimensions (hwd / cm)	46.0 x 80.5 x 25.4
Unit Dimensions (hwd / in.)	18.11 x 31.69 x 10
Unit Weight (kg)	4.79
Unit Weight (lbs.)	10.56
<b>FEATURES &amp; SPECIFICATIONS</b>	
Tools Necessary	Yes
<b>SPECIAL FEATURES</b>	
Cord Management	Yes
Security Lock	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Approvals	RoHS3, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (U.S. & Canada)	5-year limited warranty
---	-------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[DDR1327SDD](#)