



Features

- 5 to 40 amp ratings.
- Cannot be manually tripped.
- Button extends for visual trip indication.
- Push button to reset breaker.
- Numerous mounting and termination options.
 Choice of silver-cadmium oxide or silver-tin oxide contacts.
- Optional bottom marking of amperage rating

Agency Approvals

W54 series is UL 1077 Recognized as Supplementary Protectors, File E69543, for Canada and the United States. Available models meet Ignition Protection requirements in accordance with UL 1500 (excludes models rated >30A). CSA Accepted as Supplementary Protectors (Appliance Component Protectors), File 240027 (to 125VAC, excludes models rated >30A). Approved to VDE 0642/EN60934 (Circuit Breakers for Equipment) License Number 40007877 (excludes models rated >20A, models with screw terminals, models with silver-tin oxide contacts). CCC mark compliant, certificate 2004010307123217.

Users should thoroughly review the technical data before selecting a product part number. It is recommended that users also seek out the pertinent approvals files of the agencies/laboratories and review them to confirm the product meets the requirements for a given application.

Electrical Data @ 25°C

Calibration: Will continuously carry 100% of rating.

May trip between 101% and 134%, but must trip at 135% of

rating within one hour at +25°C

Dielectric Strength: 1,500VAC (60 seconds).

W54 series

Push To Reset Only P&B Thermal Circuit Breaker

c**FL**°us





Insulation Resistance: 100 megohms

Maximum Operating Voltages: 50VDC; 250VAC

Interrupt Capacity: 1,000 amps in accordance with UL standard 1077.

Resettable Overload Capacity: Ten times rated current.

Reset Time: 60 seconds.

Typical Resistance vs. Current Rating @25°C

| Current Rating in Amps | Typical Resistance in Ohms | Current Rating in Amps | Typical Resistance in Ohms | |
|------------------------------|----------------------------------|------------------------------|----------------------------------|--|
| 5.0 | 0.050 | 15.0 | 0.017 | |
| 6.0 | 0.042 | 20.0 | 0.012 | |
| 7.0 | 0.036 | 25.0 | 0.010 | |
| 8.0 | 0.031 | 30.0 | 0.008 | |
| 10.0 | 0.025 | 35.0 | 0.007 | |
| 12.0 | 0.021 | 40.0 | 0.006 | |


Mechanical/Environmental Data

Operating Temperature Range: 0°C to +60°C.

Termination: .250" (6.35mm) quick connects or #8-32 screws. Mounting: Various options. See Ordering Information and drawings.

Approximate Weight: 0.9 oz. (25.0g).

Time vs. Current Trip Curve @ +25°C



Ambient Compensation Table


| Ambient Temperature | Rating Correction Factor | | | |
|------------------------|--------------------------|--------------|--|--|
| in °C | 5-8A Models | 9-30A Models | | |
| 10 | .90 | .80 | | |
| 20 | .98 | .90 | | |
| 25 | 1.00 | 1.00 | | |
| 30 | 1.10 | 1.05 | | |
| 40 | 1.25 | 1.15 | | |
| 50 | 1.61 | 1.31 | | |
| 60 | 2.00 | 1 55 | | |

To use this chart: Divide the breaker rating by the correction factor to determine the compensated rating. Calculate the overloads in terms of the compensated rating to use the published trip curve. Do not use these devices outside

their specified operating temperature


ranges

Outline Dimensions




Optional Protective Boot

Silicone rubber boot is bonded to integral alumimum nut.



1-1423696-5


Black boot for W54 with 3/8"-24 bushing.



1-1423696-6

Clear boot for W54 with M11 X 1.0 bushing.

Ordering Information



12. UL Recognition:

Leave Blank = UL1077 recognized breaker

M = Model meeting Ignition Protection requirements in accordance with UL 1500, in addition to UL1077 recognition (not available with models >30A rating.) Code M breakers are not VDE approved or CSA certified.

Our authorized distributors are more likely to stock the following items for immediate delivery.

W54-XB1A4A10-5 W54-XB1A4A10-15 W54-XB1A4A10-25 W54-XB1A4A10-10 W54-XB1A4A10-20 W54-XB1A4A10-30

90

ORDERING NOTE:


Mounting hardware can be ordered separately. Some options are subject to extended leadtimes and significant minimum order quantities.

QC/PCB

270°

Termination Options

90



.250 QC

Revised 3-09 www.tycoelectronics.com

.250 QC


Straight

45


with #8-32 Load

Term. Bent 90°


Mounting Bushings and Recommended Panel Cutouts




Option 1 - M11 X 1.0 Thread




Option 2 & 7 - 3/8" - 24UNF Thread



Option 3 & 6 - M11 X 1.0 Thread



Option 4 - M12 X 1.0 Thread




Mounting Hardware Options




Knurled Nut



Hex Nut



Integrated Knurled Nut with Small Holes



Lockwasher

Optional Bottom Marking of Rating



Mounting Hardware Dimensions

| Dimension Code | Bushing Diameter | Plastic Knurled Nut | Integrated Plastic Knurled Nut w/Holes | Metal Knurled Nut | Metal Hex Nut | Lockwasher |
|-------------------|---------------------|------------------------|---|----------------------|------------------|-------------|
| А | 3/8" | .74 (18.8) | - | .56 (14.2) | .55 (14.0) | .49 (12.5) |
| | M11 | .74 (18.8) | .74 (18.8) | .59 (15.0) | .55 (14.0) | .587 (14.9) |
| | M12 | _ | - | .59 (15.0) | .55 (14.0) | .626 (15.9) |
| В | 3/8" | .126 (3.2) | - | .079 (2.0) | .079 (2.0) | .02 (.5) |
| | M11 | .126 (3.2) | .13 (3.3) | .102 (2.6) | .118 (3.0) | .02 (.5) |
| | M12 | - | - | .102 (2.6) | .079 (2.0) | .02 (.5) |

Mounting Hardware Ordering Information

| Mounting Bushing Material | Mounting Bushing Code | Plastic Knurled Nut | Integrated Plastic Knurled Nut w/Holes | Metal Knurled Nut | Metal Hex Nut | Lockwasher |
|------------------------------|--------------------------|------------------------|---|----------------------|------------------|-------------|
| Metal | 1 (M11) | _ | _ | 1423696-4 | 1423696-6 | 1-1423696-2 |
| | 2 (3/8") | - | - | 1-1423696-0 | 1423696-3 | 1-1423696-1 |
| | 3 (M11) | _ | - | 1423696-4 | 1423696-6 | 1-1423696-2 |
| | 4 (M12) | - | - | 1423696-5 | 1423696-7 | 1-1423696-3 |
| Plastic | 6 (M11) | 1423696-8 | 2-1423696-2 | _ | _ | _ |
| | 8 (3/8") | 1423696-2 | - | - | _ | _ |

Nameplates



Embossed Aluminum



Imprinted Aluminum (Either Silver on Black or Black on Silver)

@ 2009 by Tyco Electronics Corporation. All Rights Reserved. P&B, TE logo and Tyco Electronics are trademarks.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

1-1423696-6