

## Cisco-Compatible GLC-TE SFP Transceiver - 10/100/1000Base-TX, Copper, RJ45, Cat6, 328.08 ft. (100 m)

MODEL NUMBER: N286-01GLC-TE



Connects a Cat6 Gigabit Ethernet network cable to a Cisco router, server or switch's SFP port.

### Features

**SFP Transceiver for Connecting Copper Cabling to Your Cisco Network Switch or Router** This SFP transceiver allows you to connect a copper Cat6 cable to a 10/100/1000 Mbps fiber network router, server or switch. It transmits data up to 328.08-ft. (100 m) and supports bi-directional Gigabit Ethernet communication up to 1.25 Gbps.

**Functionally Equivalent to Cisco GLC-TE Transceiver Module** The MSA-compliant N286-01GLC-TE functions just like the equivalent Cisco GLC-TE transceiver module and is manufactured to meet or exceed Cisco specifications. You can use this transceiver with any compatible Cisco router, server or switch and receive the same performance as the GLC-TE.

**Hot-Swappable for Installation Without Network Interruption** This input/output device is fully hot-swappable, so you can install it without a potentially costly 10/100/1000 Mbps network shutdown or device reboot. Just plug the SFP end of the transceiver into your Cisco network device. The other end has an RJ45 connector to link with high-speed Cat6 patch cable (sold separately). A convenient bail clasp latch helps you carefully remove the module from the device.

**Premium Features for Superior Performance** The auto-sensing RJ45 port supports auto-negotiation and automatic MDI/MDI-X crossover to match the other end of the connection. The transceiver's zinc housing protects against electromagnetic interference (EMI) and excessive power dissipation.

### Highlights

- SFP transceiver module 100% compatible with Cisco's equivalent module
- Provides 10/100/1000 Mbps throughput up to 328.08-ft. (100 m) via Cat6 cabling
- Auto-sensing RJ45 port adjusts to match data speeds and detects MDI/MDI-X
- Hot-swappable interface lets you install and uninstall without shutting down
- Supports bi-directional Gigabit Ethernet communication up to 1.25 Gbps

### Applications

- Install an additional RJ45 port on a Cisco router, server or switch for the purpose of connecting a Cat6 Gigabit Ethernet network cable

### System Requirements

- Cisco or other compatible network router, server or switch

### Package Includes

- N286-01GLC-TE Cisco-Compatible GLC-TE SFP Transceiver

## Specifications

OVERVIEW	
UPC Code	037332248978
Technology	SFP+/QSFP+/QSFP28



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

PHYSICAL	
Color	Silver
Unit Dimensions (hwd / cm)	0.85 x 1.34 x 5.66
Unit Dimensions (hwd / in.)	0.33 x 0.53 x 2.23
Unit Dimensions (hwd / mm)	8.5 x 13.4 x 56.6
ENVIRONMENTAL	
Operating Temperature Range	32 to 158F (0 to 70C)
Storage Temperature Range	-40 to 185F (-40 to 85C)
Relative Humidity	5% to 85%
COMMUNICATIONS	
Network Speed	10/100 Mbps; 1Gbps
Transmission Distance	100 m
CONNECTIONS	
Side A - Connector 1	SFP (MALE)
Side B - Connector 1	RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
Driver Required	No
Brand Compatibility	Cisco
Multi-Source Agreement (MSA) Compliant	Yes
SPECIAL FEATURES	
Data Transfer Rate	1Gbps
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N286-01GLC-TE](#)