

## 10G Duplex Multimode 50/125 OM4 LSZH Fiber Optic Cable (LC/LC), Push/Pull Tabs, Magenta, 1 m

MODEL NUMBER: **N821-01M-MG-T**



Premium multimode fiber optic cabling transmits clear 10 Gb data and voice signals up to 400 m (@ 850 nm). Recommended for LANs, SANs and high-speed parallel interconnects for head-ends, central offices and data centers.

### Description

The N821-01M-MG-T 10 Gb Duplex Multimode 50/125 OM4 LSZH Fiber Patch Cable is OM4-rated for use with 10 Gb Ethernet applications up to 400 meters (at 850 nm). Suited for LANs, SANs and high-speed parallel interconnects for head-ends, central offices and data centers, this low-cost cable provides four times more bandwidth than conventional 62.5  $\mu$ m multimode fiber and performance rivaling that of singlemode cable.

Push/pull tab connectors are easily accessible in high-density data center applications and make the cable easy to install and remove with one hand. Dual male LC connectors are widely compatible and thoroughly tested to meet stringent insertion loss standards. Premium-grade ceramic ferrules are designed specifically to handle applications of 10 Gb or higher.

Colored magenta for immediate identification as an OM4 cable, the laser-optimized multimode fiber (LOMMF) N821-01M-MG-T is backward compatible with existing 50/125 fiber and commonly used with vertical-cavity surface-emitting laser (VCSEL) and LED laser light sources.

The low-smoke zero-halogen (LSZH) jacket limits the amount of toxic smoke emitted in case of combustion, making this cable perfect for poorly ventilated areas. The slim, space-saving uniboot design is easy to manage through ceilings, walls and ducts. The sturdy plastic housing is built to last a long time.

### Features

#### OM4-Rated for 10 Gb Ethernet Applications

### Highlights

- Nearly 4x the bandwidth over conventional 62.5  $\mu$ m multimode fiber
- Push/pull tab connectors install/remove with one hand
- Slim, space-saving uniboot design for neat cable management
- Premium-grade ceramic ferrules designed for fast applications
- Magenta color for easy OM4 identification

### Package Includes

- N821-01M-MG-T 10 Gb Duplex Multimode 50/125 OM4 LSZH Fiber Patch Cable, 1 m (3 ft.)



- Magenta color for easy OM4 identification
- Allows 10 Gb serial transmission up to 400 m (@ 850 nm)
- Recommended for LANs, SANs and high-speed parallel interconnects for head-ends, central offices and data centers
- Provides 4x more bandwidth than conventional 62.5 µm multimode fiber
- Commonly used with VCSEL and LED laser light sources
- Backward compatible with existing 50/125 fiber

#### LC Connectors with Push/Pull Tabs

- Push/pull tab connectors easy to install and remove with one hand
- Sturdy dual LC connectors tested to meet stringent insertion loss standards

#### Premium Construction for Error-Free Signal Transfer

- Premium-grade ceramic ferrules for 10 GbE and faster applications
- Slim, space-saving uniboot design easy to manage through ceilings, walls and ducts
- Low-smoke zero-halogen jacket ideal for poorly ventilated areas
- Sturdy plastic housing built to last a long time
- Meets current IEEE 802.3ae and TIA LOMMF standards

## Specifications

| OVERVIEW                        |                      |
|---------------------------------|----------------------|
| UPC Code                        | 037332201669         |
| Technology                      | Multimode            |
| Optical Mode                    | OM4                  |
| PHYSICAL                        |                      |
| Cable Jacket Color              | Magenta              |
| Clad Diameter                   | 125 micron           |
| Core Diameter                   | 50 micron            |
| Number of Fibers                | 2                    |
| Cable Length (ft.)              | 3.3                  |
| Cable Length (m)                | 1                    |
| Cable Length (in.)              | 39.4                 |
| Shipping Dimensions (hwd / cm)  | 22.86 x 17.78 x 1.27 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50   |
| Shipping Weight (kg)            | 0.02                 |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                                     |
|-------------------------------------|-------------------------------------|
| Shipping Weight (lbs.)              | 0.04                                |
| <b>ENVIRONMENTAL</b>                |                                     |
| Operating Temperature Range         | -4 TO 140 F (-20 TO 60 C)           |
| Storage Temperature Range           | -4 TO 140 F (-20 TO 60 C)           |
| <b>COMMUNICATIONS</b>               |                                     |
| Network Speed                       | 10Gbps / 40Gbps / 100Gbps           |
| <b>CONNECTIONS</b>                  |                                     |
| Side A - Connector 1                | LC DUPLEX (MALE) WITH PULL/PUSH TAB |
| Side B - Connector 1                | LC DUPLEX (MALE) WITH PULL/PUSH TAB |
| <b>SPECIAL FEATURES</b>             |                                     |
| Push/Pull Tabs                      | Yes                                 |
| <b>WARRANTY</b>                     |                                     |
| Product Warranty Period (Worldwide) | Lifetime limited warranty           |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N821-01M-MG-T](#)