

REV. 1

DCO 141326

COIL: @ 25°C  
 RESISTANCE \_\_\_\_\_ 56 OHMS ± 10%  
 NOMINAL VOLTAGE \_\_\_\_\_ 6.0 VDC  
 MUST OPERATE \_\_\_\_\_ 2.7 VDC

MUST RELEASE \_\_\_\_\_ 1.6 VDC MAX, 0.3 VDC MIN.

#### ENVIRONMENT:


VIBRATION \_\_\_\_\_ 10 \_\_\_\_\_ CPS TO \_\_\_\_\_ 3000 \_\_\_\_\_ CPS @ \_\_\_\_\_ 30 \_\_\_\_\_ g's

SHOCK \_\_\_\_\_ 75 \_\_\_\_\_ g's \_\_\_\_\_ 6 \_\_\_\_\_ MS. DURATION

TEMPERATURE \_\_\_\_\_ -65 \_\_\_\_\_ °C TO \_\_\_\_\_ +125 \_\_\_\_\_ °C

NOTES: \_\_\_\_\_ OPERATE & RELEASE 4 MS MAX.  
 \_\_\_\_\_ BOUNCE 2 MS MAX.

#### CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: \_\_\_\_\_ LOW LEVEL TO  
 \_\_\_\_\_ 2 AMPS 28 VDC RESISTIVE  
 \_\_\_\_\_ 50,000 OPERATIONS

DR. R.B. 4/29/98 CK. G9H 9/20/99



COMMUNICATIONS  
 INSTRUMENTS, INC.

CUST. \_\_\_\_\_ QPL  
 CUST. NO. \_\_\_\_\_ M39016/13-055L REV. \_\_\_\_\_

'3SBC' RELAY

3SBC1501A2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3SBC1501A2](#)