

## OmniSmart 120V 1050VA 705W Line-Interactive UPS, Tower, USB port

MODEL NUMBER: **OMNISMART1050**



### Highlights

- 1050VA / 1.05kVA tower 120V line interactive UPS
- Corrects brownouts and overvoltages from 75V to 147V
- USB port, Front panel status LEDs
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

### Package Includes

- OMNI SMART 1050 UPS System
- USB cable
- Warranty information
- Instruction manual

### Description

Tripp Lite's OMNI SMART 1050 line interactive UPS system offers voltage regulation, surge suppression and long lasting battery support for personal computers, internetworking equipment and other sensitive electronics. Supports a single entry level PC system for up to 60 minutes during power failures to facilitate a safe shutdown without data loss. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 75 volts and overvoltages to 147 volts back to normal 120V levels, all without using battery power. Includes 6 battery supported outlets and 6-ft. (1.83 m) AC line cord. USB port enables optional safe unattended system shutdown in the case of extended power failure as well as continuous UPS and site power condition monitoring, USB cable included. PowerAlert software available via free download. Built-in audible alarm and 5 front panel LEDs indicate status of line power, battery power, battery low/replace, voltage regulation and overload. 1050VA / 705 watt power handling ability supports multiple entry-level PCs, network workstations, point-of-sale terminals, small to medium business phone systems, audio/video workstations and heavily configured home theater systems. Offers 7 minutes battery runtime with a full load of 1050VA and 23 minutes with a half load of 525VA. Supports hot swap battery replacement via built-in access panel. \$200,000 connected equipment insurance (U.S., Canada, and Puerto Rico only).

### Features

- OMNISMART1050 line interactive UPS system offers voltage regulation and battery support, plus complete AC surge suppression
- Prevents equipment damage, data loss and downtime due to power problems
- Supports a single entry level PC system for up to 60 minutes during power failures to enable a safe system shutdown
- Supports a max load of 1050VA for 7 minutes
- Supports a half load of 525VA for 23 minutes
- Automatic Voltage Regulation (AVR) circuits correct brownouts as low as 75 and overvoltages as high



as 147 volts to normal 120 volt levels without using battery power

- Upright tower configuration uses only 51 square inches of floor or desktop space
- Includes 6 battery supported outlets, 6-ft. (1.83 m) AC line cord (all NEMA 5-15)
- USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [www.tripplite.com/poweralert](http://www.tripplite.com/poweralert)
- Supports Tripp Lite's WatchDog software application to restore unresponsive programs by automatically restarting them and rebooting completely locked computers by automatically switching UPS power off and back on again
- Built-in audible alarm and 5 front panel LEDs indicate status of line power, battery power, battery low/replace, voltage regulation and overload status
- 1050VA / 705 watt power handling ability supports multiple entry-level PCs, network workstations, point-of-sale terminals, small to medium business phone systems, audio/video equipment stations and heavily configured home theater systems
- Supports hot-swap battery replacement via built-in battery access panel
- Compatible with 120V / 60Hz applications for USA, Canada, Mexico and more
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OVERVIEW	
UPC Code	037332033796
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	6.7A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	15A
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	1050



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Output kVA Capacity (kVA)	1.05
Output Watt Capacity (Watts)	705
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(6) 5-15R
Individually Controllable Load Banks	No
<b>BATTERY</b>	
Full Load Runtime (min.)	7 min. (705w)
Half Load Runtime (min.)	23 min. (355w)
Expandable Runtime	No
DC System Voltage (VDC)	18
Battery Recharge Rate (Included Batteries)	Less than 8 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//www.tripplite.com/UPS-Replacement-Battery-Cartridge-select-Tripp-Lite-Best-Liebert-Minuteman-other-UPS~RBC52">RBC52</a>&nbsp;<sup>3</sup> (quantity 3)
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 75 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 93 and 107 are boosted by 14%
Severe Undervoltage Correction	Input voltages between 75 and 92 are boosted by 30%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	480
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	480
AC Suppression Response Time	Instantaneous
PHYSICAL	
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount ( <a href="http://www.tripplite.com/Wall-Mount-Bracket-Installation-Accessories-for-UPS-Systems-UPSWM">productLink</a> UPSWM - tower mounting kit)
Primary Form Factor	Tower
Primary UPS Depth (mm)	183
Primary UPS Height (mm)	292
Primary UPS Width (mm)	173
Shipping Dimensions (hwd / cm)	39.62 x 26.92 x 26.67
Shipping Dimensions (hwd / in.)	15.60 x 10.60 x 10.50
Shipping Weight (kg)	13.83
Shipping Weight (lbs.)	30.50
UPS Housing Material	PVC
UPS Power Module Dimensions (hwd, cm)	29.21 x 17.27 x 18.29
UPS Power Module Dimensions (hwd, in.)	11.5 x 6.8 x 7.2
UPS Power Module Weight (kg)	13.15
UPS Power Module Weight (lbs.)	29
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	74
Battery Mode BTU / Hr. (Full Load)	564
AC Mode Efficiency Rating (100% Load)	94%
COMMUNICATIONS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert Local software at <a href="https://www.tripplite.com/poweralert">https://www.tripplite.com/poweralert</a>
Communications Cable	USB cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Communications Interface	USB
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	75
High Voltage Transfer to Battery Power (Setpoint)	147
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
<b>STANDARDS &amp; COMPLIANCE</b>	
UPS Certifications	Meets FCC Part 15 Category B (EMI); ROHS (Restriction of Hazardous Substances); Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tripp Lite:

[OMNISMART1050](#) [OMNISMT1050PNP](#)