

REV. 1

DCO 141326


COIL: @ 25°C
 RESISTANCE _____ 650 OHMS ± 10%
 NOMINAL VOLTAGE _____ 18.0 VDC
 MUST OPERATE _____ 9.5 VDC
 MUST RELEASE _____ 5.6 VDC MAX, 1.0 VDC MIN.

ENVIRONMENT:

VIBRATION _____ 10 _____ CPS TO _____ 3000 _____ CPS @ _____ 30 _____ g's
 SHOCK _____ 75 _____ g's _____ 6 _____ MS. DURATION
 TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: _____ OPERATE & RELEASE 4 MS MAX.
 _____ BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
 2 AMPS 28 VDC RESISTIVE
 50,000 OPERATIONS

DR. _____ R.B. 1/20/98 CK. GAH 9/20/99

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. _____ OPL
 CUST. NO. M39016/13-077L REV. _____

3SBC RELAY

3SBC1542A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3SBC1542A2](#)