

REV. 0

DCO 142658


COIL: @ 25°C  
 RESISTANCE 140 OHMS ± 10%  
 NOMINAL VOLTAGE 9.0 VDC  
 MUST OPERATE 4.4 VDC  
 MUST RELEASE 2.6 VDC MAX. 0.5 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 4 MS MAX.  
CONTACT STABILIZATION TIME 25 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO  
2 AMPS 28 VDC RESISTIVE  
50,000 OPERATIONS

DR. PBB 1/25/01 CK. TLG 01-25-00

**ICII Technologies™**  
 advanced control electronic solutions

CUST. QPL  
 CUST. NO. M39016/13-075P REV.        "3SBC" RELAY

3SBC2020A2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3SBC2020A2](#)