


1.4kW 120V Single-Phase Switched Mini PDU - LX Platform Interface, NEMA 5-15P 6 ft. (1.83 m) Cord, 0U, TAA

MODEL NUMBER: PDU15NETLX



Switched PDU distributes network-grade single-phase power to connected devices in small 1- or 2-outlet installations.

Features

Switched PDU Provides Advanced Network Control and Remote Power Monitoring This 0U PDU is an ideal low-cost option for small-scale network configurations where only one or two outlets are needed. It features two NEMA 5-15R individually switched outlets, which can be remotely controlled to turn on, turn off, recycle or lock power to unresponsive devices. Front-panel LEDs indicate each outlet's on/off status.

Pre-Installed WEBCARDLX Network Interface Offers 24/7 Remote Access for Monitoring and Control The built-in WEBCARDLX with the latest version of PowerAlert Device Manager firmware (PADM20) provides enhanced remote management capabilities, including customizable dashboard graphs to fit user preferences. The PADM20 upgrade and Tripp Lite's PowerAlert Element Manager (PAEM) software form a powerful tool for expanding maintenance functions in large installations, including firmware update checks and backup and restoration of device configurations. PADM20's Auto Probe feature allows a PDU with switched loads to automatically reboot devices if a network communication failure is detected. This preserves uptime and minimizes the time and expense associated with on-site support.

Easy Connection to an AC Power Source A 6-ft. (1.83 m) power cord with NEMA 5-15P plug connects the PDU15NETLX 0U PDU to a compatible AC power source, generator or protected UPS.

Flexible Installation Options The switched PDU mounts vertically in 0U of rack space, on a wall or under a counter using the included mounting brackets and user-supplied hardware. Its half-width rack-mount form factor allows you to place it on a shelf or desktop.

TAA-Compliant for GSA Schedule Purchases The PDU15NETLX is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Highlights

- Pre-installed WEBCARDLX with latest version of PADM20 for IP-based Auto Probe feature
- 2 switched NEMA 5-15R outlets can be remotely rebooted, locked or shut down
- NEMA 5-15P input with 6-ft. (1.83 m) cord connects to mains power, generator or UPS system
- Mounts on wall, under counter or in 0U of rack space using included brackets
- Ideal low-cost option for small-scale installations requiring no more than 2 outlets

Applications

- Provide 120V power for up to 2 devices in a small-scale network configuration
- Remotely monitor, control and reboot power to connected equipment in data centers and computer rooms
- Manage kiosks and other unattended applications

Package Includes

- PDU15NETLX 1.4kW 120V Single-Phase Switched Mini PDU
- (2) Mounting brackets w/screws
- Owner's manual

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| OVERVIEW | |
|--|---|
| UPC Code | 037332203267 |
| PDU Type | Switched |
| INPUT | |
| PDU Input Voltage | 120V |
| Recommended Electrical Service | Single-phase 15A 120V service |
| Maximum Input Amps | 12 |
| Maximum Input Amps Details | Agency de-rated to 12A continuous |
| PDU Plug Type | NEMA 5-15P |
| Input Phase | Single-Phase |
| Input Cord Length (ft.) | 6 |
| Input Cord Length (m) | 1.83 |
| OUTPUT | |
| Output Capacity Details | 1.44kW (120V) / 12A total capacity; 12A max per outlet |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (2) 5-15R |
| Output Nominal Voltage | 120V |
| Overload Protection | n/a |
| Customized Load Management Receptacles | 2 individually switched output receptacles |
| USER INTERFACE, ALERTS & CONTROLS | |
| Front Panel LEDs | Set of two front-panel LEDs indicate off/on power status for each outlet. Ethernet Link and Status LED's for network activity. System status LED for monitoring system operation. |
| Switches | Reset button allows reboot of management card without affecting connected equipment. |
| PHYSICAL | |
| Form Factors Supported | 0u rackmount, Wall-mount, Under-counter mount |
| Material of Construction | Metal |
| Minimum Required Rack Depth (cm) | 17.78 |
| Minimum Required Rack Depth (inches) | 7 |
| PDU Form Factor | Vertical (0U) |
| Shipping Dimensions (hwd / cm) | 5.00 x 21.21 x 20.50 |
| Shipping Dimensions (hwd / in.) | 1.97 x 8.35 x 8.07 |
| Shipping Weight (kg) | 1.49 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|---|
| Shipping Weight (lbs.) | 3.28 |
| Unit Dimensions (hwd / cm) | 4.4 x 17.8 x 12.7 |
| Unit Dimensions (hwd / in.) | 1.73 x 7 x 5 |
| Unit Weight (kg) | 1.20 |
| Unit Weight (lbs.) | 2.64 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 0C ~ 50C (32F ~ 122F) |
| Storage Temperature Range | -30°C to +60°C (-22°F to +140°F) |
| Relative Humidity | 5 to 95% (non-condensing) |
| COMMUNICATIONS | |
| Network Monitoring Port Description | LX platform interface provides remote monitoring via Java-free HTML5 web interface, Telnet, SSH and SNMP management systems. |
| Network Monitoring Port | RJ45 Network port, RJ45 Serial Config/Console Access port; and USB A port supports a variety of Envirosense2 environmental and control modules. See Accessories>Management Hardware section for more information about these modules. |
| SNMP Compatibility | SNMP V1, v2c, V3 |
| Network Speed | 10/100 Mbps |
| Communications Interface | (1) RJ45 Network; (1) RJ45 Serial; (1) USB-A |
| SPECIAL FEATURES | |
| High Availability PDU Features | Auto Probe Monitoring and Reboot (included) |
| STANDARDS & COMPLIANCE | |
| Certifications | Tested to UL 60950-1 (USA). CSA (Canada), Class A Part 15 (Emissions), NOM (Mexico), RoHS compliant, TAA Compliant |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDU15NETLX](#)