

REV. 0

DCO 142665

TOL ± .010 UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C

RESISTANCE 210 OHMS ± 10%

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 5.4 VDC

MUST RELEASE 3.2 VDC MAX, 0.6 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's


SHOCK 75 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 4 MS MAX.

BOUNCE 2 MS MAX.

## CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO  
2 AMPS 28 VDC RESISTIVE  
50,000 OPERATIONS

DR. R.B. 9/10/97

CK. TLG 01-26-01

**CII Technologies™**  
advanced control electronic solutions

CUST. QPL

CUST. NO. M39016/13-121L REV.

RELAY

3SBC2144A2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3SBC2144A2](#)