




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		T	EC 0G3C 0734 04	17DEC04	BSV JLG
			T1	REVISED PER ECO-09-020932	25AUG09	KK AEG

OBSOLETE			2-104257-4	25	7-103640-4
			2-104257-3	24	7-103640-3
			2-104257-2	23	7-103640-2
OBSOLETE			2-104257-1	22	7-103640-1
			2-104257-0	21	7-103640-0
			1-104257-9	20	6-103640-9
			1-104257-8	19	6-103640-8
			1-104257-7	18	6-103640-7
			1-104257-6	17	6-103640-6
OBSOLETE			1-104257-5	16	6-103640-5
			1-104257-4	15	6-103640-4
			1-104257-3	14	6-103640-3
			1-104257-2	13	6-103640-2
			2-104257-4	25	2-103640-4
			2-104257-3	24	2-103640-3
SUPERSEDED			2-104257-2	23	2-103640-2
			2-104257-1	22	2-103640-1
OBSOLETE			2-104257-0	21	2-103640-0
			1-104257-9	20	1-103640-9
			1-104257-8	19	1-103640-8
			1-104257-7	18	1-103640-7
			1-104257-6	17	1-103640-6
			1-104257-5	16	1-103640-5
SUPERSEDED			1-104257-4	15	1-103640-4
			1-104257-3	14	1-103640-3
OBSOLETE			1-104257-2	13	1-103640-2
			1-104257-1	12	1-103640-1
BY 1-103960-1			1-104257-0	11	1-103640-0
BY 1-103960-0			104257-9	10	103640-9
D BY 103960-9			104257-8	9	103640-8
D BY 103960-8			104257-7	8	103640-7
D BY 103960-7			104257-6	7	103640-6
D BY 103960-6			104257-5	6	103640-5
D BY 103960-5			104257-4	5	103640-4
D BY 103960-4			104257-3	4	103640-3
D BY 103960-3			104257-2	3	103640-2
D BY 103960-2			104257-1	2	103640-1
		PLATING	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER

- 1
- CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- 2
- USE WITH #26-#30 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- 3
- THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- 4
- POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5
- FOR STRIP ASSEMBLIES SEE PART NUMBER 103960
- 6
- POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 7
- CONTACTS: .000015 GOLD IN THE CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON THE TERMINATION AREA, ALL OVER .000050 NICKEL
- 8
- CONTACTS: .000015 GOLD IN THE CONTACT AREA, .000050-.000100 MATTE TIN ON THE TERMINATION AREA, ALL OVER .000050 NICKEL
- 9
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L A MAYER 11-4-86		 Tyco Electronics Corporation Harrisburg, PA 17105-3608									
		CHK P de Jong 11-12-86											
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD P de Jong 11-12-86		NAME							
		0 PLC ± -		PRODUCT SPEC		RCPT ASSY, AMPMODU MTE, SINGLE , LATCHED & POLARIZED, FOR #26-#30 AWG WIRE SIZE							
		1 PLC ± -		108-25034									
		2 PLC ± .02		APPLICATION SPEC									
		3 PLC ± .005		114-25026									
4 PLC ± -		ANGLES ± ±		WEIGHT -		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
MATERIAL : HOUSING-FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK		FINISH		A2		00779		C=103640					
CONTACTS- PHOS BRONZE		SEE TABLE		CUSTOMER DRAWING				SCALE	4:1	SHEET	1 of 1	REV	T1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103640-5](#)