





- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 3 THE ASSEMBLY MAY BE BROKEN TO DESIRED NUMBER OF POSITIONS
- 4 BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- 5 POSTS: .000030 GOLD ON THE CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER .000050 NICKEL.
- 6 POSTS: .000030 GOLD ON THE CONTACT AREA, .000100-.000200 MATTE TIN ON THE SOLDER TAIL, ALL OVER .000050 NICKEL.
- 7 HIGH TEMPERATURE CONFIGURATION

	7	6	5	NONE	11	.584	.500	5	12	5-104133-4
	7	6	3	NONE	15	.784	.700	7	16	5-104133-3
		5	5	NONE	11	.584	.500	5	12	104133-4
		5	3	NONE	15	.784	.700	7	16	104133-3
OBSOLETE		5	1	NONE	7	.384	.300	3	8	104133-2
OBSOLETE		5	13	1,2,3,4,5	20	1.284	1.200	12	26	104133-1
REMARKS	PLATING		ROW S	ROW R	NO OF ACTIVE POSN	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER
			POSTS OMITTED							

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN H MOLL19NOV86		TE TE Connectivity																	
DIMENSIONS: INCHES				CHK L. MAYER20OCT86																			
		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		APVD T CLARK21OCT86		NAME HEADER ASSY, MOD II, BREAKAWAY, DBL ROW, RIGHT ANGLE, .100X.100 C/L WITH .025 SQUARE POSTS																	
				PRODUCT SPEC																			
				APPLICATION SPEC																			
				—																			
MATERIAL		HOUSING: FLAME RETARDANT THERMOPLASTIC COLOR-BLACK POSTS: COPPER ALLOY		FINISH		WEIGHT		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO									
				SEE TABLE		—		A2		00779		C-104133		—									
						CUSTOMER DRAWING						SCALE		4:1		SHEET		1 of 1		REV		M	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104133-3](#)