


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		L	EC 0G3C 0675 04	08JAN04	BSV DFR
			L1	REVISED PER ECO-09-020932	27AUG09	KK AEG



- 1

.000050 MIN W.E. #1 GOLD ALLOY IN CONTACT AREA, .000050-.000100 TIN-LEAD IN AREA D, ALL OVER .000050 NICKEL.
- 2

MOLDED CIRCUIT #1 IDENTIFIER IN LOCATION SHOWN.
- 3

TOLERANCE NON-CUMALATIVE
- 4

USE WITH 22-26 AWG WIRE SIZE, .050 MAX INSULATION DIA., .015 MAX INSULATION WALL THICKNESS.
- 5

CONTACT IDENTIFICATION NUMBER "2" LOCATED IN THIS AREA.
- 6

.000050 MIN W.E. #1 GOLD ALLOY IN CONTACT AREA, .000050 - .000100 TIN IN AREA D, ALL OVER .000050 NICKEL.
- 7

ROHS 2002/95/EC COMPLIANT
- 8

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8	OBSOLETE	7 6	.400	.300	3	8	5-104305-4
		7 6	1.000	.900	9	20	5-104305-3
		7 6	1.700	1.600	16	34	5-104305-2
		7 6	.500	.400	4	10	5-104305-1
		1	.400	.300	3	8	104305-4
		1	1.000	.900	9	20	104305-3
		1	1.700	1.600	16	34	104305-2
		1	.500	.400	4	10	104305-1
			C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 11-20-87	Tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608				
DIMENSIONS: INCHES		CHK P de Jong 11-20-87					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME				
		PRODUCT SPEC 108-25018	RECEPTACLE ASSY, AMPMODU, MASS TERMINATION, DBL ROW, .100 X .100 CL, #22-#26 AWG WIRE				
		APPLICATION SPEC 114-25015					
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR:BLACK, CONTACTS: PHOS BRONZE	FINISH SEE TABLE	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=104305	RESTRICTED TO -	
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1	REV L1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-104305-2](#)