





P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER EO PI9555	7-11-07		RDR
	D	REVISED PER PCN E-20-009639	10JUL2020	DM	IG



SECTION A-A
CONDUCTOR WINGS



SECTION B-B
INSULATION WINGS

- 5 TIN PLATING MAY BE IN THIS REGION.
- 4 TIN PLATED REGION.
- 3 MATERIAL: .016 [0.41] THICK COPPER ALLOY.
2. WIRE RANGE: 14 AWG TO 12 AWG [2.0-4.0mm²]
INSULATION RANGE: $\varnothing .113 - .176$ [2.87-4.47]
- 1 GOLD PLATED REGION.

NOTES: UNLESS OTHERWISE SPECIFIED

TE INTERNAL PN	DEUTSCH PN	PLATING
1060-12-0144	1060-12-0144	Selective Au, Ni/Cu overall, Sn/Ni/Cu Wire Barrel
1060-12-0166	1060-12-0166	Selective Ni, Ni/Cu overall, Sn/Ni/Cu Wire Barrel

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MEYER 14NOV2000	TE Connectivity		
DIMENSIONS: INCH [mm]		CHK B. BYFORD 11JUL2007			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. REED 11JUL2007			
0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm .025$ [0.64] 4 PLC $\pm$ ANGLES $\pm$		PRODUCT SPEC 108-151000 APPLICATION SPEC 114-151002 WEIGHT .83 g			
MATERIAL 	FINISH SEE TABLE	CUSTOMER DRAWING	NAME STAMPED CONTACT PIN SIZE 12	SIZE A3	CAGE CODE 4AFU8
			DRAWING NO C-1060-12-01XX	RESTRICTED TO -	
			SCALE 5:1	SHEET 1 OF 1	REV D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1060-12-0144 \(Cut Strip\)](#) [1060-12-0144 \(Mouser Reel\)](#) [1060-12-0144 \(Loose Piece\)](#)