



Data Sheet

Typical Performance



Horizontal: 4 MHz/Div
 Vertical: 10 dB/Div




Horizontal: 1.2 MHz/Div
 Vertical: 1 dB/Div
 Vertical: 5 deg/Div


Specifications

Parameter	Unit	Minimum	Typical	Maximum
Center Frequency	MHz	69.8	70	70.2
Insertion Loss at F_o	dB	-	9.75	10.5
1 dB Bandwidth	MHz	8.4	8.6	-
3 dB Bandwidth	MHz	9	9.4	-
40 dB Bandwidth	MHz	-	13.9	14.5
Passband Ripple	dB	-	0.8	1
Phase Linearity (90% of 3dB Bandwidth)	deg	-	9.5	11.5
Group Delay Variation (90% of 3dB Bandwidth)	nsec	-	70	95
Absolute Delay	μ sec	-	1.05	-
Substrate Material	-	-	YZ LiNbO ₃	-
Temperature Coefficient	ppm/ $^{\circ}$ C	-	-94	-
Ambient Temperature	$^{\circ}$ C	-	25	-

Package Outline



Matching Configuration



$L1 = 150\text{nH}$, $L2 = 100\text{nH}$
 Nominal Source/Load Impedance = 50Ω
 Package Style SMP-53

11/29/99

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qorvo:](#)

[854664](#) [854664-EVB](#)