

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
				B14		ECR-12-021486 (Marking C to Q)	20DEC2012	UKo	JB
				C		ECR-13-014508	13OCT2015	UKo	Ak
				C 1		ECR-14-007162	21SET2017	AP	AK
				C 2		ECR-18-017686 (Add prod. site; PN List update)	07MAY2019	HC	LS

Order Number - ABCCCC

Portugal made:

A - Packing day

B - Shift (1=day, 2=night)

C - Lot number (sequential)

Austria Made:

A - Line (1...Line1)

B - Day (1...7, Monday=1, Tuesday=2)

C - Time(hhmm)

Other country made:

A - Year (first digit)

B - Year (second digit)

C - Lot number (sequential)

H Swiss made (until 2013)

PT Portugal made

Q China made (until 2016)

C China made (until 2012)

AT Austria made

Date code (YYWW)

Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM00..	00	1.5	3-1462037-7		3-1462037-5	
IM00NS	00N	1.5				1-1462038-0*
IM01..	01	3	1462037-1	4-1462037-0	1462037-4	
IM01B..	01B	3	4-1462039-5			
IM01C ..	01C	3	1462038-4			
IM01NS	01N	3				1-1462038-1
IM01N..L	01N	3				4-1462039-3
IM01P	01P	3	9-1462037-3			
IM02..	02	4.5	1462037-9	1-1462037-1	1-1462037-3	6-1462039-4
IM02..	02	4.5	8-1462039-1			
IM02..L	02	4.5	2-1462039-3			
IM02C ..	02C	4.5	1462038-1			
IM02D ..	02D	4.5	9-1462038-8			
IM02H..	02H	4.5	1-1462039-1			
IM02I..	02I	4.5	1462047-9	1462047-8		
IM02NS	02N	4.5				1-1462038-2

*obsolete

DRAWING ALIAS: IM0C-DOK17

DIMENSIONS:		DWN		MATERIAL		FINISH	
mm		HD 9121	21FEB2003	-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK	21FEB2003	TE Connectivity			
		HD 9121					
		APVD	21FEB2003				
		HD 9121					
PRODUCT SPEC		-		NAME IM-Relay Marking			
APPLICATION SPEC		-					
WEIGHT		-					
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		-		A 4	00779	C- 1462037-1	-
CUSTOMER DRAWING				SCALE	10:1	SHEET	1 OF 6
				REV C 2			

2000

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2000

REV C2

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)			
IM07C..	07C	24	1462039-2		1462039-1				
IM07D..	07D	24		7-1462039-4	7-1462039-2				
IM07NS	07N	24				1-1462038-7			
IM08I..	08I	2.4			1462047-3				
IM11..	11	3	9-1462038-5						
IM12..	12	4.5	1462039-3						
IM13..	13	5	1462039-4						
IM15..	15	9	8-1462039-5						
IM16..	16	12	1462039-5						
IM17..	17	24	1462039-6		4-1462039-6				
IM21..	21	3	2-1462039-6		1-1462039-5				
IM22..	22	4.5	2-1462039-7		2-1462039-8	8-1462039-9			
IM23..	23	5	2-1462039-9		3-1462039-0	6-1462039-7			
IM25..	25	9	3-1462039-5						
IM26..	26	12	3-1462039-1		3-1462039-2				
IM40..	40	1.5	5-1462037-1						
IM40D..	40D	1.5	8-1462039-4						
IM40NS	40N	1.5				1-1462038-8			
IM41..	41	3	5-1462037-4	5-1462037-5	5-1462037-3				
IM41C..	41C	3	4-1462039-2						
IM41D..	41D	3	6-1462039-8						
IM41NS	41N	3				1-1462038-9			
IM42..	42	4.5	3-1462037-1	5-1462037-7	5-1462037-6				
IM42C..	42C	4.5	4-1462039-1						
IM42D..	42D	4.5	1-1462039-9						
*obsolete DRAWING ALIAS: IM0C-DOK17									
DIMENSIONS:		DWN	21FEB2003	MATERIAL		FINISH			
mm		HD 9121		-		-			
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK	21FEB2003	 TE Connectivity					
		HD 9121							
		APVD	21FEB2003						
0 PLC ±-		PRODUCT SPEC		NAME		IM-Relay Marking			
1 PLC ±-		-							
2 PLC ±-		APPLICATION SPEC							
3 PLC ±-		-							
4 PLC ±-									
ANGLES ±-		WEIGHT		SIZE		CAGE CODE		DRAWING NO	
		-		A 4		00779		C- 1462037-1	
								RESTRICTED TO	
								-	
		CUSTOMER DRAWING		SCALE		10:1		SHEET 3 OF 6	
								REV C 2	

2000

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

© COPYRIGHT 2000



0 PLC ±-


1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HJ	-		-	SEE SHEET 1	-	-	-


Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM42DNS	42D	4.5				1-1462039-6
IM42NS	42N	4.5				2-1462038-0
IM42P..	42P	4.5	5-1462039-7			
IM42PNS	42P	4.5				7-1462039-8
IM43..	43	5	5-1462037-9	6-1462037-0	5-1462037-8	
IM43C ..	43C	5	9-1462038-7			
IM43NS	43N	5				2-1462038-1
IM44..	44	6	6-1462037-2	6-1462037-3	6-1462037-1	
IM44NS	44N	6				2-1462038-2
IM45..	45	9	6-1462037-4	6-1462037-5	3-1462037-2	
IM45I..	45I	9	1462047-5			
IM45NS	45	9				2-1462038-3
IM46..	46	12	6-1462037-7	6-1462037-8	6-1462037-6	
IM46C ..	46C	12	8-1462039-0			
IM46NS	46N	12				2-1462038-4
IM46PNS	46P	12				6-1462039-1
IM47..	47	24	7-1462037-0		6-1462037-9	
IM47D ..	47D	24		7-1462039-5		
IM47NS	47N	24				2-1462038-5
IM48..	48	2.4	1462039-8			
IM48D ..	48D	2.4	1462039-9			
IM48C ..	48C	2.4	9-1462039-0			
IM48I..	48I	2.4	1462047-1			
IM49I..	49I	2	1462047-4			

*obsolete

DRAWING ALIAS: IMOC-DOK17

DIMENSIONS:		DWN	HD 9121	21FEB2003	MATERIAL		-	FINISH		-		
mm		CHK	HD 9121	21FEB2003	TE Connectivity							
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		APVD	HD 9121	21FEB2003								
		PRODUCT SPEC		NAME IM-Relay Marking								
		APPLICATION SPEC										
		WEIGHT					SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
0 PLC ±-		-		A 4	00779	C- 1462037-1		-				
1 PLC ±-												
2 PLC ±-												
3 PLC ±-												
4 PLC ±-												
ANGLES ±-												
		CUSTOMER DRAWING			SCALE	10:1	SHEET	4	OF	6	REV	C 2

2000 RELEASED FOR PUBLICATION ALL RIGHTS RESERVED. © COPYRIGHT 2000	LOC HJ	DIST -	REVISIONS					
			P	LTR	DESCRIPTION	DATE	DWN	APVD
				-	SEE SHEET 1	-	-	-
	Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)	
	IM61..	61	3	7-1462039-7				
	IM68..	68	2.4	8-1462039-2				
	IMB01C ..	B01C	3	1462041-1		1462041-4		
	IMB02C ..	B02C	4.5	1462041-2				
	IMB03C ..	B03C	5	1462041-7				
	IMB03C ..E	B03C	5	1-1462041-8				
	IMB04C ..	B04C	6	1462041-9		1-1462041-1		
	IMB05C ..	B05C	9	1-1462041-0		1-1462041-2		
	IMB06C ..	B06C	12	1462041-3		1462041-6		
	IMB07C ..	B07C	24	1-1462041-3		1-1462041-4		
	IMB32B..	B32B	4.5	2-1462041-0				
	IMB33B..	B33B	5	1-1462041-9				
	IMB41C ..	B41C	3	1-1462041-7				
	IMB42C ..	B42C	4.5	1-1462041-6		1-1462041-5		
	*obsolete							
DIMENSIONS:		DWN HD 9121	21FEB2003	MATERIAL		DRAWING ALIAS: IM0C-DOK17		
mm		CHK HD 9121	21FEB2003	FINISH		-		
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		APVD HD 9121	21FEB2003	 TE Connectivity				
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC						
		APPLICATION SPEC		IM-Relay Marking				
		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		-		A 4	00779	©- 1462037-1	-	
CUSTOMER DRAWING				SCALE	10:1	SHEET	5 OF 6	REV C 2

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)			
IMC01..	C01	3	1462042-1		1462042-4				
IMC02..	C02	4.5	1462042-2		1462042-5				
IMC03..	C03	5	1462042-8		1462042-7				
IMC06..	C06	12	1462042-3		1462042-6				
IMC07..	C07	24	1-1462042-1		1-1462042-2				
IMC02C..	C02C	4.5	1-1462042-0						
IMC03C..	C03C	5	1-1462042-5						
IMC06C..	C06C	12	1462042-9		1-1462042-4				
IMC41C..	C41C	3			1-1462042-3				
IME01..	E01	3	1462043-1		1462043-5				
IME02..	E02	4.5	1462043-2		1462043-6				
IME03..	E03	5	1462043-3		1462043-7				
IME06..	E06	12	1462043-4		1462043-8				
IMF61..	F61	3	1462048-3						
IMF68..	F68	2.4	1-1462048-0						
THIS DRAWING IS UNPUBLISHED. 2000 RELEASED FOR PUBLICATION ALL RIGHTS RESERVED. © COPYRIGHT 2000 *obsolete DRAWING ALIAS: IM0C-DOK17									
DIMENSIONS:		DWN HD 9121 21FEB2003		MATERIAL		FINISH			
mm		CHK HD 9121 21FEB2003		-		-			
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		APVD HD 9121 21FEB2003		 TE Connectivity					
0 PLC ±-		PRODUCT SPEC							
1 PLC ±-		-							
2 PLC ±-		APPLICATION SPEC		NAME					
3 PLC ±-		-		IM-Relay Marking					
4 PLC ±-		-		SIZE		CAGE CODE		DRAWING NO	
ANGLES ±-		WEIGHT		A 4		00779		C- 1462037-1	
		CUSTOMER DRAWING		SCALE		10:1		SHEET 6 OF 6	
								REV C 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[IM01JR](#)