




- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- 2 TRUE POSITION TOLERANCE OF THE POSTS TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 3 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING.
- 4 FINISH: 0.000127 [.000005] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD ON SOLDER TAIL ALL OVER 0.00127 [.000050] NICKEL.
- 5 FINISH: 0.000127 [.000005] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN ON SOLDER TAIL ALL OVER 0.00127 [.000050] NICKEL.
- 6 HIGH TEMPERATURE CONFIGURATION.

6	5	3	NONE	1.684	1.600	16	33	34	5-146223-1
	4	3	NONE	1.684	1.600	16	33	34	146223-1
REMARKS	PLATING	ROW N	ROW M	C	B	A	NO.OF ACTIVE POSN.	NO. OF POSN.	ASSEMBLY PART NUMBER
		POST OMITTED							

RECOMMENDED HOLE LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
HOUSING: FLAME RETARDANT THERMOPLASTIC,
COLOR: BLACK
POSTS: COPPER ALLOY

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.13[.005]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	0° 30'

FINISH
SEE TABLE

DWN
T. HOFFMAN
CHK
G.DUBNICZKI
APVD
G.DUBNICZKI
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
-
CUSTOMER DRAWING

6-3-95
25-3-95
25-3-95

NAME
TE Connectivity
HEADER ASSEMBLY, MOD II, BREAKAWAY,
DOUBLE ROW, .100 X.100, VERTICAL,
.025 SQ.POST, SELECT LOAD

SIZE
A2
CAGE CODE
00779
DRAWING NO
C=146223
SCALE
4:1
SHEET
1 OF 1
REV
H

1471-9 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146223-1](#)