



LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECO-11-004820	11MAR11	RK	HMR

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
4. HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
5. FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.
6. FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.



RECOMMENDED HOLE LAYOUT

5	101.19 [3.984]	99.06 [3.900]	39	40	4-146472-0
	98.65 [3.884]	96.52 [3.800]	38	39	3-146472-9
	96.11 [3.784]	93.98 [3.700]	37	38	3-146472-8
	93.57 [3.684]	91.44 [3.600]	36	37	3-146472-7
	91.03 [3.584]	88.90 [3.500]	35	36	3-146472-6
	88.49 [3.484]	86.36 [3.400]	34	35	3-146472-5
	85.95 [3.384]	83.82 [3.300]	33	34	3-146472-4
	83.41 [3.284]	81.28 [3.200]	32	33	3-146472-3
	80.87 [3.184]	78.74 [3.100]	31	32	3-146472-2
	78.33 [3.084]	76.20 [3.000]	30	31	3-146472-1
	75.79 [2.984]	73.66 [2.900]	29	30	3-146472-0
	73.25 [2.884]	71.12 [2.800]	28	29	2-146472-9
	70.71 [2.784]	68.58 [2.700]	27	28	2-146472-8
	68.17 [2.684]	66.04 [2.600]	26	27	2-146472-7
	65.63 [2.584]	63.50 [2.500]	25	26	2-146472-6
	63.09 [2.484]	60.96 [2.400]	24	25	2-146472-5
	60.55 [2.384]	58.42 [2.300]	23	24	2-146472-4
	58.01 [2.284]	55.88 [2.200]	22	23	2-146472-3
	55.47 [2.184]	53.34 [2.100]	21	22	2-146472-2
	52.93 [2.084]	50.80 [2.000]	20	21	2-146472-1
	50.39 [1.984]	48.26 [1.900]	19	20	2-146472-0
	47.85 [1.884]	45.72 [1.800]	18	19	1-146472-9
	45.31 [1.784]	43.18 [1.700]	17	18	1-146472-8
	42.77 [1.684]	40.64 [1.600]	16	17	1-146472-7
	40.23 [1.584]	38.10 [1.500]	15	16	1-146472-6
	37.69 [1.484]	35.56 [1.400]	14	15	1-146472-5
	35.15 [1.384]	33.02 [1.300]	13	14	1-146472-4
	32.61 [1.284]	30.48 [1.200]	12	13	1-146472-3
	30.07 [1.184]	27.94 [1.100]	11	12	1-146472-2
	27.53 [1.084]	25.40 [1.000]	10	11	1-146472-1
	24.99 [.984]	22.86 [.900]	9	10	1-146472-0
	22.45 [.884]	20.32 [.800]	8	9	146472-9
19.91 [.784]	17.78 [.700]	7	8	146472-8	
17.37 [.684]	15.24 [.600]	6	7	146472-7	
14.83 [.584]	12.70 [.500]	5	6	146472-6	
12.29 [.484]	10.16 [.400]	4	5	146472-5	
9.75 [.384]	7.62 [.300]	3	4	146472-4	
7.21 [.284]	5.08 [.200]	2	3	146472-3	
4.67 [.184]	2.54 [.100]	1	2	146472-2	
2.13 [.084]	— —	—	1	146472-1	
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG E. BRANDBERG	13MAR97	 TE Connectivity				
		CHK G. HUBNICZKI	13MAR97					
		APP'D G. HUBNICZKI	13MAR97					
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME HEADER ASSEMBLY, MOD II, STACKING, SINGLE ROW, .025 SUB.POST, UNSHROUDED				
		PRODUCT SPEC						
		APPLICATION SPEC						
		FINISH						
MATERIAL		SEE TABLE	WEIGHT	—	SIZE A1	CAGE CODE 00779	DRAWING NO C146472	RESTRICTED TO —
CUSTOMER DRAWING		SCALE	4:1	SHEET				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-146472-9](#)