


### General Description

The QPQ1286 is a high performance Bulk Acoustic Wave (BAW) filter designed to meet the strict LTE rejection requirements for use in B40, Sub-Band 2320-2370 MHz


QPQ1286 is specifically designed to meet the high performance expectations of insertion loss and rejection for LTE TDD systems under all operating conditions.

The QPQ1286 uses common module packaging techniques to achieve the industry standard 2.0 x 1.6 x 0.73 mm footprint.



3 Pin 2 x 1.6 mm leadless SMT Package

### Functional Block Diagram



Top View

### Pin Configuration

Pin No.	Label
1	RF in
2	RF out
3	Ground

### Product Features

- Highly selective BAW filter achieving low insertion loss over full bandwidth and operating conditions
- Performance -20 to +90 °C
- Excellent Wi-Fi rejection
- Single-ended operation
- No Matching required for operation at 50 Ω
- High Power Handling Compatible for Small Cells
- Small Size
- RoHS compliant (2002/95/EC), Pb-free

### Applications

- For Band 40 TD-LTE applications
- 2320 – 2370 MHz Sub-Band
- For Small Cells Base Stations

### Ordering Information

Part No.	Description
QPQ1286	2,500 pieces on a 7" reel (standard)
QPQ1286-PCB	Evaluation Board

## Absolute Maximum Ratings

Parameter	Rating
Storage Temperature <sup>(1)</sup>	-40 to +125 °C
Operating Temperature <sup>(2)</sup>	-40 to +105°C

<sup>(1)</sup> Operation of this device outside the parameter ranges given may cause permanent damage.

<sup>(2)</sup> Device will function but it is not guaranteed to meet electrical specifications.

## Electrical Specifications <sup>(1)</sup>

Test conditions unless otherwise specified. Temperature Range: -20 to +90 °C

Parameter	Conditions	Min	Typ	Max	Units
Maximum Insertion Loss	2320.0 – 2370.0	-	1.9	2.8	dB
Input / Output VSWR	2320.0–2370.0 MHz	-	1.6:1	2.0:1	-
Input / Output Return Loss	2320.0–2370.0 MHz	9.5	14	-	dB
Amplitude Variation <sup>(2)</sup>	2320.0–2370.0 MHz	-	0.9	1.5	dB
Group Delay Ripple <sup>(3)</sup>	2320.0–2370.0 MHz	-	7	25	ns p-p
Phase Ripple <sup>(4)</sup>	2320.0–2370.0 MHz	-	11	35	° p-p
Attenuation in WIFI Band <sup>(5)</sup> (Average per Channel using 802.11b Spectrum mask)	2405 – 2440 MHz (Channel 1 - 7) 2440 – 2480 MHz (Channel 8 - 14)	42 38	47 40	- -	dB
Attenuation <sup>(6)</sup>	10–960 MHz	41	45	-	dB
	961–1709 MHz	31	33	-	
	1710–1880 MHz	30	32	-	
	1920–2170 MHz	30	32	-	
	2171–2295 MHz	10	23	-	
	2395–2405 MHz	10	17	-	
	2480–2500 MHz	36	38	-	
	2500–3660 MHz	32	34	-	
	3750–4600 MHz	34	37	-	
	4600–4800 MHz	43	49	-	
4901–6000 MHz	25	29	-		
6001–8000 MHz	30	34	-		
2 <sup>nd</sup> Harmonic	Pin = +29 dBm (2320-2370 MHz)	65	86	-	dBc
Source/Load Impedance <sup>(7)</sup>	Single-ended	-	50	-	Ω

Notes:

- All specifications are based on the QORVO schematic for the main reference design shown on page 3.
- Amplitude Variation is defined as the difference between the lowest loss and the highest loss within defined frequency points.
- This is defined as the worst difference between a peak and adjacent valley within defined frequency points.
- Typical values are and average of 20 pieces measured at a temperature of 25 C.
- WIFI attenuation is calculated by averaging |S21| in dB referenced to ZERO dB for each measured point within defined frequency range.
- Attenuation is referenced to ZERO dB.
- This is the optimum impedance in order to achieve the performance shown.







## Life Test

Conditions	Rating
+29 dBm, LTE SIGNAL PAR = 8dB, 5MHz, 16 QAM + 90 °C	>25000 hrs.



Power rating is valid when Power is injected into Pin 1

### Performance Plots

Test conditions unless otherwise noted: Temp.= +25 °C



## Evaluation Board



**Notes:**


1. Top, middle & bottom layers: 1/2 oz copper, Substrates: FR4 dielectric, .062" thick, Finish plating: Nickel: 3-8 μm thick, Gold: .03-.2 μm thick, Hole plating: Copper min .0008 μm thick

## Bill of Material

Reference Des.	Value	Description	Manuf.	Part Number
U1	N/A	Band 40 BAW Filter	Qorvo	QPQ1286
PCB	N/A	3-layer	Multiple	1132983
SMA	N/A	SMA connector	Radiall	9602-1111-018


## PCB Mounting Pattern

Standard T/R size = 2500 units/ 7" reel. All dimensions are in millimeters



## Package Marking and Dimensions


Body: Al<sub>2</sub>O<sub>3</sub> ceramic  
 Lid: Kovar, Au over Ni plating  
 Terminations: Au plating 0.5 - 1.0µm, over a 2-6µm Ni plating




- Notes:
1. All dimensions are in millimeters. Angles are in degrees.
  2. Dimension and tolerance formats conform to ASME Y14.4M-1994.
  3. The terminal #1 identifier and terminal numbering conform to JESD 95-1 SPP-012.

## Tape and Reel Information – Carrier and Cover Tape Dimensions

Tape and reel specifications for this part are also available on the Qorvo website.  
 Standard T/R size = 2500 pieces on a 7" reel.




Feature	Measure	Symbol	Size (in)	Size (mm)
Cavity	Length	A0	0.092	2.34
	Width	B0	0.112	2.85
	Depth	K0	0.043	1.10
	Pitch	P1	0.157	4.00
Centerline Distance	Cavity to Perforation - Length Direction	P2	0.079	2.00
	Cavity to Perforation - Width Direction	F	0.138	3.50
Cover Tape	Width	C	0.213	5.40
Carrier Tape	Width	W	0.315	8.00



## Tape and Reel Information – Reel Dimensions

Tape and reel specifications for this part are also available on the Qorvo website.  
 Standard T/R size = 2500 pieces on a 7" reel.



Feature	Measure	Symbol	Size (in)	Size (mm)
Flange	Diameter	A	6.969	177.0
	Thickness	W2	0.559	14.2
	Space Between Flange	W1	0.346	8.8
Hub	Outer Diameter	N	2.283	58.0
	Arbor Hole Diameter	C	0.512	13.0
	Key Slit Width	B	0.079	2.0
	Key Slit Diameter	D	0.787	20.0

## Handling Precautions

Parameter	Rating	Standard
ESD – Human Body Model (HBM)	Class TBD	ESDA / JEDEC JS-001
ESD – Charged Device Model (CDM)	Class TBD	ESDA / JEDEC JS-002
MSL – Moisture Sensitivity Level	Level 3	IPC/JEDEC J-STD-020



Caution!  
ESD-Sensitive Device

## Solderability

Compatible with both lead-free (260°C max. reflow temp.) and tin/lead (245°C max. reflow temp.) soldering processes. Solder profiles available upon request.

Contact plating: Au over Ni

## RoHS Compliance

This part is compliant with EU 2002/95/EC RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment). This product also has the following attributes:

- Lead Free
- Halogen Free (Chlorine, Bromine)
- Antimony Free
- TBBP-A (C<sub>15</sub>H<sub>12</sub>Br<sub>4</sub>O<sub>2</sub>) Free
- PFOS Free
- SVHC Free
- Qorvo Green



## Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Tel: 1-844-890-8163

Web: [www.qorvo.com](http://www.qorvo.com)

Email: [customer.support@qorvo.com](mailto:customer.support@qorvo.com)

For technical questions and application information: Email: [sicapplications.engineering@qorvo.com](mailto:sicapplications.engineering@qorvo.com)

## Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.**

Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

Copyright 2016 © Qorvo, Inc. | Qorvo is a registered trademark of Qorvo, Inc.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qorvo:](#)

[QPQ1286SR](#) [QPQ1286TR7](#)