




F	LTR	DESCRIPTION	DATE	DWN	APVD
C		REVISED PER ECO-17-015513	19DEC2017	PHM	CT

D

C

B

A



D

C

B

A

1. CONNECTOR DIMENSIONS ARE PER ARINC 600 SPECIFICATION

2. KEYING SHOWN IN POSITION "01" FOR REFERENCE ONLY. SEE TABLE FOR KEYING POSITION. FOR POSITION "00" KEYING SHIPPED UNASSEMBLED.

COMPONENT	MATERIAL	FINISH
SHELL	DIE CAST ALUMINUM PER ASTM-B-85	ELECTROLESS NICKEL PER MIL-C-26074,
RETENTION PLATES	ALUMINUM ALLOY PER ASTM-B-209	ELECTROLESS NICKEL PER MIL-C-26074,
SCREWS	STEEL OR STAINLESS STEEL	PASSIVATED
POLARIZING POSTS	ZINC ALLOY PER ASTM-B-86	ELECTROLESS NICKEL PER MIL-C-26074,
INSERTS	THERMOSET	-
EMI GROUND SPRING	BERYLLIUM COPPER 172 (ALLOY 29)	ELECTRODEPOSITED NICKEL PER QQ-N-290
GROMMET	FLUOROSILICONE	-
POLARIZING POST RETAINING PLATE	ALUMINUM ALLOY PER ASTM-B-209	BLUE ANODIZED PER MIL-A-8625

08	MODULE A 208262-3 (SIZE 22 PIN CONTACT; QTY=150) MODULE B 208267-2 (SIZE 22 SOCKET CONTACT; QTY=60) MODULE C 208267-2 (SIZE 20 SOCKET; QTY=24) 208270-2 (SIZE 16 SOCKET; QTY=10)		1663346-1
	KEYING POSITION	CONTACTS INCLUDED NOT INSTALLED	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			
DIMENSIONS: INCHES		DWN C.C.THOMAS 10-25-04 CHK K.HOGAN 10-26-04 APVD K.HOGAN 10-26-04 PRODUCT SPEC	NAME
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC	SIZE
MATERIAL SEE TABLE		WEIGHT	RESTRICTED TO
SEE TABLE		CUSTOMER DRAWING	SCALE 1:1 SHEET 1 OF 1 REV C



TE Connectivity

PLUG ASSY,SIZE 2,ARR 262ARINC 600,
(150/60/34)
NIC66HN262F08AAO

A1 00779 1663346

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1663346-1](#)