

2		1					
LOC	DIST	REVISIONS					
HB	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E	REMOVED THE RIB ON BASE TO CASE ECO-15-011310	29-Sep-15	YS.H	SM.C
			E1	ADD NEW PN ECO-19-017316	13-Nov-19	WQ.Y	K.T

TE





T77V1D10-12-02

10A 120V~

10A 30V= Res.

P&B CHINA

LOT No



CONNECTION FIGURE




FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Fu Bo	TE TE Connectivity				
		CHK					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD CH,HSU	NAME T77*1D10-** CUSTOMER DRAWING				
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC -					
		APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL -	FINISH -	WEIGHT -	A3	00779	C= 1-1393194-9	-	
CUSTOMER DRAWING					SCALE 5:1	SHEET 1 of 2	REV E1

LOC	DIST	REVISIONS				
HB	—	P	LTR	DESCRIPTION	DATE	DWN
			—	SEE SHEET 1	—	—

107-84030	4-1393194-2	T77V1D10-12	T77V1D10-12	r
107-79010	3-1393194-8	T77V1D10-24-01	T77V1D10-24-01	q
107-79010	2-1393194-2	T77V1D10-48	T77V1D10-48	p
107-79010	2-1393194-1	T77V1D10-24	T77V1D10-24	o
107-79010	2-1393194-0	T77V1D10-18	T77V1D10-18	n
107-79010	1-1393194-9	T77V1D10-12	T77V1D10-12	m
107-79010	1440005-1	T77V1D10-09	T77V1D10-09	l
107-79010	8-1440009-1	T77V1D10-06	T77V1D10-06	k
107-79010	1-1393194-8	T77V1D10-05	T77V1D10-05	j
107-79010	1-1393194-7	T77V1D10-03	T77V1D10-03	i
107-79010	9-1440004-7	T77S1D10-48	T77S1D10-48	h
107-79010	1-1393194-0	T77S1D10-24	T77S1D10-24	g
107-79010	9-1440004-5	T77S1D10-18	T77S1D10-18	f
107-79010	1393194-9	T7S1D10-12	T77S1D10-12	e
107-79010	1393194-8	T77S1D10-09	T77S1D10-09	d
107-79010	9-1440004-2	T77S1D10-06	T77S1D10-06	c
107-79010	1393194-7	T77S1D10-05	T77S1D10-05	b
107-79010	1393194-6	T77S1D10-03	T77S1D10-03	a
PACKAGE SPEC.	PART NO	DESCRIPTION	PART A	TYPE

RELAY TYPE

NOTE
1.LOT NO SYSTEM AS FOLLOWING:



- 2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;
3.FOR THE TIN-PLATING OF THE PINS:
+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.
+0.5mm FOR LENGTH.
4.MARKING FROM INK TO LASER AND USING WELDED CONTACT

5.ADD LOT NO. SYSTEM AS FOLLOWING;



- I, DIGITS FOR DAY OF THE WEEK
1...MONDAY IN THIS WEEK;
2...TUESDAY IN THIS WEEK;
.....
7...SUNDAY IN THIS WEEK
II, DIGITS FOR SHIFT OF THE DAY
1...DAY SHIFT IN THIS DAY;
2...NIGHT SHIFT IN THIS DAY;
III, ONE CHARACTER DISTINGUISH THE LINE IDENTITY, SUCH AS: A,B,.....Z

		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
		MW79	MAGNETIC WIRE	14
94V-0		P.B.T	CASE	13
94V-0		P.B.T	BASE	12
94VHB		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		P.P.S	CARD	9
		Ag ALLOY	MOVABLE CONTACT	8
		Ag	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	CU ALLOY	NO.TERMINAL	5
	SOLDER DIP	CU ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —

FINISH
—

DWN
Fu Bo

CHK
Xiaoning.Zhang

APVD
CH,HSU

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

TE Connectivity

NAME
—
T77*1D10-** CUSTOMER DRAWING

SIZE
A3

CAGE CODE
00779

DRAWING NO
C= 1-1393194-9

RESTRICTED TO
—

SCALE
5:1

SHEET
2 of 2

REV
E1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T77V1D10-24](#)