

PROJECT NR.:				REVISIONS			
PRJ-14-000000805				AENDERUNGEN	DATE	DWN	APVD
P	LTR	DESCRIPTION		BESCHREIBUNG			
	A1	NEW DRAWING			08MAY2014	YR	CS




1 MATERIAL: ITEM NO. 1: HOUSING - CUZn (BRASS NICKEL PLATED)
ITEM NO. 2: CONTACT BODY - PA
ITEM NO. 3: CONTACT - CuZn (brass)
CONTACT FINISH - Au (gold)

2 ALL DIMENSIONS ARE FOR NOMINAL REFERENCE ONLY UNLESS OTHERWISE STATED

3 MEASUREMENT REFERENCE ONLY

4 PACKAGING: 1 PIECE IN A BAG



TECHNICAL DATA	0-2120958-1	1-2120958-1
RATED VOLTAGE	60V	30V
RATED IMPULSE VOLTAGE	800V	800V
POLLUTION DEGREE	3	3
OVERVOLTAGE CATEGORY	II	II
MATERIAL GROUP	II	II
RATED CURRENT	4A	4A
VOLUME RESISTIVITY	≤ 3mΩ	≤ 3mΩ
DEGREE OF PROTECTION	IP67	IP67
UPPER TEMPERATURE	+85 °C	+85 °C
LOWER TEMPERATURE	-40 °C	-40 °C



PIN ARRANGEMENT (SCALE 5:1)

0-2120958-1

1-2120958-1



1-1 AS SHOWN
WIE GEZEICHNET

24 / 0.25mm ²	1	4	1-2120958-1
24 / 0.25mm ²	1	3	0-2120958-1
WIRES AWG / mm ²	MATERIAL	NUMBER OF POLES	TE-PART-NO.

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).							
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).				DWN YASHKUMAR 08MAY2014 CHK M. STRELOW 08MAY2014 APVD C. SCHRETLINGER 08MAY2014			
DIMENSIONS: MASSEINHEITEN: (MM)		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN		PRODUCT SPEC PRODUKTSPEZ.		NAME	
1 PLC ±		2 PLC ±		3 PLC ±		4 PLC ±	
ANGLES/WINKEL ±		FINISH/OBERFLÄCHE/FARBE		WEIGHT GEWICHT		SIZE	
-		-		-		A2	
-		-		Customer Drawing		/KUNDENZEICHNUNG	
				SCALE MASSSTAB		SHEET BLATT	
				5:1		1 OF 1	
				REV		A1	

SIZE ISO 14405

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2120958-1](#)