

7x 6

7x 6

A

A

7x 6

7x 6

A

A-A

Step 2

PN 0-2141630-1
EXPLODE VIEW

Step 1

PN 0-2141630-1
AS SHOWN

0-2141630-1	B	2POS.MCON-1.2. REC HSG.ASSY	1	2. LOCK	PA6-(GF+GB)30	35%	RED/ rot	3
			1	CABLE ASSY 1 POS. MCON 1.2. HV-INTERLOCK	-	-	-	2
			1	5POS. AMP MCP 6.3/4.8K. REC HSG	PA66-GF30	20%	BLACK/ schwarz	1
TE-ASSY-NO.	REV	DESCRIPTION	QTY	DESCRIPTION	MATERIAL	MAX. REGRIND ALLOWED	COLOR	ITEM Pos.
COMPONENT								

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT.
BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).

DIMENSIONS:
MASSE IN MM

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN

0 PLC ± DIN ISO
1 PLC ± 2768-mK
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES/WINKEL ±
FINISH/OBERFLÄCHE/FARBE

MATERIAL

-

-

-

DWN
Maithreya K.P.

CHK
F. Wittrock

APVD
A. Ketteler

030CT2013

20DEC2013

20DEC2013

PRODUCT SPEC
108-94235

APPLICATION SPEC
114-94114

WEIGHT
10.2g

Customer Drawing

NAME
RECEPTACLE HSG. ASSY, HV CONNECTOR
Kontaktgehäuse Baugruppe, HV Stecker

SIZE
A2

CAGE CODE
00779

DRAWING NO.
C=2141630

RESTRICTED TO
NUR FÜR

SCALE
MASSSTAB 2:1

SHEET
BLATT 1

OF
VON 1

REV
B1

TE Connectivity

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2141630-1](#)