










8				7				6			
VITE PRAMĀNĀS PĀRBAUDĪŠANĀS PROBĒS, IERĒDZĪTĀJĀS PĀRBAUDĪŠANĀS COPYRIGHT 2011				PĒRBAUDĪŠANĀS PĒRBAUDĪŠANĀS PĒRBAUDĪŠANĀS PĒRBAUDĪŠANĀS PĒRBAUDĪŠANĀS PĒRBAUDĪŠANĀS				PĒRBAUDĪŠANĀS PĒRBAUDĪŠANĀS PĒRBAUDĪŠANĀS PĒRBAUDĪŠANĀS PĒRBAUDĪŠANĀS PĒRBAUDĪŠANĀS			
ALL INFORMATION IS UNCLASSIFIED											
A	5-2177053-2	A	95.1	1	0-2208243-1	-	CPA, HVPB00 CPA, HVPB00	1.08	RED / Rot SIM. / aehnlich RAL 3000	6	○
				1	0-2208242-1	-	CPA-ADAPTER CPA-Adapter	3.96	DUSTY-GREY / Staubgrau SIM. / aehnlich RAL 7037	5	
				1	0-2177055-1	-	LEVER, 2POS, 180 DEG Spannhebel, 2pos, 180 Grad	19.8	BLACK / schwarz RAL 9005 (9011)	4	
				1	-	0-2177056-1	2POS, MC0N-1.2, REC HSG, 180 DEG, Assy 2pot, MC0N-1.2, Dichtungshalter-Assy, 180 Grad	-	-	3	
				1	0-2141152-1	-	RADIAL SEAL 23.9x43.3 Radialdichtung , 90 Grad	3.2	NATURAL RAL 9001	2	
				1	5-2177054-1	-	2POS, 8MM HV. REC HSG, 180 DEG, SEALED 2pot Gehaeuse, 8mm HV. REC HSG, 180 Grad, gedichtet	62	DUSTY-GREY / Staubgrau SIM. / aehnlich RAL 7037	1	○
A	5-2177053-1	A	95.1	1	0-2208243-1	-	CPA, HVPB00 CPA, HVPB00	1.08	RED / Rot SIM. / aehnlich RAL 3000	6	△
				1	0-2208242-1	-	CPA-ADAPTER CPA-Adapter	3.96	DUSTY-GREY / Staubgrau SIM. / aehnlich RAL 7037	5	
				1	0-2177055-1	-	LEVER, 2POS, 180 DEG Spannhebel, 2pos, 180 Grad	19.8	BLACK / schwarz RAL 9005 (9011)	4	
				1	-	0-2177056-1	2POS, MC0N-1.2, REC HSG, 180 DEG, Assy 2pot, MC0N-1.2, Dichtungshalter-Assy, 180 Grad	-	-	3	
				1	0-2141152-1	-	RADIAL SEAL 23.9x43.3 Radialdichtung , 90 Grad	3.2	NATURAL RAL 9001	2	
				1	5-2177054-1	-	2POS, 8MM HV. REC HSG, 180 DEG, SEALED 2pot Gehaeuse, 8mm HV. REC HSG, 180 Grad, gedichtet	62	DUSTY-GREY / Staubgrau SIM. / aehnlich RAL 7037	1	△
B	1-2177053-4	B	95.1	1	0-2208243-1	-	CPA, HVPB00 CPA, HVPB00	1.08	RED / Rot SIM. / aehnlich RAL 3000	6	○
				1	0-2208242-1	-	CPA-ADAPTER CPA-Adapter	3.96	DUSTY-GREY / Staubgrau SIM. / aehnlich RAL 7037	5	
				1	0-2177055-2	-	LEVER, 2POS, 180 DEG Spannhebel, 2pos, 180 Grad	19.8	WHITE / weiss RAL 9010 (9011)	4	
				1	-	0-2177056-1	2POS, MC0N-1.2, REC HSG, 180 DEG, Assy 2pot, MC0N-1.2, Dichtungshalter-Assy, 180 Grad	-	-	3	
				1	0-2141152-1	-	RADIAL SEAL 23.9x43.3 Radialdichtung , 90 Grad	3.2	NATURAL RAL 9001	2	
				1	0-2177054-2	-	2POS, 8MM HV. REC HSG, 180 DEG, SEALED 2pot Gehaeuse, 8mm HV. REC HSG, 180 Grad, gedichtet	62	ORANGE RAL 2003	1	○
B	1-2177053-3	B	95.1	1	0-2208243-1	-	CPA, HVPB00 CPA, HVPB00	1.08	RED / Rot SIM. / aehnlich RAL 3000	6	△
				1	0-2208242-1	-	CPA-ADAPTER CPA-Adapter	3.96	DUSTY-GREY / Staubgrau SIM. / aehnlich RAL 7037	5	
				1	0-2177055-2	-	LEVER, 2POS, 180 DEG Spannhebel, 2pos, 180 Grad	19.8	WHITE / weiss RAL 9010 (9011)	4	
				1	-	0-2177056-1	2POS, MC0N-1.2, REC HSG, 180 DEG, Assy 2pot, MC0N-1.2, Dichtungshalter-Assy, 180 Grad	-	-	3	
				1	0-2141152-1	-	RADIAL SEAL 23.9x43.3 Radialdichtung , 90 Grad	3.2	NATURAL RAL 9001	2	
				1	0-2177054-2	-	2POS, 8MM HV. REC HSG, 180 DEG, SEALED 2pot Gehaeuse, 8mm HV. REC HSG, 180 Grad, gedichtet	62	ORANGE RAL 2003	1	△
A	1-2177053-2	B	95.1	1	0-2208243-1	-	CPA, HVPB00 CPA, HVPB00	1.08	RED / Rot SIM. / aehnlich RAL 3000	6	○
				1	0-2208242-1	-	CPA-ADAPTER CPA-Adapter	3.96	DUSTY-GREY / Staubgrau SIM. / aehnlich RAL 7037	5	
				1	0-2177055-1	-	LEVER, 2POS, 180 DEG Spannhebel, 2pos, 180 Grad	19.8	BLACK / schwarz RAL 9005 (9011)	4	
				1	-	0-2177056-1	2POS, MC0N-1.2, REC HSG, 180 DEG, Assy 2pot, MC0N-1.2, Dichtungshalter-Assy, 180 Grad	-	-	3	
				1	0-2141152-1	-	RADIAL SEAL 23.9x43.3 Radialdichtung , 90 Grad	3.2	NATURAL RAL 9001	2	
				1	0-2177054-1	-	2POS, 8MM HV. REC HSG, 180 DEG, SEALED 2pot Gehaeuse, 8mm HV. REC HSG, 180 Grad, gedichtet	62	ORANGE RAL 2003	1	○
A	1-2177053-1	B	95.1	1	0-2208243-1	-	CPA, HVPB00 CPA, HVPB00	1.08	RED / Rot SIM. / aehnlich RAL 3000	6	△
				1	0-2208242-1	-	CPA-ADAPTER CPA-Adapter	3.96	DUSTY-GREY / Staubgrau SIM. / aehnlich RAL 7037	5	
				1	0-2177055-1	-	LEVER, 2POS, 180 DEG Spannhebel, 2pos, 180 Grad	19.8	BLACK / schwarz RAL 9005 (9011)	4	
				1	-	0-2177056-1	2POS, MC0N-1.2, REC HSG, 180 DEG, Assy 2pot, MC0N-1.2, Dichtungshalter-Assy, 180 Grad	-	-	3	
				1	0-2141152-1	-	RADIAL SEAL 23.9x43.3 Radialdichtung , 90 Grad	3.2	NATURAL RAL 9001	2	
				1	0-2177054-1	-	2POS, 8MM HV. REC HSG, 180 DEG, SEALED 2pot Gehaeuse, 8mm HV. REC HSG, 180 Grad, gedichtet	62	ORANGE RAL 2003	1	△
COD.	TE ASSY-NO.	REV	WEIGHT (g)	QTY	TE PART-NO.	TE SUB-ASSY-NO.	DESCRIPTION	WEIGHT (g)	SURFACE COLOUR	ITEM	SYMBOL
A	0-2177053-2	B	93	1	0-2208242-1	-	CPA-ADAPTER CPA-Adapter	3.96	DUSTY-GREY / Staubgrau SIM. / aehnlich RAL 7037	5	○
				1	0-2177055-1	-	LEVER, 2POS, 180 DEG Spannhebel, 2pos, 180 Grad	19.8	BLACK / schwarz RAL 9005 (9011)	4	
				1	-	0-2177056-1	2POS, MC0N-1.2, REC HSG, 180 DEG, Assy 2pot, MC0N-1.2, Dichtungshalter-Assy, 180 Grad	-	-	3	
				1	0-2141152-1	-	RADIAL SEAL 23.9x43.3 Radialdichtung , 90 Grad	3.2	NATURAL RAL 9001	2	
				1	0-2177054-1	-	2POS, 8MM HV. REC HSG, 180 DEG, SEALED 2pot Gehaeuse, 8mm HV. REC HSG, 180 Grad, gedichtet	62	ORANGE RAL 2003	1	○
A	0-2177053-1	B	93	1	0-2208242-1	-	CPA-ADAPTER CPA-Adapter	3.96	DUSTY-GREY / Staubgrau SIM. / aehnlich RAL 7037	5	△
				1	0-2177055-1	-	LEVER, 2POS, 180 DEG Spannhebel, 2pos, 180 Grad	19.8	BLACK / schwarz RAL 9005 (9011)	4	
				1	-	0-2177056-1	2POS, MC0N-1.2, REC HSG, 180 DEG, Assy 2pot, MC0N-1.2, Dichtungshalter-Assy, 180 Grad	-	-	3	
				1	0-2141152-1	-	RADIAL SEAL 23.9x43.3 Radialdichtung , 90 Grad	3.2	NATURAL RAL 9001	2	
				1	0-2177054-1	-	2POS, 8MM HV. REC HSG, 180 DEG, SEALED 2pot Gehaeuse, 8mm HV. REC HSG, 180 Grad, gedichtet	62	ORANGE RAL 2003	1	△
COD.	TE ASSY-NO.	REV	WEIGHT (g)	QTY	TE PART-NO.	TE SUB-ASSY-NO.	DESCRIPTION	WEIGHT (g)	SURFACE COLOUR	ITEM	SYMBOL



Code - A 	Code - B 
Code - C 	Code - D 



LOC	DIFF	REVISIONS					
AI	-	P	LIT	DESCRIPTION	DATE	OWN	APPD
				REVISION			
PROJECT NO. 1			G1	SEE ECR-15-014098	28SEP2005	WSA	DHV
			H1	Variant 0-2177063-1 and -2 added	19FEB2006	WSA	DHV
			H1	Rev. adapted to TC-System	04MAY2006	WSA	DHV
			H2	Code C and Code D activated	02JUN2006	WSA	DHV
			J	PN 9-2177053-1r,2r,3r+4. Obsolete	04SEP2007	CR	DHV

NOTES
Bemerkungen

- 1 IN CASE OF DISCREPANCIES BETWEEN GERMAN AND ENGLISH TEXT THE GERMAN TEXT IS BINDING
Im Falle von Unterschieden zwischen dem deutschen und dem englischen Text ist der deutsche Text verbindlich
- 2 LAYER PACKING WITH CORRUGATED CARDBOARD INTO CARTON ACCORDING SPEC 107-18032
Lagenweise Verpackung mit
- 3 SPECIFIED WIRE RANGE: SEE
Spezifizierter Leitungsquerschnitt: siehe
- 4 VISUAL CONTROL OF VARIANT, SEE TABLE
Optische Kontrolle der Variante, siehe Tabelle
- 5 SUPPLY CONDITION: LEVER IN ENDLOCKING POSITION
Anlieferzustand: Hebel in Endraststellung
- 6 SUPPLIER MARK
Lieferantenkennzeichnung
- 7 CAVITY IDENTIFICATION
Kammerbezeichnung



NOTE Bem.	FEATURE Merkmal
8	PRODUCT-SPEC. 108-94297 Produkt-Spez.
9	APPLICATION-SPEC. 114-94130 Verarbeitungs-Spez.

THIS DRAWING IS A CONTROL DOCUMENT. IT IS THE PROPERTY OF STC AND IS NOT TO BE REPRODUCED OR COPIED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT THE WRITTEN PERMISSION OF STC.		DATE: 19NOV2014		DRAWN BY: JHY		TE Connectivity	
DIMENSIONS: (mm)		TOLERANCES: UNLESS OTHERWISE SPECIFIED		NAME: 2P05.8mmHV.REC HSG.180DEG.ASSY.SEALED Zplc. gedrichete Assy. 8mm HV, 180 grad			
MATERIAL: SEE TABLE		FINISH: SEE TABLE		PRODUCT SPEC: 2P05.8mmHV.REC HSG.180DEG.ASSY.SEALED Zplc. gedrichete Assy. 8mm HV, 180 grad DRAWING NO: 00779 © 2177053		SIZE: 2P05.8mmHV.REC HSG.180DEG.ASSY.SEALED Zplc. gedrichete Assy. 8mm HV, 180 grad RESTRICTED TO MAP FOR	
CUSTOMER DRAWING		CUSTOMER DRAWING		CUSTOMER DRAWING		CUSTOMER DRAWING	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2177053-1](#)