



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED	23NOV2020	SS	DZ
			B1	REVISED	25NOV2020	DZ	SS
			B2	ADD TYPE VI PACKAGE	25DEC2020	SS	DZ




- | | | | | | | | | |
|---|--|---------------------------------|---|-----------|------------|---------------|-----|----|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN
17JAN2014
RICHARD MA |  TE Connectivity | | | | | |
| | | CHK
17JAN2014
SIMON LI | | | | | | |
| DIMENSIONS: | TOLERANCES UNLESS OTHERWISE SPECIFIED: | APVD
17JAN2014
COREI WANG | NAME | | | | | |
| mm | | PRODUCT SPEC
108-115068 | SOCKET ASSEMBLY
DDR4 DIMM, SMT TYPE GENERAL
288 POSITION | | | | | |
|  | 0 PLC ±.
1 PLC ±0.25
2 PLC ±0.15
3 PLC ±0.10
4 PLC ±.
ANGLES ±.
FINISH | APPLICATION SPEC
- | SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO | | |
| | MATERIAL | WEIGHT | A200779C-2199155 | | | | | |
| - | | RESTRICTED CUSTOMER | SCALE | 2.1 | SHEET | 1 OF 14 | REV | B2 |



Printed on 4 Jan 2021 12:09 from FG086959

- 7 SHORT, LONG AND MIDDLE LATCH ARE OPTIONAL FOR DIFFERENT KEEPOUT APPLICATION.
- 8 BOARDLOCK AND TAB ARE OPTIONAL FOR DIFFERENT APPLICATION.
- 9 MYLAR AND LARGE CAP&SMALL CAP ARE OPTIONAL FOR DIFFERENT APPLICATION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RICHARD MA 17JAN2014	TE Connectivity SOCKET ASSEMBLY DDR4 DIMM, SMT TYPE GENERAL 288 POSITION			
DIMENSIONS: mm		CHK SIMON LI 17JAN2014				
		APVD COREI WANG 17JAN2014	NAME			
		PRODUCT SPEC	108-115068			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	-			
MATERIAL		WEIGHT	-			
FINISH		RESTRICTED CUSTOMER	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
-		-	A200779C-2199155			
			SCALE 3:1 SHEET 2 OF 14 REV B2			



Printed on 4 Jan 2021 12:09 from F6086959

- 1.DATUM Z IS THE TOP SIZE OF PCB.
- 2.HOLD DOWN HOLE SHOULD BE PLATED THROUGH HOLE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RICHARD MA CHK SIMON LI APVD COREL WANG	17JAN2014 17JAN2014 17JAN2014	 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.25 2 PLC ±0.15 3 PLC ±0.10 4 PLC ± ANGLES ± FINISH		NAME SOCKET ASSEMBLY DDR4 DIMM, SMT TYPE GENERAL 288 POSITION	
		PRODUCT SPEC 108-115068		SIZE A200779	
MATERIAL		APPLICATION SPEC -		CAGE CODE C-2199155	
-		WEIGHT -		DRAWING NO C-2199155	
-		RESTRICTED CUSTOMER		SCALE 1:1	SHEET 3 OF 14
				REV B2	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SHORT LATCH TYPE

TYPE V	NO MYLAR	SHORT LATCH	3 TAB	NATURAL	BLACK	0.00038 MIN	2368060-4
TYPE V	NO MYLAR	SHORT LATCH	3 TAB	BLACK	BLACK	0.00038 MIN	2368060-3
TYPE I	MYLAR	SHORT LATCH	3 TAB	NATURAL	YELLOW(107C)	0.00038 MIN	9-2199155-3
TYPE I	MYLAR	SHORT LATCH	3 TAB	NATURAL	BLACK	0.00076 MIN	9-2199155-2
TYPE I	MYLAR	SHORT LATCH	3 TAB	NATURAL	BLACK	0.00038 MIN	9-2199155-1
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	GREEN(375C)	BLACK	0.00050 MIN	8-2199155-1
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	BLUE(2935U)	BLUE(2935U)	0.00076 MIN	6-2199155-9
TYPE I	NO MYLAR	SHORT LATCH	3 BOARDLOCK	NATURAL	BLACK	0.00076 MIN	6-2199155-8
TYPE I	NO MYLAR	SHORT LATCH	3 BOARDLOCK	BLACK	BLACK	0.00076 MIN	6-2199155-4
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	BLACK	BLACK	0.00050 MIN	5-2199155-2
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	NATURAL	BLACK	0.00050 MIN	5-2199155-1
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	NATURAL	BLUE(2935U)	0.00038 MIN	5-2199155-0
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	BLACK	NATURAL	0.00076 MIN	4-2199155-8
TYPE I	NO MYLAR	SHORT LATCH	3 BOARDLOCK	NATURAL	NATURAL	0.00076 MIN	4-2199155-7
TYPE I	MYLAR	SHORT LATCH	3 TAB	NATURAL	NATURAL	0.00076 MIN	4-2199155-6
TYPE I	MYLAR	SHORT LATCH	3 TAB	BLACK	BLACK	0.00076 MIN	4-2199155-5
TYPE III	NO MYLAR	SHORT LATCH	3 TAB	NATURAL	BLACK	0.00038 MIN	3-2199155-4
TYPE III	NO MYLAR	SHORT LATCH	3 TAB	BLACK	BLACK	0.00038 MIN	3-2199155-3
TYPE I	MYLAR	SHORT LATCH	3 TAB	BLACK	BLACK	0.00038 MIN	3-2199155-2
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	NATURAL	BLUE(2935U)	0.00076 MIN	1-2199155-3
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	GREEN(375C)	BLACK	0.00076 MIN	2199155-7
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	NATURAL	NATURAL	0.00076 MIN	2199155-6
TYPE I	MYLAR	SHORT LATCH	3 TAB	NATURAL	BLUE(2935U)	0.00076 MIN	2199155-5
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	BLACK	BLACK	0.00076 MIN	2199155-4
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	BLACK	BLACK	0.00038 MIN	2199155-3
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	NATURAL	BLACK	0.00076 MIN	2199155-2
TYPE I	MYLAR	SHORT LATCH	3 BOARDLOCK	NATURAL	BLACK	0.00038 MIN	2199155-1
PACKAGE TYPE	PICK-UP TYPE	LATCH TYPE	HOUSING HOLD DOWN	LATCH COLOR	HOUSING COLOR	CONTACT GOLD INTERFACE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

±

-

1 PLC

±

0.25

2 PLC

±

0.15

3 PLC

±

0.10

4 PLC

±

-

ANGLES

±

-

FINISH

-

DWN

17JAN2014

RICHARD MA

CHK

17JAN2014

SIMON LI

APVD

17JAN2014

COREL WANG

PRODUCT SPEC

108-115068

APPLICATION SPEC

-

WEIGHT

-

RESTRICTED CUSTOMER

TE Connectivity

NAME

SOCKET ASSEMBLY
DDR4 DIMM,SMT TYPE GENERAL
288 POSITION

SIZE

A2

CAGE CODE

00779

DRAWING NO

C-2199155

RESTRICTED TO

SCALE

1:1

SHEET

4

OF

14

REV

B2

1471-9 (3/11)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

LONG LATCH TYPE

TYPE VI

NO MYLAR

LONG LATCH

3 BOARDLOCK

NATURAL

BLUE(2935U)

0.00076 MIN

1-2368060-9

TYPE VI

NO MYLAR

LONG LATCH

3 BOARDLOCK

NATURAL

BLACK

0.00076 MIN

1-2368060-8

TYPE I

MYLAR

LONG LATCH

3 TAB

BLACK

BLACK

0.00076 MIN

9-2199155-9

TYPE I

MYLAR

LONG LATCH

3 TAB

NATURAL

BLACK

0.00076 MIN

9-2199155-6

TYPE I

MYLAR

LONG LATCH

3 TAB

NATURAL

YELLOW(107C)

0.00038 MIN

9-2199155-5

TYPE I

MYLAR

LONG LATCH

3 TAB

NATURAL

BLACK

0.00038 MIN

9-2199155-4

TYPE I

MYLAR

LONG LATCH

3 BOARDLOCK

BLACK

BLACK

0.00038 MIN

9-2199155-0

TYPE I

NO MYLAR

LONG LATCH

3 TAB

NATURAL

BLUE(2935U)

0.00038 MIN

8-2199155-9

TYPE I

NO MYLAR

LONG LATCH

3 TAB

NATURAL

BLACK

0.00038 MIN

8-2199155-8

TYPE I

MYLAR

LONG LATCH

3 TAB

NATURAL

BLUE(2935U)

0.00076 MIN

8-2199155-5

TYPE I

MYLAR

LONG LATCH

3 BOARDLOCK

NATURAL

NATURAL

0.00038 MIN

8-2199155-4

TYPE I

MYLAR

LONG LATCH

3 BOARDLOCK

BLUE(2935U)

BLUE(2935U)

0.00038 MIN

8-2199155-3

TYPE I

MYLAR

LONG LATCH

3 TAB

BLUE(2935U)

BLUE(2935U)

0.00076 MIN

8-2199155-2

TYPE I

NO MYLAR

LONG LATCH

3 BOARDLOCK

BLACK

BLACK

0.00076 MIN

7-2199155-8

TYPE II

MYLAR

LONG LATCH

2TAB+1BOARDLOCK

NATURAL

NATURAL

0.00038 MIN

7-2199155-7

TYPE II

MYLAR

LONG LATCH

2TAB+1BOARDLOCK

BLACK

BLACK

0.00038 MIN

7-2199155-6

TYPE I

NO MYLAR

LONG LATCH

3 BOARDLOCK

BLUE(2935U)

BLUE(2935U)

0.00076 MIN

7-2199155-5

TYPE I

NO MYLAR

LONG LATCH

3 BOARDLOCK

BLUE(2935U)

BLUE(2935U)

0.00038 MIN

7-2199155-4

TYPE I

NO MYLAR

LONG LATCH

3 BOARDLOCK

BLACK

BLACK

0.00038 MIN

7-2199155-3

TYPE I

MYLAR

LONG LATCH

3 BOARDLOCK

BLACK

BLACK

0.00076 MIN

7-2199155-2

TYPE I

MYLAR

LONG LATCH

3 BOARDLOCK

NATURAL

BLUE(2935U)

0.00045 MIN

7-2199155-1

TYPE I

MYLAR

LONG LATCH

3 BOARDLOCK

NATURAL

BLACK

0.00045 MIN

7-2199155-0

TYPE I

MYLAR

LONG LATCH

3 TAB

GREEN(375C)

YELLOW(107C)

0.00038 MIN

6-2199155-7

TYPE I

MYLAR

LONG LATCH

3 TAB

GREEN(375C)

BLACK

0.00038 MIN

6-2199155-6

TYPE I

MYLAR

LONG LATCH

3 TAB

NATURAL

YELLOW(107C)

0.00038 MIN

6-2199155-5

TYPE I

NO MYLAR

LONG LATCH

3 BOARDLOCK

NATURAL

YELLOW(107C)

0.00038 MIN

6-2199155-3

TYPE I

MYLAR

LONG LATCH

3 BOARDLOCK

BLUE(2935U)

BLUE(2935U)

0.00076 MIN

4-2199155-9

TYPE I

NO MYLAR

LONG LATCH

3 TAB

NATURAL

YELLOW(107C)

0.00038 MIN

2-2199155-4

TYPE I

MYLAR

LONG LATCH

3 BOARDLOCK

NATURAL

NATURAL

0.00076 MIN

2-2199155-3

TYPE I

MYLAR

LONG LATCH

3 TAB

NATURAL

NATURAL

0.00076 MIN

2-2199155-2

TYPE VI

NO MYLAR

LONG LATCH

3 BOARDLOCK

NATURAL

BLUE(2935U)

0.00076 MIN

1-2199155-9

TYPE VI

NO MYLAR

LONG LATCH

3 BOARDLOCK

NATURAL

BLACK

0.00076 MIN

1-2199155-8

TYPE I

MYLAR

LONG LATCH

3 TAB

BLACK

BLACK

0.00038 MIN

1-2199155-6

TYPE I

MYLAR

LONG LATCH

3 TAB

NATURAL

BLUE(2935U)

0.00038 MIN

1-2199155-5

PACKAGE TYPE

PICK-UP TYPE

LATCH TYPE

HOUSING HOLD DOWN

LATCH COLOR

HOUSING COLOR

CONTACT GOLD INTERFACE

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.25

2 PLC ±0.15

3 PLC ±0.10

4 PLC ±-

ANGLES ±-

FINISH

MATERIAL

-

DWN 17JAN2014

CHK 17JAN2014

APVD 17JAN2014

PRODUCT SPEC

108-115068

APPLICATION SPEC

-

WEIGHT

-

RESTRICTED CUSTOMER

NAME

SOCKET ASSEMBLY

DDR4 DIMM,SMT TYPE GENERAL

288 POSITION

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C-2199155

SCALE

1:1

SHEET

5

OF

14

REV

B2

TE Connectivity

SOCKET ASSEMBLY

DDR4 DIMM,SMT TYPE GENERAL

288 POSITION

1471-9 (3/11)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

MIDDLE LATCH TYPE

TYPE I	MYLAR	MIDDLE LATCH	3 TAB	NATURAL	BLACK	0.00076 MIN	2368060-6
TYPE I	MYLAR	MIDDLE LATCH	3 TAB	BLACK	BLACK	0.00076 MIN	2368060-5
TYPE I	MYLAR	MIDDLE LATCH	3 BOARDLOCK	NATURAL	YELLOW(107C)	0.00038 MIN	2368060-2
TYPE I	MYLAR	MIDDLE LATCH	3 BOARDLOCK	NATURAL	BLACK	0.00038 MIN	2368060-1
TYPE I	MYLAR	MIDDLE LATCH	3 TAB	NATURAL	NATURAL	0.00076 MIN	6-2199155-2
TYPE I	MYLAR	MIDDLE LATCH	3 TAB	BLACK	BLACK	0.00076 MIN	6-2199155-1
TYPE I	MYLAR	MIDDLE LATCH	2TAB+1BOARDLOCK	NATURAL	BLACK	0.00038 MIN	6-2199155-0
TYPE I	MYLAR	MIDDLE LATCH	2TAB+1BOARDLOCK	NATURAL	BLUE(2935U)	0.00038 MIN	5-2199155-9
TYPE I	NO MYLAR	MIDDLE LATCH	3 BOARDLOCK	NATURAL	BLACK	0.00038 MIN	5-2199155-8
TYPE I	NO MYLAR	MIDDLE LATCH	3 BOARDLOCK	NATURAL	YELLOW(107C)	0.00038 MIN	5-2199155-7
TYPE I	NO MYLAR	MIDDLE LATCH	3 BOARDLOCK	NATURAL	BLACK	0.00076 MIN	5-2199155-6
TYPE I	NO MYLAR	MIDDLE LATCH	3 BOARDLOCK	NATURAL	YELLOW(107C)	0.00076 MIN	5-2199155-5
TYPE I	MYLAR	MIDDLE LATCH	3 BOARDLOCK	BLACK	BLACK	0.00076 MIN	5-2199155-4
TYPE I	MYLAR	MIDDLE LATCH	3 BOARDLOCK	NATURAL	BLACK	0.00076 MIN	5-2199155-3
TYPE I	LARGE CAP	MIDDLE LATCH	3 TAB	NATURAL	BLACK	0.00038 MIN	3-2199155-7
TYPE I	LARGE CAP	MIDDLE LATCH	3 TAB	BLACK	BLACK	0.00038 MIN	3-2199155-6
TYPE I	NO MYLAR	MIDDLE LATCH	3 TAB	BLACK	BLACK	0.00076 MIN	2-2199155-6
TYPE I	NO MYLAR	MIDDLE LATCH	3 TAB	NATURAL	NATURAL	0.00076 MIN	2-2199155-5
TYPE IV	SMALL CAP	MIDDLE LATCH	3 TAB	NATURAL	BLACK	0.00038 MIN	2-2199155-1
TYPE IV	SMALL CAP	MIDDLE LATCH	3 TAB	BLACK	BLACK	0.00038 MIN	2-2199155-0
TYPE I	MYLAR	MIDDLE LATCH	3 TAB	NATURAL	BLACK	0.00076 MIN	1-2199155-7
TYPE I	NO MYLAR	MIDDLE LATCH	3 BOARDLOCK	NATURAL	BLUE(2935U)	0.00045 MIN	1-2199155-4
TYPE I	NO MYLAR	MIDDLE LATCH	3 TAB	BLACK	BLUE(2935U)	0.00076 MIN	1-2199155-0
PACKAGE TYPE	PICK-UP TYPE	LATCH TYPE	HOUSING HOLD DOWN	LATCH COLOR	HOUSING COLOR	CONTACT GOLD INTERFACE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.25

2 PLC ±0.15

3 PLC ±0.10

4 PLC ±-

ANGLES ±-

FINISH

DWN 17JAN2014 RICHARD MA

CHK 17JAN2014 SIMON LI

APVD 17JAN2014 COREL WANG

PRODUCT SPEC 108-115068

APPLICATION SPEC -

WEIGHT -

RESTRICTED CUSTOMER

NAME SOCKET ASSEMBLY DDR4 DIMM,SMT TYPE GENERAL 288 POSITION

SIZE A2

CAGE CODE 00779

DRAWING NO C-2199155

RESTRICTED TO

SCALE 1:1

SHEET 6 OF 14

REV B2

TE Connectivity

1471-9 (3/11)


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-						

—FIXED LATCH

TAB (3X)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17JAN2014 RICHARD MA		 TE Connectivity	
		CHK 17JAN2014 SIMON LI			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD 17JAN2014 COREL WANG		SOCKET ASSEMBLY DDR4 DIMM, SMT TYPE GENERAL 288 POSITION	
		PRODUCT SPEC 108-115068			
		APPLICATION SPEC -			
MATERIAL		WEIGHT		SIZE	CAGE CODE
-		-		DRAWING NO	
				A200779	
				C-2199155	
RESTRICTED CUSTOMER				SCALE	SHEET
				1 : 1	7 OF 14
				REV	B2

printed on 4 Jan 2021	12:09 from FG086959
-----------------------	---------------------



Printed on 4 Jan 2021 12:09 from F6086959

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17JAN2014 RICHARD MA	TE Connectivity			
DIMENSIONS: mm		CHK 17JAN2014 SIMON LI				
		APVD 17JAN2014 COREL WANG	NAME SOCKET ASSEMBLY DDR4 DIMM, SMT TYPE GENERAL 288 POSITION			
		PRODUCT SPEC 108-115068	SIZE A200779			
MATERIAL -		APPLICATION SPEC -	DRAWING NO C-2199155		RESTRICTED TO B2	
		WEIGHT -	RESTRICTED CUSTOMER		SCALE 1:1	SHEET 8 OF 14




HARD TRAY TYPE I


- 1. MATERIALS :
TRAY: HIPS, COLOR: BLACK
BOX: CORRUGATED FIBERBOARD
TRANSPARENT BAG: PE
- 2. DIMENSIONS:
TRAY: L=310;W=134;H=26
BOX: L=340;W=300;H=310
- 3. QUANTITY:
24 PCS/TRAY
480 PCS/BOX
- 4. WEIGHT:
NET WEIGHT: 2.6KG
GROSS WEIGHT: 5.8KG

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RICHARD MA 17JAN2014	TE Connectivity			
DIMENSIONS: mm		CHK SIMON LI 17JAN2014				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD COREI WANG 17JAN2014	NAME SOCKET ASSEMBLY DDR4 DIMM,SMT TYPE GENERAL 288 POSITION			
0 PLC ± 1 PLC ±0.25 2 PLC ±0.15 3 PLC ±0.10 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-115068 APPLICATION SPEC - WEIGHT -	SIZE A200779		DRAWING NO C-2199155	
MATERIAL -		RESTRICTED CUSTOMER		RESTRICTED TO		REV B2
		SCALE 1:1		SHEET 9 OF 14		


Printed on 4 Jan 2021 12:09 from FG086959



printed on 4 Jan 2021 12:09 from FG086959




HARD TRAY TYPE II



1. MATERIALS :
TRAY: HIPS, COLOR: BLACK
BOX: CORRUGATED FIBERBOARD
TRANSPARENT BAG: PE
2. DIMENSIONS:
TRAY: L=315;W=150;H=28;PITCH=8.5
BOX: L=330;W=320;H=335
3. QUANTITY:
32 PCS/TRAY
640 PCS/BOX

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RICHARD MA 17JAN2014	TE Connectivity		
		CHK SIMON LI 17JAN2014			
DIMENSIONS: mm		APVD COREL WANG 17JAN2014	NAME SOCKET ASSEMBLY DDR4 DIMM,SMT TYPE GENERAL 288 POSITION		
		PRODUCT SPEC 108-115068	SIZE A200779		
		APPLICATION SPEC -	CAGE CODE C-2199155		
MATERIAL -		WEIGHT -	DRAWING NO -		
		RESTRICTED CUSTOMER		SCALE 1:1	SHEET 10 OF 14
				REV B2	



Printed on 4 Jan 2021 12:09 from FG086959

D


C

B

A



LOC	DIST	REVISIONS				
-	-	P	LTR	DESCRIPTION	DATE	DWN APVD

1. MATERIALS :
- TRAY: HIPS, COLOR: BLACK
- BOX: CORRUGATED FIBERBOARD
- TRANSPARENT BAG: PE
2. DIMENSIONS:
- TRAY: L=298;W=170;H=29;PITCH=9.8
- BOX: L=355;W=315;H=350
3. QUANTITY:
- 29 PCS/TRAY
- 580 PCS/BOX



HARD TRAY TYPE III

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RICHARD MA 17JAN2014	TE TE Connectivity			
		CHK SIMON LI 17JAN2014				
		APVD COREL WANG 17JAN2014	NAME SOCKET ASSEMBLY			
		PRODUCT SPEC 108-115068	DDR4 DIMM, SMT TYPE GENERAL			
		APPLICATION SPEC -	288 POSITION			
		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-2199155	RESTRICTED TO
		RESTRICTED CUSTOMER	SCALE 1:1	SHEET 11	OF 14	REV B2




- 1. MATERIALS :
TRAY: HIPS, COLOR: BLACK
BOX: CORRUGATED FIBERBOARD
TRANSPARENT BAG: PE
- 2. DIMENSIONS:
TRAY: L=315;W=138;H=28;PITCH=8.0
BOX: L=330;W=295;H=335
- 3. QUANTITY:
32 PCS/TRAY
640 PCS/BOX

HARD TRAY TYPE IV

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RICHARD MA 17JAN2014	TE Connectivity			
DIMENSIONS:		CHK SIMON LI 17JAN2014				
mm		APVD COREL WANG 17JAN2014	NAME SOCKET ASSEMBLY DDR4 DIMM, SMT TYPE GENERAL 288 POSITION			
		PRODUCT SPEC 108-115068	SIZE A200779		DRAWING NO C-2199155	
		APPLICATION SPEC -	CAGE CODE A200779		RESTRICTED TO B2	
MATERIAL -		WEIGHT -	RESTRICTED CUSTOMER		SCALE 1:1	SHEET 12 OF 14

printed on 4 Jan 2021 12:09 from FG086959





printed on 4 Jan 2021 12:09 from FG086959

LOC	DIST	REVISIONS					
-	-	P	LTR	DESCRIPTION	DATE	DWN	APVD

1. MATERIALS :
- TRAY: PVC, COLOR: TRANSPARENT
- BOX: CORRUGATED FIBERBOARD
- TRANSPARENT BAG: PE
2. DIMENSIONS:
- TRAY: L=410;W=270;H=36.3;
- BOX: L=460;W=320;H=290
3. QUANTITY:
- 60 PCS/TRAY
- 420 PCS/BOX

SOFT TRAY TYPE V

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	17JAN2014	TE Connectivity			
		CHK	17JAN2014				
		APVD	17JAN2014	NAME			
		PRODUCT SPEC		SOCKET ASSEMBLY			
		APPLICATION SPEC		DDR4 DIMM, SMT TYPE GENERAL			
		WEIGHT		288 POSITION			
		RESTRICTED CUSTOMER		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				A2	00779	C-2199155	
				SCALE	1:1	SHEET	OF
				13		14	REV
						B2	



- 1. MATERIALS :
TRAY: HIPS, COLOR: BLACK
BOX: CORRUGATED FIBERBOARD
TRANSPARENT BAG: PE
- 2. DIMENSIONS:
TRAY: L=310;W=134;H=26
BOX: L=340;W=300;H=310
- 3. QUANTITY:
24 PCS/TRAY
480 PCS/BOX
- 4. WEIGHT:
NET WEIGHT: 2.6KG
GROSS WEIGHT: 5.8KG

HARD TRAY TYPE VI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RICHARD MA 17JAN2014		
		CHK SIMON LI 17JAN2014		
		APVD COREL WANG 17JAN2014	NAME SOCKET ASSEMBLY DDR4 DIMM,SMT TYPE GENERAL 288 POSITION	
DIMENSIONS: mm		PRODUCT SPEC 108-115068	SIZE A200779	
		APPLICATION SPEC -	DRAWING NO C-2199155	
MATERIAL -		WEIGHT -	RESTRICTED TO B2	
		RESTRICTED CUSTOMER		SCALE 1:1
				SHEET 14 OF 14

printed on 4 Jan 2021 12:09 from F6086959

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2199154-3](#)